



中国国家强制性产品认证证书



证书编号: 2020322307003149

认证委托人名称: Bürkert Werke GmbH & Co. KG
 认证委托人地址: Christian-Bürkert-Str. 13-17, 74653 Ingelfingen, Germany
 生产者名称: Bürkert Werke GmbH & Co. KG
 生产者地址: Christian-Bürkert-Str. 13-17, 74653 Ingelfingen, Germany
 生产企业名称: Bürkert Werke GmbH & Co. KG
 企业地址: Landauer Straße 24, 74582 Gerabronn, Germany
 产品名称: 电磁线圈
 系列、规格、型号: AC19 系列
 标准: GB/T 3836. 1-2021、GB/T 3836. 3-2021、GB/T 3836. 9-2021、
 GB/T 3836. 31-2021

认证模式: 型式试验+初始工厂检查+获证后监督

上述产品符合 CNCA-C23-01:2019 《强制性产品认证实施规则 防爆电气》的要求, 特发此证。
产品相关信息详见附件。

发证日期: 2023年04月30日

有效期至: 2025年11月03日

首次发证日期: 2020年11月04日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



批准:



上海仪器仪表自控系统检验测试所有限公司

<http://www.sitiias.com.cn>

中国·上海·漕宝路103号200233

电话: +86 21 64510844

S 0011674

ABD 1000458836 ML Version: A Status: RL (released | freigegeben) printed: 21.06.2024



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION



CERTIFICATE NO: 2020322307003149

APPLICANT: Bürkert Werke GmbH & Co. KG
ADDRESS: Christian-Bürkert-Str.13-17,74653 Ingelfingen,Germany
MANUFACTURER: Bürkert Werke GmbH & Co. KG
ADDRESS: Christian-Bürkert-Str.13-17,74653 Ingelfingen,Germany
FACTORY: Bürkert Werke GmbH & Co. KG
ADDRESS: Landauer Straße 24,74582 Gerabromm,Germany

PRODUCT: Solenoid coil
SERIES,SPECIFICATION,MODEL: AC19 Series
STANDARDS: GB/T 3836.1-2021、GB/T 3836.3-2021、GB/T 3836.9-2021、
 GB/T 3836.31-2021

Type of Certification: Type test + Initial inspection + Surveillance inspection

This is to certify that the above mentioned product(s)complies with the requirements of implementation rules for compulsory certification (REFNO. CNCA-C23-01:2019).

Refer to the attachment for detailed information.

Valid from:April 30, 2023

Valid until:November 3, 2025

Date of original certification:November 4, 2020

The validity of this certificate is subject to positive result of the periodic surveillance by issuing certification body until the expiry date.

This certificate is available through CNCA's website: www.cnca.gov.cn



APPROVAL:

Guo AiHua



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.

<http://www.sitiias.com.cn>

Building 9,103 Cao Bao Road, Shanghai 200233,China

Tel: +86 21 64510844

s 0009108

ABD 1000458836 ML Version: A Status: RL (released | freigegeben) printed: 21.06.2024



中国国家强制性产品认证证书



证书编号: 2020322307003149

附件


产品名称: 电磁线圈

型号规格: AC19-SAS-SG-SW_1-VAR*

Feature	Description	Form
Typ	Bürkert type designation	AC19
SAS	Interface between valve and coil	U5
SG	Spool size 42mm	K
SW 1	Winding code	**E*
VAR*	Bridge rectifier wiring Circuitry power switching	CZ24 CZ05
	Electrical connection Terminal box (various internal threads and outlet directions, see PTB 15 ATEX 1011 U / IECEx PTB 15.0037U)	JA**
	Electrical connection cable outlet Betaflamkabel	JJ04
	Electrical connection cable outlet silicone cable	JJ05
	Cable length (various)	JW**
	Identification of Ex devices	PX38

防爆标志: Ex mb IIC T4 Gb
 Ex mb IIIC T130°C Db
 Ex eb mb IIC T4 Gb
 Ex mb tb IIIC T130°C Db

电气参数: 额定电压: 24VDC/110VDC/230VDC;
 24VAC/110VAC/230VAC, 50/60Hz
 120VAC/240VAC, 60Hz。
 功率: 15W/44W

批准: 



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



证书编号：2020322307003149

附件

相关报告编号： 2020S17402-004138, 2023S17402-011377

使用条件：

1. 特殊（限制）使用条件：

1) 产品使用环境温度范围：

线圈类型	桥式整流	开关电源
功率	15W	44W
使用环境温度	-40 ~ +55 (°C)	-40 ~ +70 (°C)

2) 产品禁止在可能产生静电荷积聚的区域使用。

3) 产品一般为单体安装。对于一组多个产品的安装，用户必须确保产品相互间发热不会超过允许的环境温度。

4) 产品应始终配合铁芯一起使用。

5) 电缆在安装时必须注意弯曲半径不得太小。

2. 产品外壳防护等级：IP64。

批 准：



上海仪器仪表自控系统检验测试所有限公司