Accessories for pneumatic stroke and rotary actuators of the CLASSIC, INOX and ELEMENT series

- Complete modular designed accessory program
- More for less – optimal configuration costs
- Easy maintenance and commissioning
- Increase system and operational safety

Product variants described in the data sheet may differ from the product presentation and description.

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Can be combined with

Type 2000
Pneumatically operated 2/2-way angle seat valve (Type CLASSIC)

Type 2006
Pneumatically operated 3/2-way seat valve CLASSIC

Type 2031
2/2-way diaphragm valve with pneumatic plastic actuator (Type CLASSIC)

Type 2012
Pneumatically operated 2/2-way globe valve (Type CLASSIC)

Type 210X
ELEMENT process valves

Type 2060
Pneumatically operated 2/2-way angle seat valve with stainless steel actuator

Type 2063
2/2-way diaphragm valve with pneumatic actuator in stainless steel (Type INOX)

Type description

The accessory option package is the comprehensive addition to the Bürkert process valves with pneumatic actuators. The flexible, easily accessible concept of modular accessories has been designed to cover individual application requirements in a cost-effective way.

The accessories are easy to fit (even on site).

© Christian Bürkert GmbH & Co. KG, Subject to alteration

Visit product website

Table of contents

1. Product accessories overview 3

1.1. Product properties....3

2. Product accessories 4

2.1. Pneumatic control/electrical feedback unit....4
Type 8697 and Type 8690 for on/off process valves....4
Type 8691 and Type 8695 for decentralised automation of on/off CLASSIC and ELEMENT process valves....5
2.2. Type 1060 electrical position feedback for CLASSIC and INOX valves....6
2.3. Proximity switch adapters for CLASSIC, INOX and ELEMENT valves....8
Mounting bracket....8
Threaded nipple....10
2.4. Stroke limiter....11
CLASSIC/INOX....11
ELEMENT....13
2.5. Handwheel for CLASSIC and INOX valves....16
2.6. Installation wrench for CLASSIC actuator cover....17
2.7. NAMUR adapter for pilot valves for CLASSIC valves....18
50 (D)...80 (F) for seat valve, 63 (E)...100 (G) for diaphragm valve....19
100 (G), 125 (H) for seat valve, 25 (H) for diaphragm valve....20
2.8. Type SC02 electrical position indicator for INOX valves....21
2.9. Actuator blocking for CLASSIC and INOX valves....22
2.10. Dead man's lever....23
2.11. Stroke limiter for Type 869x CLASSIC and ELEMENT valves....24

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

1. Product accessories overview

1.1. Product properties

Note:
If the product accessories are installed, the customer must ensure that appropriate documentation is provided.

Type	Description	Actuator size Ø [mm]	Further information
CLASSIC	**(Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033)**		
Type 8697	Electrical position feedback	40 (C)...225 (L)	"2.1. Pneumatic control/electrical feedback unit" on page 4
Type 8697	Pneumatic control	40 (C)...50 (D)	
Type 8690	Pneumatic control	63 (E)...125 (H)	
Type 8691	Pneumatic control	175 (K)...225 (L)	
Type 8695	Control head/electrical feedback unit	40 (C)...50 (D)	
Type 8691	Control head/electrical feedback unit	63 (E)...225 (L)	
Type 1060	Position feedback	40 (C)...225 (L)	"2.2. Type 1060 electrical position feedback for CLASSIC and INOX valves" on page 3
–	Adapter for proximity switch	40 (C)...225 (L)	"2.3. Proximity switch adapters for CLASSIC, INOX and ELEMENT valves" on page 8
–	Stroke limiter	40 (C)...225 (L)	"2.4. Stroke limiter" on page 11
–	Handwheel for linear actuators	50 (D)...125 (H)	"2.5. Handwheel for CLASSIC and INOX valves" on page 16
–	Mounting installation wrench	40 (C)...125 (H)	"2.6. Installation wrench for CLASSIC actuator cover" on page 17
–	NAMUR adapter	50 (D)...125 (H)	"2.7. NAMUR adapter for pilot valves for CLASSIC valves" on page 18
–	Stroke limiter on Type 869x	50 (D)...125 (H)	"2.11. Stroke limiter for Type 869x CLASSIC and ELEMENT valves" on page 3
INOX	**(Type 2060, Type 2063, Type 2064, Type 2065, Type 2080)**		
Type 8697	Electrical position feedback	40 (C)...125 (H)	"2.1. Pneumatic control/electrical feedback unit" on page 4
Type 8697	Pneumatic control	40 (C)...50 (D)	
Type 8690	Pneumatic control	63 (E)...125 (H)	
Type 8695	Control head/electrical feedback unit	40 (C))...50 (D)	
Type 8691	Control head/electrical feedback unit	63 (E)...125 (H)	
Type 1060	Position feedback	40 (C)...125 (H)	"2.2. Type 1060 electrical position feedback for CLASSIC and INOX valves" on page 3
Type SC02	Electrical position feedback	32 (B)	"2.8. Type SC02 electrical position indicator for INOX valves" on page 3
–	Adaption for inductive proximity switch	40 (C)...125 (H)	"2.3. Proximity switch adapters for CLASSIC, INOX and ELEMENT valves" on page 8
–	Stroke limiter	40 (C)...125 (H)	"2.4. Stroke limiter" on page 11
–	Handwheel for linear actuators	50 (D)...125 (H)	"2.5. Handwheel for CLASSIC and INOX valves" on page 16
–	Actuator blocking	40 (C)...125 (H)	"2.9. Actuator blocking for CLASSIC and INOX valves" on page 22
–	Dead man's lever	32 (B)	"2.10. Dead man's lever" on page 23
–	Stroke limiter for Type 869x	50 (D)...125 (H)	"2.11. Stroke limiter for Type 869x CLASSIC and ELEMENT valves" on page 3
ELEMENT	**(Type 2100, Type 2300, Type 2101, Type 2301, Type 2106, Type 2103, Type 2104, Type 2105)**		
Type 8697	Pneumatic control/feedback unit	50 (D)	"2.1. Pneumatic control/electrical feedback unit" on page 4
Type 8690	Pneumatic control/feedback unit	70 (M)...130 (P)	
Type 8695	Control head/electrical feedback unit	50 (D)	
Type 8691	Control head/electrical feedback unit	70 (M)...225 (L)	
–	Adaption for inductive proximity switch	50 (D)...130 (P)	"2.3. Proximity switch adapters for CLASSIC, INOX and ELEMENT valves" on page 8
–	Stroke limiter	50 (D)...225 (L)	"2.4. Stroke limiter" on page 11
–	Stroke limiter for Type 869x	70 (M)...130 (P)	"2.11. Stroke limiter for Type 869x CLASSIC and ELEMENT valves" on page 3

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2. Product accessories

2.1. Pneumatic control/electrical feedback unit

Type 8697 and Type 8690 for on/off process valves

Note:

- Non-retrofittable components are only orderable with valve actuator as Type 8801.
- The feedback variant of Type 8690 for CLASSIC process valves is covered by the electrical feedback unit of Type 8697.

Variant	ss(without pilot valve)	Pneumatic control (with pilot valve)	Pneumatic control (with pilot valve)
Type	**Type 8697** ▶	**Type 8697** ▶	**Type 8690** ▶
Pictures			
Type description	The electrical feedback variant of Type 8697 is optimised for integrated mounting on process valves of the CLASSIC and the INOX series. Mechanical or inductive limit switches detect the valve position and report it electrically to the control unit. The feedback unit Type 8697 can be combined with all available actuator sizes for CLASSIC.	The pneumatic control and feedback unit Type 8697 is designed for integrated mounting on process valves of the CLASSIC and the ELEMENT series with a small nominal diameter. Mechanical or inductive limit switches detect the valve position and report it electrically to the control unit.	The pneumatic control unit Type 8690 is designed for the decentralised automation of ELEMENT series pneumatic process valves. Mechanical or inductive limit switches detect the valve position. The integrated pilot valve controls single-acting or double-acting actuators.
	An intrinsically safe variant in accordance with ATEX / IECEx is optionally available for use in potentially explosive environments.		
Actuator size (Ø) in mm			
CLASSIC	40 (C), 50 (D), 63 (E), 80 (F), 100 (G), 125 (H), 175 (K), 225 (L)	40 (C), 50 (D)	63 (E), 80 (F), 100 (G), 125 (H)
INOX	40 (C), 50 (D), 63 (E), 80 (F), 100 (G), 125 (H)	40 (C), 50 (D)	63 (E), 80 (F), 100 (G), 125 (H)
INOX REV1	50 (D), 70 (M), 90 (N), 130 (P)	–	–
ELEMENT	50 (D)	50 (D)	70 (M), 90 (N), 225 (L), 130 (P)
Mounting on seat valves			
CLASSIC	Type 2000, Type 2012, Type 2006		
INOX	Type 2060		
ELEMENT	Type 2100, Type 2101, Type 2106		
Mounting on diaphragm valves			
CLASSIC	Type 2031, Type 2032, Type 2033		
INOX	Type 2063, Type 2064, Type 2065		
ELEMENT	Type 2103, Type 2104, Type 2105		
Features			
End position indicator	Micro switch or proximity switch		
Position indicator	Visual display pen		
Approvals	ATEX Cat. 3GD / IECEx, ATEX Cat. 2DG / IECEx		
Fieldbus communication	No		
Electrical connection	Cable gland or M12 push-in connector		

Type 8691 and Type 8695 for decentralised automation of on/off CLASSIC and ELEMENT process valves

Variant	Control head/electrical feedback unit	
	Type 8695 ▶	**Type 8691** ▶
Picture		
Type description	The control head Type 8695 is designed for the decentralised automation of ELEMENT series pneumatic process valves with a small nominal diameter. The valve position is detected via a contactless, analogue sensor element which automatically detects and saves the valve end positions during commissioning via the teach function. The integrated pilot valve controls single-acting or double-acting actuators. The design of the control head and actuator is specially conceived for the requirements of hygienic process conditions and enables integrated pilot air duct without external pipework.	The control head Type 8691 is designed for the decentralised automation of the ELEMENT series pneumatic process valves. The valve position is detected via a contactless, analogue sensor element which automatically detects and saves the valve end positions during commissioning via the teach function. The integrated pilot valve controls single-acting or double-acting actuators. The design of the control head and actuator is specially conceived for the requirements of hygienic process conditions and enables integrated pilot air duct without external pipework.
Actuator size (Ø) in mm		
CLASSIC	40 (C), 50 (D)	63 (E), 80 (F), 100 (G), 125 (H), 175 (K), 225 (L)
INOX	40 (C), 50 (D)	63 (E), 80 (F), 100 (G), 125 (H)
ELEMENT	50 (D)	70 (D), 90 (N), 130 (P), 225 (L)
Mounting on seat valves		
CLASSIC	Type 2000, Type 2012, Type 2006	
INOX	Type 2060	
ELEMENT	Type 2100, Type 2101, Type 2106	
Mounting on diaphragm valves		
CLASSIC	Type 2031, Type 2032, Type 2033	
INOX	Type 2063, Type 2064, Type 2065	
ELEMENT	Type 2103, Type 2104, Type 2105	
Features		
End position indicator	Contact-free inductive position detection with teach function	
Status indicator	Coloured high-power LEDs	Coloured LEDs
Approvals	ATEX Cat. 3GD, IECEx	
Fieldbus communication	AS-Interface, IO-Link, Bürkert system bus (büS)	
Electrical connection	Cable gland or M12 push-in connector	M12 push-in connector

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.2. Type 1060 electrical position feedback for CLASSIC and INOX valves

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
INOX: Type 2060, Type 2063, Type 2064, Type 2065

The electrical position indicator is screwed in instead of the visual position indicator. When the valve opens, the actuator piston lifts a mushroom which actuates a micro switch with changeover contact for electrical position feedback. At the same time the mushroom serves as an visual position indicator.

Note:
Further information can be found in the data sheet **Type 1060** ▶.

Dimensions

Note:
Dimensions in mm, unless otherwise stated

50 (D)...80 (F) SW32, 100 (G), 125 (H) SW41	40 (C) SW30 (with cover), 175 (K)...225 (L) SW32
	

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	Article no.
CLASSIC/INOX	40 (C)	293113 1.)
	50 (D)...80 (F)	701515
	100 (G), 125 (H)	701516
CLASSIC	175 (K), 225 (L)	655696

1.) For valves built as of 2016

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.3. Proximity switch adapters for CLASSIC, INOX and ELEMENT valves

Applicable to:

- CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
- INOX: Type 2060, Type 2063, Type 2064, Type 2065
- ELEMENT: Type 2100, Type 2300, Type 2101, Type 2301, Type 2106, Type 2103, Type 2104, Type 2105

The adaptation for M12 proximity switches is available for all actuator series and control functions and can easily be retrofitted instead of the normal position indicator. It is available in single and double variants, depending on which valve position is to be queried.

Mounting bracket

Dimensions



DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Sensor	Actuator size Ø [mm]	A	B	C	D	E	F	Ø G	H [SW]	J [SW]	K 45° (angle seat) 40° (tank bottom) 35° (tank bottom)	L	M	Article no.
CLASSIC/ INOX	Single	50 (D), 63 (E), 80 (F)	66	32	43	–	–	29	62	19	30	44 47 50	51 52 52	–	649381
		100 (G), 125 (H)	81	35	46	–	–	29	62	19	30	52 56 59	53 54 54	–	649382
	Double	50 (D), 63 (E), 80 (F)	81	28	–	74	85	24	52	19	30	59 63 68	–	78 81 84	667988
		100 (G), 125 (H)	96	31	–	77	88	24	52	19	30	69 75 80	–	80 83 86	667989
CLASSIC	Double	175 (K), 225 (L)	145	68	–	136	147	24	52	19	30	104 112 120	–	106 111 116	669810
INOX REV1	Single	50 (D), 70 (M)	91	33	44	–	–	29	26	18	30	66 71 76	52 52 53	–	699989
		90 (N), 130 (P)	46	41	53	–	–	22	38	18	30	51 55 58	54 55 57	–	699991
	Double	50 (D), 70 (M)	93	29	–	75	86	24	26	18	30	67 73 78	–	78 82 85	699990
		90 (N), 130 (P)	94	30	–	76	87	25	38	18	30	68 74 78	–	79 83 86	699992
ELEMENT	Single	50 (D)	55	36	47	–	–	26	20	18	17	41 44 46	52 53 54	–	279579
		70 (M), 90 (N), 130 (P)	70	38	49	–	–	26	42	18	19	51 55 58	53 54 55	–	279578
	Double	50 (D)	95	38	–	88	99	29	42	18	19	69 74 79	–	90 94 97	674053
		70 (M), 90 (N), 130 (P)	95	36	–	86	97	29	20	18	17	69 74 79	–	89 93 96	674052
		225 (L)	86	30	–	76	87	24	42	18	19	62	–	78	60035187

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Threaded nipple

The simple adaptation for M12 initiators is mounted in place of the normal position indicator and records the open valve position. Due to the lack of sealing of the upper actuator chamber, this cost-effective variant is only suitable for control function A.

Dimensions



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	A	B	C 45° (angle seat) 40° (tank bottom) 35° (tank bottom)	Article no.
CLASSIC/INOX	40 (C), 50 (D), 63 (E), 80 (F)	6	SW32	17	648152
				16	
				15	
	100 (G), 125 (H)	6	SW41	21	649257
				20	
				18	
CLASSIC	175 (K), 225 (L)	29	SW32	34	669773
INOX REV1	50 (D), 70 (M)	16	SW19	20	698536
	90 (N), 130 (P)	17	SW36	26	698537
ELEMENT	50 (D)	20	SW17	22	673967
	70 (M), 90 (N), 130 (P)	19	SW24	24	673968 1.)
		14		21	581139 2.)

1.) PPS
2.) Stainless steel

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.4. Stroke limiter

CLASSIC/INOX

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
INOX: Type 2060, Type 2063, Type 2064, Type 2065

Maximum stroke limiter without visual position indicator

Actuator size Ø [mm]	
40 (C)...80 (F)	**175 (K)...225 (L)**

Product properties	
Maximum stroke limiter	
Special feature	Without visual position indicator (upwards stroke limiter only)
Mounting	The stroke limiter replaces both the position indicator and the transparent cover. For Ø 100 (G) mm and Ø 125 (H) mm, the actuator cover must be removed for mounting. To do this, a special key is required (see "2.6. Installation wrench for CLASSIC actuator cover" on page 17).

Dimensions

Note:
Dimensions in mm, unless otherwise stated

Actuator size Ø 40 (C)...225 (L) mm (maximum stroke limiter)
(single variant, only for valves with control function A, closed by spring force in rest position)



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	B	H	Article no.
CLASSIC/INOX	40 (C), 50 (D), 63 (E), 80 (F)	SW17	40	637866
	100 (G)	SW19	55	637867
	125 (H)			637868
CLASSIC	175 (K), 225 (L)	SW24	97	655600

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Minimum/maximum stroke limiter with visual position indicator

Actuator size Ø [mm]	
50 (D)...80 (F)	175 (K)...225 (L)

Product properties	
Minimum/maximum stroke limiter	
Special feature	Minimum/maximum flow setting (upwards and downwards stroke limiter) with visual position indicator
Mounting	The stroke limiter replaces both the position indicator and the transparent cover (see "2.6. Installation wrench for CLASSIC actuator cover" on page 17). The variant for actuator size Ø 175 (K) mm cannot be retrofitted and must be installed at the factory.

Dimensions

Actuator size Ø 50 (D)...175 (K) mm (minimum/maximum stroke limiter)



Ordering chart

Valve actuator series	Actuator size Ø [mm]	D	H	Article no.
CLASSIC/INOX	50 (D), 63 (E), 80 (F) 1.)	39	50	636820
	100 (G) 1.)	53	73	636821
	125 (H) 1.)			640703
CLASSIC	175 (K), 225 (L) (diaphragm valves)	86	172	655631
	175 (K) (globe valves)			659038

1.) Can be retrofitted by the customer

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

ELEMENT

Applicable to:
ELEMENT: Type 2100, Type 2300, Type 2101, Type 2301, Type 2106, Type 2103, Type 2104, Type 2105

Maximum stroke limiter without visual position indicator

Actuator size Ø [mm]	
50 (D)	**70 (M)...130 (P)...225 (L)**

Product properties	
Special feature	Without visual position indicator (upwards stroke limiter only)
Mounting	The stroke limiter replaces both the position indicator and the transparent cover. Actuator size 50 (D)...130 (P) can be easily retrofitted.

Dimensions

Note:
Dimensions in mm, unless otherwise stated

Actuator size 50 (D)...225 (L) (maximum stroke limiter)
(Single variant, only for valves with control function A, closed by spring force in rest position)



1.) Dimension for actuator size 225 (L)

Ordering chart

Valve actuator series	Actuator size Ø [mm]	A	B	C	2-kt SW	Article no.
ELEMENT	50 (D) 1.)	20	15	40	17	677535
	70 (M) 1.)	42	18	53	24	673962
	90 (N) 1.)		16			
	130 (P) 1.)		2			
	225 (L)	40	20	115	32	60011488

1.) Can be retrofitted by the customer

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

Minimum/maximum stroke limiter with visual position indicator

Actuator size Ø [mm]	
50 (D)	70 (M)...130 (P), 225 (L)

Product properties	
Special feature	Minimum/maximum flow setting (upper and lower stroke limiter) with visual position indicator
Mounting	The stroke limiter replaces both the position indicator and the transparent cover. Actuator size 50 (D)...130 (P) can be easily retrofitted.

Dimensions

Actuator size Ø 50 (D)...225 (L) (minimum/maximum stroke limiter)



Ordering chart

Valve actuator series	Actuator size Ø [mm]	A	B	C	Article no.
ELEMENT	50 (D) 1.)	27	38	66	673950
	70 (M) 1.)	45	61	100	673951
	90 (N) 1.)		59		
	130 (P) 1.)		45		
	225 (L)	86	93	184	60011493

1.) Can be retrofitted by the customer

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.5. Handwheel for CLASSIC and INOX valves

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
INOX: Type 2060, Type 2063, Type 2064, Type 2065

Handwheel with visual position indicator for manual actuation of the valve, e.g. in the event of a pressure failure. Only for actuators with control function A (closed by spring force).

Dimensions



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	D	H	Article no.
CLASSIC/INOX	50 (D), 63 (E), 80 (F)	80	68	636822
	100 (G), 125 (H)	150	85	636823

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.6. Installation wrench for CLASSIC actuator cover

These installation spanners are required to open the CLASSIC series actuators when, for example, maintenance is to be carried out or seals are to be replaced.

Ordering chart

Valve actuator series		Actuator size Ø [mm]	Article no.
CLASSIC		40 (C), 50 (D)	639175
		63 (E)	639170
		80 (F)	639171
		100 (G)	639172
		125 (H)	639173

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.7. NAMUR adapter for pilot valves for CLASSIC valves

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033

By using these adapter plates, pilot valves according to NAMUR standard can be fitted directly to the actuators.

Product properties	
Material	
Plate and hollow screw	Stainless steel 1.4021 or CuZn39 Pb3 F44
Seal: O-ring	NBR 75



Mounting of NAMUR adapter	
No.	**Description**
1	Plate
2	Hollow screw
3	O-rings

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

50 (D)...80 (F) for seat valve, 63 (E)...100 (G) for diaphragm valve

Dimensions

Note:
Dimensions in mm, unless otherwise stated



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	Material	Article no.
CLASSIC	50 (D)...80 (F) (seat valve) 63 (E)...100 (G) (diaphragm valve)	Stainless steel	632974
		Brass	637113

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

100 (G), 125 (H) for seat valve, 25 (H) for diaphragm valve

Dimensions

Note:
Dimensions in mm, unless otherwise stated



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	Material	Article no.
CLASSIC	100 (G), 125 (H) (seat valve) 125 (H) (diaphragm valve)	Stainless steel	634275
		Brass	637114

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.8. Type SC02 electrical position indicator for INOX valves

Applicable to:
INOX: Type 2060, Type 2063, Type 2064, Type 2065

The SC02 electrical feedback unit for INOX valves in actuator size Ø 32 (B) can be retrofitted to all actuators in this series. The included initiator is screwed into the cover and thus detects the closed actuator position. It is therefore advisable to use a NO initiator, but variants with NC initiators are also available.

Dimensions



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Execution	A	B 45° (angle seat) 40° (tank bottom) 35° (tank bottom)	C	D	Article no.
INOX INOX REV1	NO Ini, 4 mm hose push-in connector	39	17	54	19	583555
	NO Ini, 6 mm hose push-in connector		22			586253
	NC Ini, 4 mm hose push-in connector		27			60005041

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.9. Actuator blocking for CLASSIC and INOX valves

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
INOX: Type 2060, Type 2063, Type 2064, Type 2065

The actuator blocking is used to keep NC (normally closed) valves open in situations when no control pressure is available, for example when the entire valve is to be autoclaved. The actuator blocking replaces both the position indicator and the transparent cover.

Dimensions



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	A	C	D	E	Article no.
CLASSIC/INOX	40 (C)	35	14	8	9	20088712
	50 (D), 63 (E), 80 (F)	35	20	8	9	20088713
	100 (G), 125 (H)	42	28	10	10	20088714
INOX REV1	50 (D)	35	3	17	10	20055972
	70 (M)					
	90 (N)	42	5	19	10	20055973

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.10. Dead man's lever

Applicable to:
INOX: Type 2060, Type 2063, Type 2064, Type 2065, Type 2080

This conversion kit converts any pneumatically operated actuator from the INOX series (Ø 32 (B)) into a manually operated / unpressurised 'push button'. This means that the valve only remains open as long as the levers are actuated. When the levers are released, the valve closes automatically with the normal actuator spring force.

An application case would be a sampling valve, for example, where it must be ensured that the valve is closed again as soon as the operator leaves.

Dimensions



Ordering chart

Note:
Can be retrofitted by the customer

Valve actuator series	Actuator size Ø [mm]	A	B 45° (angle seat) 40° (tank bottom) 35° (tank bottom)	C	Article no.
INOX REV1	32 (B)	94	24	20	20043467
			23		
			21		

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026

2.11. Stroke limiter for Type 869x CLASSIC and ELEMENT valves

Applicable to:
CLASSIC: Type 2000, Type 2012, Type 2006, Type 2031, Type 2032, Type 2033
ELEMENT: Type 2100, Type 2300, Type 2101, Type 2301, Type 2106, Type 2103, Type 2104, Type 2105

The simple stroke limiter for limiting the maximum opening enables the simultaneous use of control heads.

Note:
Only suitable for actuators with control function A (closed by spring force in rest position). ELEMENT variants must also have pilot air ports with G ⅛ threaded socket.

CLASSIC/INOX	ELEMENT

Ordering chart

Valve actuator series	Actuator size Ø [mm]	Type	Article no.
CLASSIC/INOX	50 (D), 63 (E)	Type 8690, Type 8691, Type 8695, Type 8697	689353
	80 (F)		689354
	100 (G), 125 (H)		689355
ELEMENT	70 (M), 90 (N)	Type 8690	680594
	70 (M), 90 (N)	Type 8691, Type 8692, Type 8693, Type 8694	679013
	130 (P)		684134

DTS 1000102756 EN Version: AS Status: RL (released | freigegeben | valide) printed: 09.09.2026