Ecolab Deutschland GmbH
Ecolab-Allee 1
D-40789 Monheim am Rhein

certifies that for

Bürkert Fluid Control Systems
Bürkert Werke GmbH & Co. KG
Christian-Bürkert-Straße 13-17
D-74653 Ingelfingen

Material Resistance Tests

were performed with the cleaning/disinfecting products **Topactive 200, Topactive 500, P3-Topax 66, Topactive OKTO, P3-Topax 990** and deionized water used as reference.

The material compatibility of the tested

- **Control head type 8682**

can be evaluated as resistant to the Ecolab products used in the test under the application conditions mentioned overleaf.

Monheim am Rhein, August 10th 2026

Ecolab Deutschland GmbH
Ecolab-Allee 1
D-40789 Monheim am Rhein

ABD 1000758147 ML Version: - Status: RL (released | freigegeben) printed: 01.09.2026

ECOLAB

This certificate is based on:

- Documented test procedures (Test Method: F&E No. 40-1 Rev. 5) according to material resistance
- Defined product descriptions
- Standardized cleaning plan

Test Procedure
Ecolab Test Method F&E Nr. 40-1

Test Material:
- Test Report TBA-Ecolab_Typ 8682

Test Method:
- Complete immersion in solutions/liquid

Test Period:
- 28 days

Temperature:
- Room temperature (constant)

Analysis:
- Visual assessment
- Comparison with zero value (demineralized water)
- Photo documentation

Product Specifications

Topactive 200
Alkaline foam cleaning agent for the food and beverage industry

Topactive 500
Acid foam cleaning agent for the food and beverage industry

P3-Topax 66
Alkaline foam cleaner/disinfectant with available chlorine for the food and beverage industry

Topactive OKTO
Acid foaming disinfectant based on peracetic acid/hydrogen peroxide for the food and beverage industry

P3-Topax 990
Mild-alkaline sanitizer for the food and beverage industry

Cleaning Plan for the Food and Beverage Industry*

Rinsing with water 40 – 50 °C
Rinsing with low pressure. Rinsing from top to bottom in the direction of the drains. Cleaning of the drains



Foaming from bottom to top

alkaline:	Topactive 200 or P3-topax 66	2 – 5 % daily
acid:	Topactive 500	2 – 5 % on demand
temperature:	from cold up to 50 °C	
contact time:	approx. 15 min are recommended	

Intermediate rinsing with water 40 – 50 °C
Rinsing from top to bottom with low pressure



Foam disinfection

Peracids:	Topactive OKTO	1 – 3 %, 10 - 30 min
Alternatively, neutral	P3-topax 990	1 – 3 %, 15 - 60 min
temperature:	from cold up to 50 °C	

Final rinse with water 40 – 50 °C
Rinse from top to bottom with potable water after disinfection!

*The final step of a cleaning regime is always a thorough water rinse!

ABD 1000758147 ML Version: - Status: RL (released | freigegeben) printed: 01.09.2026