



Pneumatic cylinder in plastic according to ISO

- Corrosion-resistant
- Also suitable for aggressive environments
- Lightweight
- Optionally with foodstuffs approval
- Optionally in completely metal-free design



Product variants described in the data sheet may differ from the product presentation and description.

Type description

Single-acting (Type 0045) and double-acting (Type 0044) pneumatic cylinders according to ISO 6432 (Ø 12...25 mm) without end position damping and according to ISO 15552 (Ø 32...50 mm) with end position damping with piston rod nut.

Table of contents



1. General technical data	3
2. Circuit functions	3
3. Dimensions	4
3.1. DN 12...DN 25	4
3.2. DN 32...DN 50	4
4. Performance specifications	5
4.1. Force chart.....	5
Type 0045 single-acting, without end position cushioning (ISO 6432).....	5
Type 0044 double-acting, without end position cushioning (ISO 6432).....	5
Type 0044 double-acting, with end position cushioning (ISO 15552).....	5
5. Ordering information	5
5.1. Bürkert eShop – Easy ordering and quick delivery.....	5
5.2. Bürkert product filter.....	6
5.3. Ordering chart cylinders	6
Type 0045 single-acting, without end position cushioning (ISO 6432).....	6
Type 0044 double-acting, without end position cushioning (ISO 6432).....	6
Type 0044 double-acting, with end position cushioning (ISO 15552).....	7
5.4. Ordering chart accessories.....	7
Bearing support	7
Foot fastener.....	7
Mounting and piston rod nut set.....	8
Fork head according to DIN 71 752.....	8
Fork fastener.....	8
End support for Fork fastener.....	8

1. General technical data

Product properties	
Dimensions	Detailed information can be found in chapter "3. Dimensions" on page 4.
Material	
Cylinder tube	PA6 und PA12, both fibreglass reinforced (optional PP Ø 32...50 mm)
Piston rod	Stainless steel 1.4401
Solenoid piston	On request
Seal	NBR with PA6 (optional FKM), P5600 with PA12
Performance data	
Pressure range	1...10 bar ¹⁾
Medium data	
Operating medium	Lubricated or non-lubricated, filtered compressed air
Medium temperature	-20 °C...+70 °C
Approvals und Certificates	
Approvals	FDA, EU-Directive 2002/72/EG for PA12
Environment and installation	
Installation position	As required
Ambient temperature	-20 °C...+70 °C

1.) Measured as overpressure to the atmospheric pressure

2. Circuit functions


Circuit function	Description
	Single-acting: air - spring
	Double-acting: air - air

3. Dimensions

3.1. DN 12...DN 25

Note:

- Dimensions in mm
- Cylinder with piston diameter 12...25 according to ISO 6432 (CETOP) Rp 52 P




Piston diameter [mm]	D1	D2	D3	D4	D6	L1	L2	L3	L4	L5	B1	B2
12	M16×1.5	M6	6	18	M5	75	38	9	17	15	12	17
16	M16×1.5	M6	6	22	M5	82	38	9	17	15	12	17
20	M22×1.5	M8	8	26	G 1/8	95	44	12	20	18	16	22
25	M22×1.5	M10×1.25	8	31	G 1/8	104	50	12	22	20	16	24

3.2. DN 32...DN 50

Note:

- Dimensions in mm
- Cylinder with piston diameter 32...50 mm according to ISO 6431



Piston diameter [mm]	D1	D2	D3	D4	D5	L	M	N	O	P	A	B	R	S
32	30	M10×1.25	4.5	12	40	94	120	G 1/8	9	22	47	32.5	5.5	M5
40	34	M12×1.25	6	16	48	105	135	G 1/4	11	24	57	38	6.5	M6
50	40	M16×1.5	6	20	58	106	143	G 1/4	13	32	68	46.5	9	M8

4. Performance specifications

4.1. Force chart

Type 0045 single-acting, without end position cushioning (ISO 6432)

Piston diameter [mm]	Extension force at operating pressure					Min. retraction force ^{1.)}	
	2 bar [N]	4 bar [N]	6 bar [N]	8 bar [N]	10 bar [N]	Stroke 25 mm [N]	Stroke 50 mm [N]
12	7	24.5	46.5	69.5	92.5	8.5	6.5
16	13	53	93	133	173	10	7
20	24	87	150	213	276	13.5	10
25	43	141	239	337	435	18	15

1.) Tensile force at retracted piston rod

Type 0044 double-acting, without end position cushioning (ISO 6432)

Piston diameter [mm]	Extension force at operating pressure					Min. retraction force [N] in % of extension force	
	2 bar [N]	4 bar [N]	6 bar [N]	8 bar [N]	10 bar [N]	[%]	
12	16	39	61	84	107	75	
16	30	70	110	150	190	85	
20	46	109	172	235	298	84	
25	73	171	269	367	465	84	

Type 0044 double-acting, with end position cushioning (ISO 15552)

Piston diameter [mm]	Extension force at operating pressure					Min. retraction force [N] in % of extension force	
	2 bar [N]	4 bar [N]	6 bar [N]	8 bar [N]	10 bar [N]	[%]	
32	145	290	430	580	729	86	
40	230	450	680	900	1130	84	
50	350	710	1060	1410	1770	84	

5. Ordering information

5.1. Bürkert eShop – Easy ordering and quick delivery



Bürkert eShop – Easy ordering and fast delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

5.2. Bürkert product filter



Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

5.3. Ordering chart cylinders

Type 0045 single-acting, without end position cushioning (ISO 6432)

Note:

Further versions on request

Piston diameter [mm]	Stroke [mm]	Article no. version PA6	Article no. version PA12 FDA
012	25	074440	773171
	50	074805	773172
016	25	074868	773173
	50	074642	773174
020	25	074265	773175
	50	074181	773176
025	25	074580	773177
	50	074287	773178

Type 0044 double-acting, without end position cushioning (ISO 6432)

Note:

Further versions on request

Piston diameter [mm]	Stroke [mm]	Article no. version PA6	Article no. version PA12 FDA
012	25	073049	773179
	50	073211	773180
	80	072820	773181
	100	074130	773182
016	25	073204	773183
	50	072876	773184
	80	072835	773185
	100	073084	773186
020	25	072833	773187
	50	072787	773188
	80	072905	773189
	100	072808	773190
025	25	072832	773191
	50	072829	773192
	80	072803	773193
	100	072854	773194

Type 0044 double-acting, with end position cushioning (ISO 15552)

Note:

Further versions on request

Piston diameter [mm]	Stroke [mm]	Article no. version PA6	Article no. version PA12 FDA
032	50	075748	773195
	100	075219	773196
	150	075756	773197
	200	075220	773198
	300	075221	773199
040	50	075758	773200
	100	075222	773201
	150	075976	773202
	200	075759	773203
	300	076228	773204
050	50	075483	773205
	100	075225	773206
	150	075382	773207
	200	075226	773208
	300	773210	773209

5.4. Ordering chart accessories

Bearing support

Note:

For cylinder DN 12...DN 25, ISO 6432

Dimensions	Piston Ø	L	A	H	B	b	l	a	d1	d2	d6	Article no. plastic
	12/16	32	24	24	22	12	20	4	5.4	10	6	192373
	20/25	42	32	28	30.5	16	24	5	6.4	11	8	192374

Foot fastener

Note:

Consists of an angle bracket and 2 fastening screws

Dimensions	Piston Ø	A	B	C	D	G	H	J	R	S	Article no. steel	Article no. stainless steel
	12/16	16	5.5	32	40	14	20	20	13.4	4	780754	192380
	20/25	22	6.6	40	54	17	25	25	18	5	780755	192381

Mounting and piston rod nut set

Note:

Each consists of a fastening nut and a piston rod nut

Dimensions	Piston Ø	Fastening nut			Piston rod nut			Article no. steel	Article no. stainless steel
		A	B	C	A	B	C		
	12/16	M16 x 1.5	22	5	M6	10	3	780766	192385
	20	M22 x 1.5	27	8	M8 x 1.25	13	4	780768	192386
	25	M22 x 1.5	27	8	M10 x 1.25	17	6	780769	192387

Fork head according to DIN 71 752

Dimensions	Piston Ø	q	r	s	t	u	v	w	Article no. steel	Article no. stainless steel
	12/16	12	6	6	31	24	12	M6	192360	192361
	20	16	8	8	42	32	16	M8	192360	192363
	25/32	20	10	10	52	40	20	M10 x 1.25	192364	192365
	40	24	12	12	62	48	24	M12 x 1.25	192366	192367
	50	32	16	16	83	64	32	M16 x 1.5	192368	192369

Fork fastener

Dimensions	Piston Ø	F	J	K	R	V	W	Article no. cast aluminium
	32	22	10	26	45	15	46	192370
	40	25	12	28	52	17	56	192371
	50	27	12	32	60	17	66	192372

End support for Fork fastener

Dimensions	Piston Ø	S H1	T±0.2	U±0.15	V±0.1	W	XH13	Y	Article no. cast aluminium
	32	10	30	32.5	25.8	45	5.5	11	192375
	40	12	36	38	27.8	56	6.6	14	192376
	50	12	45	46.5	31.8	66	9	18	192377

DTS 1000268330 EN Version: H Status: RL (released | freigegeben | valide) printed: 16.11.2021

Bürkert – Close to You

For up-to-date addresses
please visit us at
www.burkert.com

DTS 1000268330 EN Version: H Status: RL (released | freigegeben | validé) printed: 16.11.2021

