



## Pneumatically operated 3/2-way seat valve ELEMENT for decentralized automation

- For mixing or distributing of mediums
- Decentralized automation with control head
- Flow optimized body in stainless steel
- Long service life and maintenance-free operation
- Control Head is connected w/o external tubing

Product variants described in the data sheet may differ from the product presentation and description.

### Can be combined with

	<b>Type 8695</b> ▶ Control head for decentralised automation of ELEMENT process valves
	<b>Type 8691</b> ▶ Control head for decentralised automation of ELEMENT process valves
	<b>Type 8690</b> ▶ Pneumatic control unit for decentralised automation of process valves ELEMENT
	<b>Type 8697</b> ▶ Pneumatic control unit for decentralised automation of process valves ELEMENT
	<b>Type 8801</b> ▶ ELEMENT on/off valve systems with decentralised automation – overview
	<b>Type 8840</b> ▶ Modular process valve cluster – distributor and collector

### Type description

The Bürkert 3/2-way seat valve, Type 2106, consists of a pneumatically operated ELEMENT actuator and a 3-way stainless steel valve body. Interchanging of pressure and service ports enables different fluidic circuit functions, such as the mixing or distributing of mediums. The flow-optimized valve body of Type 2106 allows excellent flow rates. The tried and tested self-adjusting gland secures a high level of tightness and thus ensures reliable operation over years. The design of the 3/2-way valve, Type 2106, offers all the advantages of a modern, decentralized automation: The directly connected control head and actuator provide a compact and smooth design, integrated pneumatic lines, protection class IP65/67, NEMA Type 4X, and a high chemical resistance. An optionally integrated fieldbus interface through to an explosion-proof automation units are further advantages of the 3-way shut-off valve. For the user, the compact Type 2106 is thus often an economical alternative to two single valves.

## Table of contents





<b>1. General technical data</b>	<b>3</b>
<hr/>	
<b>2. Control functions</b>	<b>4</b>
2.1. Control function .....	4
2.2. Pin assignment for fluidic circuit functions C, D, E and F.....	4
<hr/>	
<b>3. Approvals and conformities</b>	<b>5</b>
3.1. General notes.....	5
3.2. Conformity .....	5
3.3. Standards.....	5
3.4. Explosion protection .....	5
3.5. Drinking water .....	5
3.6. Foods and beverages/Hygiene .....	6
3.7. Others .....	6
Oxygen.....	6
Fuel gases.....	6
<hr/>	
<b>4. Materials</b>	<b>7</b>
4.1. Bürkert resistApp .....	7
4.2. Material specifications .....	7
<hr/>	
<b>5. Dimensions</b>	<b>8</b>
<hr/>	
<b>6. Performance specifications</b>	<b>9</b>
6.1. Pilot pressure diagram .....	9
<hr/>	
<b>7. Product accessories</b>	<b>10</b>
<hr/>	
<b>8. Networking and combination with other Bürkert products</b>	<b>11</b>
<hr/>	
<b>9. Ordering information</b>	<b>12</b>
9.1. Bürkert eShop.....	12
9.2. Bürkert product filter.....	12
9.3. Bürkert Product Enquiry Form .....	12
9.4. Ordering chart.....	13

## 1. General technical data

<b>Product properties</b>	
Dimensions	Further information can be found in chapter <b>"5. Dimensions"</b> on page 8.
<b>Material</b>	
Body	Cast stainless steel 316L
Actuator	PPS
Seal	PTFE
Cover	Stainless steel 1.4561 (316Ti)
Spindle packing	PTFE seal with spring compensation
Nominal diameter (port connection)	DN 15...DN 50
<b>Performance data</b>	
Nominal pressure	PN 16 (body)
Pilot pressure	Max. 10 bar(g), actuator size 130 mm, 7 bar(g)
<b>Medium data</b>	
Medium	Steam, water, neutral gases, alcohols, oils, fuels, hydraulic fluids, salt solutions, alkalis, organic solvents, oxygen and fuel gases of families I, II and III in accordance with the Gas Appliances Regulation (EU) 2016/426
Medium temperature	-10...+185 °C
Viscosity	Max. 600 mm <sup>2</sup> /s
Control medium	Air, neutral gases
<b>Process/Port connection &amp; communication</b>	
<b>Port connection</b>	
Threaded connection	G (DIN ISO 228 -1) NPT (ASME B1.20.1) (RC on request)
<b>Pilot air port</b>	Push-in connector (external Ø 6 mm or ¼") or thread G ⅛" (on request)
<b>Approvals and conformities</b>	
Further information can be found in chapter <b>"3. Approvals and conformities"</b> on page 5.	
Material certificate	2.2, 3.1
<b>Environment and installation</b>	
Ambient temperature	-10...+60 °C (integrated control unit) -10...+100 °C (push-in air ports)
Installation position	As required, preferably with actuator in upright position

## 2. Control functions


### 2.1. Control function

Symbol	Description
	<b>Control function C (CF C)</b> Pneumatically operated 3/2-way process valve When de-energised, pressure port 1 closed, service port 2 exhausted
	<b>Control function D (CF D)</b> Pneumatically operated 3/2-way process valve When de-energised, pressure port 3 connected to service port 2, exhaust port 1 closed
	<b>Control function E (CF E)</b> Pneumatically operated 3/2-way mixer valve When de-energised, pressure port 3 connected to service port 2, pressure port 1 closed
	<b>Control function F (CF F)</b> Pneumatically operated 3/2-way distributor valve When de-energised, pressure port 2 connected to service port 3, service port 1 closed

### 2.2. Pin assignment for fluidic circuit functions C, D, E and F

**Note:**

- Actuator with Control function A
- When de-energised port connection 1 is closed with spring



Fluidic circuit function	Connection		
	1	2	3
C	P	A	R
D	R	A	P
E	P1	A	P2
F	A	P	B

A, B Service ports  
P, P1, P2 Pressure ports  
R Exhaust port

### 3. Approvals and conformities

#### 3.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available versions can be supplied with the below mentioned approvals or conformities.

#### 3.2. Conformity



In accordance with the Declaration of Conformity, the product is compliant with the EU Directives. This includes the following directives:

- Pressure Equipment Directive 2014/68/EU
- Machinery Directive 2006/42/EG


#### 3.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

#### 3.4. Explosion protection


Approval	Description																								
 	<p><b>Optional: Explosion protection</b> As a category 2 device suitable for zone 1/21 and zone 2/22 (optional).</p> <p><b>ATEX:</b> EPS 18 ATEX 2 008 X II 2G Ex h IIC T4...T2 Gb II 2D Ex h IIIC T135 °C...T300 °C Db</p> <p><b>IECEx:</b> IECEx EPS 18.0007 X Ex h IIC T4...T2 Gb Ex h IIIC T135 °C...T300 °C Db</p> <table border="1"> <thead> <tr> <th>Temperature class</th> <th>T2</th> <th>T3</th> <th>T4</th> </tr> </thead> <tbody> <tr> <td>Permissible surface temperature</td> <td>+300 °C</td> <td>+200 °C</td> <td>+135 °C</td> </tr> <tr> <td>Ambient temperature</td> <td>-40...+80 °C</td> <td>-40...+80 °C</td> <td>-40...+80 °C</td> </tr> <tr> <td>Restrictions from the device</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Maximum medium temperature</td> <td>+230 °C</td> <td>+185 °C</td> <td>+125 °C</td> </tr> <tr> <td>Restrictions from the device</td> <td></td> <td></td> <td></td> </tr> </tbody> </table>	Temperature class	T2	T3	T4	Permissible surface temperature	+300 °C	+200 °C	+135 °C	Ambient temperature	-40...+80 °C	-40...+80 °C	-40...+80 °C	Restrictions from the device				Maximum medium temperature	+230 °C	+185 °C	+125 °C	Restrictions from the device			
Temperature class	T2	T3	T4																						
Permissible surface temperature	+300 °C	+200 °C	+135 °C																						
Ambient temperature	-40...+80 °C	-40...+80 °C	-40...+80 °C																						
Restrictions from the device																									
Maximum medium temperature	+230 °C	+185 °C	+125 °C																						
Restrictions from the device																									

#### 3.5. Drinking water

Conformity	Description
	<p><b>Suitable for use in drinking water applications</b> The materials comply with the assessment principles (UBA) for materials in contact with drinking water (TrinkwasserV).</p> <p><b>Stainless steel body</b> PF39: Suitable for products with medium temperature up to 85 °C (hot water)</p>


DTS 1000257617 EN Version: K Status: RL (released | freigegeben | validé) printed: 20.03.2024

**3.6. Foods and beverages/Hygiene**


Conformity	Description
FDA	<b>FDA – Code of Federal Regulations (valid for the variable code PL02)</b> All wetted materials are compliant with the Code of Federal Regulations published by the FDA (Food and Drug Administration, USA) according to the manufacturer’s declaration.
	<b>EC Regulation 1935/2004 of the European Parliament and of the Council (valid for the variable code PL01, PL02)</b> All wetted materials are compliant with EC Regulation 1935/2004/EC according to the manufacturer’s declaration.

**3.7. Others**

**Oxygen**

Conformity	Description
	<b>Optional: Suitability for oxygen (valid for the variable code NL02)</b> The products are suitable for use with gaseous oxygen, according to the manufacturer’s declaration.


**Fuel gases**

Conformity	Description
	<b>Fuel gases (valid for the variable code PO19, PO20)</b> The products comply with: <ul style="list-style-type: none"> <li>• Regulation (EU) 2016/426 – Appliances burning gaseous fuels and</li> <li>• DVGW DIN EN 161 (Automatic shut-off valves for gas burners and gas appliances) and</li> <li>• DIN EN 16678, Class A or Class D (Safety and control devices for gas burners and gas burning appliances – Automatic shut-off valves for operating pressure of above 500 kPa up to and including 6 300 kPa)</li> </ul>

DTS 1000257617 EN Version: K Status: RL (released | freigegeben | validé) printed: 20.03.2024

## 4. Materials

### 4.1. Bürkert resistApp



#### Bürkert resistApp – Chemical resistance chart


You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

[Start chemical resistance check](#)

### 4.2. Material specifications

**Note:**

The lubricants for packing gland and actuator are classified according to NSF H1.




No.	Element	Material
1	Transparent cap	Polysulfone PSU
2	Pilot air ports	Push-in connector PP (standard) Thread G 1/8" stainless steel 1.4305 (on request)
3	Actuator	PPS
4	Case	Stainless steel 1.4561 (316Ti)
5	Piston seal	FKM
6	Spring	Stainless steel 1.4310
7	Tube	Stainless steel 1.4401 (316)/1.4404 (316L)
8	Spindle seal	PTFE
9	Spindle	Stainless steel 1.4401 (316)/1.4404 (316L)
10	Spindle guide	PEEK
11	Valve body	Stainless steel 1.4404 (316L)
12	Body closer	Stainless steel 1.4404 (316L)
13	Seal	PTFE
14	Seat nipple	Stainless steel 1.4404 (316L)

## 5. Dimensions

**Note:**

Dimensions in mm



DN	Actuator size Ø	Ø A	B	C	R	H	All threaded bodies					G			NPT			RC		
							A1	T	G 2	SW1	SW2	G 1	C1/ C2	LTA	G 1	C1/ C2	LTA	G 1	C1/ C2	LTA
15	50 (D)	64.5	6.0	19.8	19.8	202.4	85	58.3	M40×1.5	32	30	1/2	14	GM84	1/2	13.7	NM84	1/2	13.2	RC84
	70 (M)	91	8.5	23.3	30.5	202.4	85	58.3	M40×1.5	32	30	1/2	14	GM84	1/2	13.7	NM84	1/2	13.2	RC84
20	50 (D)	64.5	6.0	19.8	19.8	202.4	85	58.3	M40×1.5	32	30	3/4	16	GM85	3/4	14.0	NM85	3/4	14.5	RC85
	70 (M)	91	8.5	23.3	30.5	202.4	85	58.3	M40×1.5	32	30	3/4	16	GM85	3/4	14.0	NM85	3/4	14.5	RC85
25	50 (D)	64.5	6.0	19.8	19.8	227.4	105	54.9	M50×2	41	41	1	18	GM86	1	16.8	NM86	1	16.8	RC86
	70 (M)	90	8.5	23.3	30.5	227.4	105	54.9	M50×2	41	41	1	18	GM86	1	16.8	NM86	1	16.8	RC86
32	70 (M)	91	8.5	23.3	30.5	234.7	130	67.8	M70×2	55	55	1 1/4	20	GM87	1 1/4	17.3	NM87	1 1/4	19.1	RC87
	90 (N)	120				294.4	130	78.1	M70×2	55	55	1 1/4	20	GM87	1 1/4	17.3	NM87	1 1/4	19.1	RC87
	130 (P)	159				346.7	130	68.0	M70×2	55	55	1 1/4	20	GM87	1 1/4	17.3	NM87	1 1/4	19.1	RC87
40	70 (M)	91	8.5	23.3	30.5	234.7	130	68.0	M70×2	55	55	1 1/2	22	GM88	1 1/2	17.3	NM88	1 1/2	19.1	RC88
	90 (N)	120				294.4	130	68.3	M70×2	55	55	1 1/2	22	GM88	1 1/2	17.3	NM88	1 1/2	19.1	RC88
	130 (P)	159				346.7	130	68.0	M70×2	55	55	1 1/2	22	GM88	1 1/2	17.3	NM88	1 1/2	19.1	RC88
50	70 (M)	91	8.5	23.3	30.5	245.5	150	72.0	M84×2	70	70	2	24	GM89	2	17.6	NM89	2	23.4	RC89
	90 (N)	120				310.7	150	72.0	M84×2	70	70	2	24	GM89	2	17.6	NM89	2	23.4	RC89
	130 (P)	159				353.7	150	72.0	M84×2	70	70	2	24	GM89	2	17.6	NM89	2	23.4	RC89

DTS 1000257617 EN Version: K Status: RL (released | freigegeben | valide) printed: 20.03.2024



## 6. Performance specifications

### 6.1. Pilot pressure diagram


**Note:**

Legend for actuator size D, M, N, P, see “5. Dimensions” on page 8

**Actuator size Ø 50 mm**

Maximum control pressure 10 bar(g)


Actuator size Ø 50



**Actuator size Ø 70 mm**

Maximum control pressure 10 bar(g)


Actuator size Ø 70



**Actuator size Ø 90 mm**

Maximum control pressure 10 bar(g)

Actuator size Ø 90



**Actuator size Ø 130 mm**

Maximum control pressure 7 bar(g)

Actuator size Ø 130



## 7. Product accessories

<b>Electrical position indicator</b>	
<b>Control head</b>	
<b>Type 8691 ▶ Actuator size Ø 70 mm</b>	
	<p>The control heads Type 8691 and Type 8695 are optimised for integrated mounting on process valves of the 21XX series. The valve position is detected without contact via an analogue sensor element. The sensor element automatically detects and stores the valve end positions during commissioning using the teach function. The integrated pilot valve controls single-acting or double-acting actuators. The valve switching status is indicated by coloured high-performance LEDs.</p> <p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Status indication via coloured high-performance LEDs</li> <li>• Wear-free inductive position sensor</li> <li>• Pilot valve with manual override</li> <li>• Teach function for automatic recognition of valve end positions</li> <li>• Hygienic stainless steel design</li> <li>• Easy-to-clean, chemically resistant housing according to IP65/67, 4X rating</li> <li>• AS-Interface, IO-Link, Bürkert system bus (büS)</li> </ul>
<b>Type 8695 ▶ Actuator size Ø 50 mm</b>	
	<p><b>Customer benefits</b></p> <ul style="list-style-type: none"> <li>• Simple and safe commissioning using the teach function</li> <li>• Easy process monitoring and fault detection through visible coloured high-performance LEDs</li> <li>• High degree of system availability due to increased actuator service life by means of spring chamber ventilation</li> <li>• Minimal space requirement in plant piping for more flexibility in plant design</li> </ul>
<b>Pneumatic control unit/position feedback</b>	
<b>Type 8690 ▶ Actuator size Ø 70 mm</b>	
	<p>The pneumatic control units Type 8690 and 8697 are optimised for integrated mounting on process valves of the 21XX series. Mechanical or inductive limit switches detect the valve position. The integrated pilot valve controls single-acting or double-acting (Type 8690) actuators.</p> <p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Optical position indicator</li> <li>• Mechanical or inductive proximity switches for end position detection</li> <li>• Pilot valve with manual override</li> <li>• Compact design</li> <li>• Easy-to-clean, chemically resistant housing according to IP65/67, 4X rating</li> <li>• Optionally intrinsically safe design according to ATEX/IECEx</li> </ul>
<b>Type 8697 ▶ Actuator size Ø 50 mm</b>	
	<p><b>Customer benefits</b></p> <ul style="list-style-type: none"> <li>• Simple and safe commissioning using the teach function (Type 8697)</li> <li>• Signal reliability due to the automatic adjustment of the limit switches</li> <li>• Minimal space requirement in plant piping for more flexibility in plant design</li> </ul>

DTS 1000257617 EN Version: K Status: RL (released | freigegeben | valide) printed: 20.03.2024


## 8. Networking and combination with other Bürkert products

The **seat valve Type 2106** can be combined with the **position feedback Type 8690/8697** and the **control head Type 8691/8695** to valve system **On/Off ELEMENT Type 8801-GE**.

**Note:**

- For the configuration of further valve systems use the **Product Enquiry Form** (see **"9.3. Bürkert Product Enquiry Form" on page 12**).
- You order two components and receive a completely assembled and tested valve.

**Example with welded connection**



DTS 1000257617 EN Version: K Status: RL (released | freigegeben | validé) printed: 20.03.2024

## 9. Ordering information

### 9.1. Bürkert eShop



#### Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

### 9.2. Bürkert product filter



#### Bürkert product filter – Get quickly to the right product


You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

### 9.3. Bürkert Product Enquiry Form

**Note:**

Please see our Product Enquiry Form for a full explanation of our specification key.



#### Bürkert Product Enquiry Form – Your enquiry quickly and compactly

Would you like to make a specific product enquiry based on your technical requirements? Use our Product Enquiry Form for this purpose. There you will find all the relevant information for your Bürkert contact. This will enable us to provide you with the best possible advice.

[Fill out the form now](#)

DTS 1000257617 EN Version: K Status: RL (released | freigegeben | validé) printed: 20.03.2024

### 9.4. Ordering chart

**Note:**

- Valves in closed position, pressure port 1 closed
- Other versions are available on request.

Control function	Nominal diameter (port connection)	Port connection	Actuator size Ø	K <sub>v</sub> value water		Pilot pressure min.	Operating pressure max. 180 °C		Weight	Article no.
				1 → 2	2 → 3		1 → 2	2 → 3 2 → 1		
				[m <sup>3</sup> /h]	[m <sup>3</sup> /h]		[bar(g)]	[bar(g)]		
DN	NPS	[mm]	[m <sup>3</sup> /h]	[m <sup>3</sup> /h]	[bar(g)]	[bar(g)]	[bar(g)]	[kg]		
<b>DIN ISO 228 - 1</b>										
<b>A (CF A)</b> see control functions <sup>1)2)</sup>	15	G ½	50 (D)	7	4.5	5.5	16	16	1.5	282698
			70 (M)	7	4.5	4.5	16	16	2.2	282701
	20	G ¾	50 (D)	9	6.2	5.5	16	16	1.4	282702
			70 (M)	9	6.2	4.5	16	16	2.1	282704
	25	G 1	50 (D)	17	11	5.5	9	11	1.9	282705
			70 (M)	17	11	4.5	16	16	2.6	282706
	32	G 1¼	70 (M)	32	21	4.5	8	11	3.9	282707
			90 (N)	32	21	5.1	11	16	5.4	282708
	40	G 1½	70 (M)	35	24	4.5	7	11	3.7	282711
			90 (N)	35	24	5.1	12	16	5.2	282712
	50	G 2	90 (N)	51	35	5.1	9	8	7.3	282715
			130 (P)	51	35	4.9	16	16	10.4	282716
<b>ANSI B 1.20.1</b>										
<b>A (CF A)</b> see control functions <sup>1)2)</sup>	15	NPT ½	50 (D)	7	4.5	5.5	16	16	1.5	292478
			70 (M)	7	4.5	4.5	16	16	2.2	292531
	20	NPT ¾	50 (D)	9	6.2	5.5	16	16	1.4	292532
			70 (M)	9	6.2	4.5	16	16	2.1	292533
	25	NPT 1	50 (D)	17	11	5.5	9	11	1.9	292534
			70 (M)	17	11	4.5	16	16	2.6	292535
	32	NPT 1¼	70 (M)	32	21	4.5	8	11	3.9	292536
			90 (N)	32	21	5.1	11	16	5.4	292537
	40	NPT 1½	70 (M)	35	24	4.5	7	11	3.7	292538
			90 (N)	35	24	5.1	12	16	5.2	292539
	50	NPT 2	90 (N)	51	35	5.1	9	8	7.3	292540
			130 (P)	51	35	4.9	16	16	10.4	292541

1.) Further information can be found in chapter "2. Control functions" on page 4.  
 2.) See "2.2. Pin assignment for fluidic circuit functions C, D, E and F" on page 4

**Further versions on request**

**Process connection**  
 RC thread

DTS 1000257617 EN Version: K Status: RL (released | freigegeben | valide) printed: 20.03.2024