Cable plug, form A according to DIN EN 175301 - 803

- Variants with protective circuits with or without LED
- Simple connection and safe contacting
- Approval UR and CSA (depending on variant)
- Available with and without cable

Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

Type 6013
Plunger valve 2/2-way direct-acting

Type 0330
Direct-acting 2/2 or 3/2-way pivoted armature valve

Type 6213
Servo-assisted 2/2-way diaphragm valve

Type description

Plug for the connection of electrical components according to DIN EN 175301 - 803 Form A. Type 2518 offers easy connection of lines as well as reliable contacting. A wide range of protective circuits with or without LED are available.

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

© Christian Bürkert GmbH & Co. KG, Subject to alteration

Visit product website

Table of contents

1. General technical data 3

2. Approvals and conformities 4

2.1. General notes ... 4
2.2. Conformity ... 4
2.3. Standards ... 4
2.4. North America (USA/Canada) ... 4
2.5. Others ... 4
Fire protection on railway vehicles ... 4

3. Materials 5

3.1. Bürkert resistApp ... 5
3.2. Variant with UR approval, field attachable ... 5
3.3. Variant without UR approval, field attachable ... 6
3.4. Variant with cable ... 6
3.5. Variant with M12 connection ... 7

4. Dimensions 7

4.1. Cable plug without cable, field attachable ... 7
4.2. Cable plug with cable, moulded ... 8
4.3. Cable plug with M12 connection ... 9

5. Product connections 10

5.1. Electrical connections ... 10
Pin assignment plug M12, 5-pin ... 10

6. Performance specifications 10

6.1. Derating diagram ... 10
Variant without wiring, 2-pin and 3-pin , field attachable ... 10
Variant without wiring, 2-pin and 3-pin, moulded ... 10
Variant with LED or varistor or LED and varistor, field attachable ... 11
Variant with LED or varistor or LED and varistor, moulded ... 11
Variant with bridge rectifier and varistor, with and without LED, field attachable ... 11
Variant with bridge rectifier and varistor, with and without LED, moulded ... 12
Variant with pin protection diode and free-wheeling diode, with and without LED, field attachable ... 12
Variant with pin protection diode and free-wheeling diode, with and without LED, moulded ... 12

7. Ordering information 13

7.1. Bürkert eShop ... 13
7.2. Bürkert product filter ... 13
7.3. Ordering chart ... 13
Cable plug without cable, field attachable ... 13
Cable plug with cable, moulded ... 14
Cable plug with M12 connection ... 15
7.4. Ordering chart accessories ... 16
Seal kit ... 16

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

1. General technical data

Product properties	Field attachable cable plug (without cable)	Moulded cable plug (with cable, M12 connection)
Dimensions	Further information can be found in chapter "4. Dimensions" on page 7.	
Material		
Seal	NBR (Standard) EPDM and silicone can be ordered as a set	TPU, moulded
Body	Polyamide	–
Cable	–	PUR (M12 without cable)
Contacts	Brass	Brass
Operating display	Yellow LED, if available	Yellow LED, if available
Cable outlet	Can be rotated through 4×90°	On or opposite the protective conductor
Cable gland	M16×1.5	–
Number of pins	See "7.3. Ordering chart" on page 13	See "7.3. Ordering chart" on page 13
Transition resistance	≤ 10 mΩ Standard	≤ 10 mΩ Standard
Electrical data		
Nominal voltage	Depends on the variant Further information can be found in chapter "7. Ordering information" on page 13.	Depends on the variant Further information can be found in chapter "7. Ordering information" on page 13.
Medium data		
Continuous limit temperature [1.)]		
Cable plug	- 40 °C...+ 125 °C	- 25 °C...+ 85 °C (M12: - 25 °C...+ 80 °C)
Seal NBR	- 30 °C...+ 90 °C	–
Seal EPDM	- 40 °C...+ 125 °C	–
Seal silicone	- 55 °C...+ 140 °C	–
Product connections		
Suitable cable	Ø 6.0...Ø 8.0 mm with UR approval Ø 4.5...Ø 10.0 mm without UR approval	–
Connection type	Screw terminal	–
Connection cross-section	0.25 mm^2...1.5 mm^2	0.75 mm^2 (M12 without cable)
Electrical connection	According to DIN EN 175301 - 803 form A	According to DIN EN 175301 - 803 form A
Plug cycles	Max. 50	Max. 50
Approvals and conformities		
Degree of protection	IP65 / IP67 (see "7.3. Ordering chart" on page 13)	IP65 / IP67
North America (USA/Canada)	Further information can be found in chapter "2.4. North America (USA/Canada)" on page 4.	
Others	Further information can be found in chapter "2.5. Others" on page 4.	

1.) Observe derating, see "6.1. Derating diagram" on page 10.

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

2. Approvals and conformities

2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available variants can be supplied with the below mentioned approvals or conformities.

2.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

2.4. North America (USA/Canada)

Approval	Description
c UL us	**Optional: UL Recognized for the USA and Canada (E315587)** The product variant without cable is UL Recognized for the USA and Canada according to: • UL2238 (Cable assemblies and fittings for industrial control and signal distribution) • CAN/CSA-C22.2 No. 182.3 - 16

2.5. Others

Fire protection on railway vehicles

Approval	Description
DIN EN 45545	**Optional: Fire protection on railway vehicles in accordance with DIN EN 45545 applicable parts 2 and 5: requirements for fire behaviour of materials and components** The products comply with the fire protection requirements in accordance with applicable parts 2 and 5 of DIN EN 45545 for use in the interior of railway vehicles for operating classes 1 - 3 (OC1 - 3) in conjunction with hazard levels 1 - 2 (HL1 - 2) in accordance with the manufacturer's declaration.

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

3. Materials

3.1. Bürkert resistApp



Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

Start chemical resistance check

3.2. Variant with UR approval, field attachable

Available wiring:

- Without wiring
- With varistor
- With bridging rectifier and varistor
- With pin protection diode and free wheeling diode



No.	Element	Material
1	Central screw	Stainless steel
2	Pressure screw	Polyamide
3	Clamping ring	–
4	Seal	–
5	Cover	Polyamide
6	Contact holder	Polyamide
7	Seal	NBR

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

3.3. Variant without UR approval, field attachable

Available wiring:

- Without wiring (only in packaging units of 200 pieces see "Cable plug without cable, field attachable" on page 13)
- With LED
- With LED and varistor
- With LED, bridging rectifier and varistor
- With pin protection diode, free wheeling diode and LED



No.	Element	Material
1	Central screw	Stainless steel
2	Pressure screw	Polyamide
3	Pressure ring	–
4	Seal	–
5	Cover	Polyamide
6	Contact holder	Polyamide
7	Seal	NBR

3.4. Variant with cable

Available wiring:

- Without wiring
- With LED
- With varistor
- With bridging rectifier and varistor
- With LED and varistor
- With LED, bridging rectifier and varistor
- With pin protection diode and free wheeling diode
- With pin protection diode, free wheeling diode and LED

Note:
The variants with cables do not possess a UR approval.



No.	Element	Material
1	Contact holder	PBT GF
2	Central screw	V2 A
3	Cable	PUR
4	Seal moulded on	TPU

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

3.5. Variant with M12 connection

Available wiring:

- With LED and varistor

Note:

The variants with M12 connection do not possess a UR approval.



No.	Element	Material
1	Contact holder	PBT
2	M12 connection	CuZn, nickel-plated
3	Seal moulded on	TPU
4	Central screw	V2 A

4. Dimensions

4.1. Cable plug without cable, field attachable

Note:

Dimensions in mm



DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

4.2. Cable plug with cable, moulded

Note:
Dimensions in mm



Note on the length tolerances:

Cable length prefabricated part		Stripping length
L	**Tolerances of L**	**L1**
< 1 m	- 10/+ 20	60 ± 1
< 1...2 m	- 20/+ 50	60 ± 1
> 2...5 m	- 40/+ 70	60 ± 1
> 5...10 m	- 90/+ 120	60 ± 1
> 10 m	- 120/+ 140	60 ± 1

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

4.3. Cable plug with M12 connection

Note:
Dimensions in mm



DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

5. Product connections

5.1. Electrical connections

Pin assignment plug M12, 5-pin



Pin	Pin assignment
1	Not connected
2	Not connected
3	2
4	1
5	Grounding

6. Performance specifications

6.1. Derating diagram

Variant without wiring, 2-pin and 3-pin , field attachable

Derating DIN EN 60512-5-2



Variant without wiring, 2-pin and 3-pin, moulded

Derating DIN EN 60512-5-2



DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

Variant with LED or varistor or LED and varistor, field attachable

Derating DIN EN 60512-5-2



Variant with LED or varistor or LED and varistor, moulded

Derating DIN EN 60512-5-2



Variant with bridge rectifier and varistor, with and without LED, field attachable

Derating DIN EN 60512-5-2



DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

Variant with bridge rectifier and varistor, with and without LED, moulded

Derating DIN EN 60512-5-2



Variant with pin protection diode and free-wheeling diode, with and without LED, field attachable

Derating DIN EN 60512-5-2



Variant with pin protection diode and free-wheeling diode, with and without LED, moulded

Derating DIN EN 60512-5-2



DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

7. Ordering information

7.1. Bürkert eShop

Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

Order online now

7.2. Bürkert product filter

Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements?
Use the Bürkert product filter and find suitable articles for your application quickly and easily.

Try out our product filter

7.3. Ordering chart

Cable plug without cable, field attachable

Note:
The delivery is made in a polythene bag with stainless steel screw and NBR seal.

Circuit diagram	Operating voltage [V/Hz]	Rated voltage [V/Hz]	Continuous current [A]	Number of pins without cable	Degree of protection without cable	Article no.
Without circuit						
	230 V AC/DC 300 V AC/DC (UL)	250 V (VDE) 300 V (UL)	10 A (VDE, UL) 8 A (CSA)	2+PE	IP65/IP67	314802 [1.]
	230 V AC/DC	250 V	10 A (VDE)	2+PE	IP65	314803 [2.]
Without circuit, 3-pins, protective earth conductor						
	230 V AC/DC 300 V AC/DC (UL)	250 V (VDE) 300 V (UL)	10 A (VDE)	3+PE	IP65/IP67	315329 [1.]
With LED						
	24 V AC/DC	30 V	10 A	2+PE	IP65	314812
	120 V AC/DC	150 V	10 A	2+PE	IP65	315330
	230 V AC/DC	250 V	10 A	2+PE	IP65	315334
With Rectifier, LED and varistor						
	24 V AC/DC	30 V	1 A	2+PE	IP65	314816
	120 V AC/DC	150 V	1 A	2+PE	IP65	315338
	230 V AC/DC	250 V	1 A	2+PE	IP65	315342

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

Circuit diagram	Operating voltage [V/Hz]	Rated voltage [V/Hz]	Continuous current [A]	Number of pins without cable	Degree of protection without cable	Article no.
With LED and varistor						
	24 V AC/DC	30 V	10 A	2+PE	IP65	314820
	120 V AC/DC	150 V	10 A	2+PE	IP65	315346
	230 V AC/DC	250 V	10 A	2+PE	IP65	314825
With varistor						
	24 V AC/DC	30 V	10 A	2+PE	IP65/IP67	314826 1.)
	230 V AC/DC	250 V	10 A	2+PE	IP65/IP67	315353 1.)
With pin protection, free wheeling diode and LED						
	24 V DC	30 V	1 A	2+PE	IP65	315357
With pin protection and free wheeling diode						
	230 V DC	250 V	1 A	2+PE	IP65/IP67	314830 1.)
With rectifier and varistor						
	230 V AC/DC	250 V	1 A	2+PE	IP65/IP67	314839 4.)

1.) cURus approval E315587

2.) Only available in packaging units of 200 pieces and with galvanised steel screw and NBR seal

Cable plug with cable, moulded

Note:
The delivery is made in a polythene bag with stainless steel screw.

Circuit diagram	Operating voltage [V/Hz]	Rated voltage [V/Hz]	Continuous current [A]	Number of pins with cable	Degree of protection with cable	Article no.		
						With 1 m cable	With 3 m cable	With 5 m cable
Without circuit								
	230 V AC/DC	250 V AC/ DC	10 A	2 + 2PE	IP65/IP67	314806	314807	314808
Without circuit, 3-pins, protective earth conductor								
	230 V AC/DC	250 V AC/ DC	10 A	3+PE	IP65/IP67	314809	314810	314811
With LED								
	24 V AC/DC	30 V	10 A	2 + 2PE	IP65/IP67	314813	314814	314815
	120 V AC/DC	150 V	10 A	2 + 2PE	IP65/IP67	315331	315332	315333
	230 V AC/DC	250 V	10 A	2 + 2PE	IP65/IP67	315335	315336	315337

Circuit diagram	Operating voltage [V/Hz]	Rated voltage [V/Hz]	Continuous current [A]	Number of pins with cable	Degree of protection with cable	Article no. With 1 m cable	Article no. With 3 m cable	Article no. With 5 m cable
With Rectifier, LED and varistor								
	24 V AC/DC	30 V	1 A	2+PE	IP65/IP67	314817	314818	314819
	120 V AC/DC	150 V	1 A	2+PE	IP65/IP67	315339	315340	315341
	230 V AC/DC	250 V	1 A	2+PE	IP65/IP67	315343	315344	315345
With LED and varistor								
	24 V AC/DC	30 V	10 A	2 + 2PE	IP65/IP67	314821	314822	314824
	120 V AC/DC	150 V	10 A	2 + 2PE	IP65/IP67	315347	315348	315349
	230 V AC/DC	250 V	10 A	2 + 2PE	IP65/IP67	315350	315351	315352
With varistor								
	24 V AC/DC	30 V	10 A	2 + 2PE	IP65/IP67	314827	314828	314829
	230 V AC/DC	250 V	10 A	2 + 2PE	IP65/IP67	315354	315355	315356
With pin protection, free wheeling diode and LED								
	24 V DC	30 V	1 A	2 + 2PE	IP65/IP67	315358	314837	314838
With pin protection and free wheeling diode								
	230 V DC	250 V	1 A	2 + 2PE	IP65/IP67	314831	314832	314833
With rectifier and varistor								
	230 V AC/DC	250 V	1 A	2+PE	IP65/IP67	314840	314841	314842

Cable plug with M12 connection

Note:
The delivery is made in a polythene bag with stainless steel screw.

Circuit diagram	Operating voltage [V/Hz]	Rated voltage [V/Hz]	Continuous current [A]	Number of pins without cable	Degree of protection without cable	Article no.
With LED and varistor						
	24 V	32 V	4	2+PE	IP67	902801

Further variants on request

Material
Further seal materials on request

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

7.4. Ordering chart accessories

Seal kit

Note:
Please note that the screw set is only suitable for field attachable variants.

Description	Material	Packaging unit	Article no.
Seal kit SC02 - 2518 - 700	EPDM	50 pieces	356539
Seal kit SC02 - 2518 - 700	Silicone	50 pieces	356537
Seal kit SC02 - 2518 - 700	NBR	50 pieces	20005658
Screw set SC02 - 2518 - 700	Stainless steel	100 pieces	356540

DTS 1000386344 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026