



### Cable plug, form A according to DIN EN 175301 - 803

- Degree of protection IP65
- UL/UR approvals



Product variants described in the data sheet may differ from the product presentation and description.

#### Type description

Cable plug device key 2509 for connection of electrical components according to DIN EN 175301 - 803.

## Table of contents

<b>1. General technical data</b>	<b>3</b>
<b>2. Approvals and conformities</b>	<b>3</b>
2.1. General notes .....	3
2.2. Conformity .....	3
2.3. Standards .....	3
2.4. North America (USA/Canada) .....	4
<b>3. Dimensions</b>	<b>4</b>
<b>4. Ordering information</b>	<b>5</b>
4.1. Bürkert eShop .....	5
4.2. Bürkert product filter .....	5
4.3. Ordering chart .....	5

DTS 1000010988 EN Version: | Status: RL (released | freigegeben | validé) printed: 18.12.2024

## 1. General technical data

Product properties	
Dimensions	Further information can be found in chapter "3. Dimensions" on page 4.
Material	
Flat seal	NBR
Body	Polyamide
Contacts	Copper alloy, silver-plated
Cable outlet	Vertically to the plug bottom, insert can be rotated by 4 × 90°
Flying leads cross section	≤ 3 mm <sup>2</sup>
Number of pins	2-pin + protective conductor
Electrical data	
Maximum continuous current	6 A
Nominal voltage	0...250 V AC/DC
Process/Port connection & communication	
Connectable cable	Max. 6.5 mm
Connection type	Screw-type terminal
Electrical connection	According to DIN EN 175301 - 803 form A
Connection thread	NPT 1/2"
Approvals and conformities	
Flammability class (insert)	UL94 HB
Flammability class (body & cover)	UL94 V-0
Degree of protection	IP65 (NEMA 4)
North America (USA/Canada)	Further information can be found in chapter "2.4. North America (USA/Canada)" on page 4.
Environment and installation	
Ambient temperature	- 10 °C...+ 55 °C

## 2. Approvals and conformities

### 2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available versions can be supplied with the below mentioned approvals or conformities.

### 2.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

### 2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.


### 2.4. North America (USA/Canada)

Approval	Description
	<p><b>Optional: UL Listed for the USA and Canada</b></p> <p>The products are UL Listed for the USA and Canada according to:</p> <ul style="list-style-type: none"> <li>UL 2238 (ELECTRICAL EQUIPMENT FOR MEASUREMENT, CONTROL, AND LABORATORY USE – Part 1: General Requirements)</li> <li>CAN/CSA-C22.2 No. 182.3-1</li> </ul>
	<p><b>Optional: UL Recognized for the USA and Canada</b></p> <p>The products are UL Recognized for the USA and Canada according to:</p> <ul style="list-style-type: none"> <li>UL 2238 (ELECTRICAL EQUIPMENT FOR MEASUREMENT, CONTROL, AND LABORATORY USE – Part 1: General Requirements)</li> <li>CAN/CSA-C22.2 No. 182.3-1</li> </ul>

### 3. Dimensions


**Note:**

Dimensions in mm



## 4. Ordering information

### 4.1. Bürkert eShop




**Bürkert eShop – Easy ordering and quick delivery**

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

### 4.2. Bürkert product filter




**Bürkert product filter – Get quickly to the right product**

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

### 4.3. Ordering chart

Circuit diagram	Operating voltage [V/Hz]	Continuous current [A]	Article no.
<b>Without circuitry (Standard)</b>			
	0...250 V AC/DC	Max. 6 A	137943

DTS 1000010988 EN Version: | Status: RL (released | freigegeben | validé) printed: 18.12.2024