



## Direct-acting 2/2-way plunger valve up to 900 bar

- Hydrogen-resistant screwed valve body
- Function test with forming gas at nominal pressure
- Explosion-proof variant ATEX and IECEx
- Inspection holes for monitoring the process seal
- Normally Open (NO) variants on request

Product variants described in the data sheet may differ from the product presentation and description.

### Type description

The valve Type 6080 is a direct-acting plunger valve for hydrogen applications. The plunger guiding tube and stopper are screwed together to increase the pressure resistance in contact with hydrogen. Certified 3.1 materials suitable for hydrogen and carbon-coated magnetic steels are used. Each valve is subject to a functional test at maximum nominal pressure. The external leakage at nominal pressure is  $5 \times 10^{-5}$  mbar l/s. On request, the push-over coil can be provided as a Zone 1 or Category 2 explosion-proof variant.

## Table of contents

<b>1. General technical data</b>	<b>3</b>
<b>2. Circuit functions</b>	<b>4</b>
<b>3. Approvals and conformities</b>	<b>4</b>
3.1. General notes .....	4
3.2. Conformity .....	4
3.3. Standards .....	4
3.4. Explosion protection .....	4
<b>4. Materials</b>	<b>5</b>
4.1. Bürkert resistApp .....	5
<b>5. Dimensions</b>	<b>5</b>
5.1. Threaded variant .....	5
Standard variant, normally closed (CF A) .....	5
ATEX/IECEX terminal box variant .....	6
<b>6. Performance specifications</b>	<b>7</b>
6.1. Power consumption .....	7
<b>7. Ordering information</b>	<b>7</b>
7.1. Bürkert eShop .....	7
7.2. Bürkert product filter .....	7
7.3. Bürkert Product Enquiry Form .....	7
7.4. Ordering chart .....	8
Standard variant .....	8
ATEX/IECEX terminal box variant .....	8

DTS 1000636664 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.12.2025

## 1. General technical data

Product properties	
Dimensions	Further information can be found in chapter "5. Dimensions" on page 5.
Material	
Seal	PCTFE/PTFE
Body	Stainless steel 1.4404/316L
Coil	Powder-coated steel
Tightness	
Permissible internal leakage rate	$2 \times 10^{-3}$ mbar l/s at 20 bar, $5 \times 10^{-5}$ mbar l/s at nominal pressure
Permissible external leakage rate	$5 \times 10^{-5}$ mbar l/s
Max. switching cycles regarding leakage rates	Approx. 50.000 at $\Delta p = 100 \dots 200$ bar
Max. absolute switching cycles (service)	Approx. 100.000 (1 year) at $\Delta p = 100 \dots 200$ bar
Pressure	
Pressure level	PN 900 bar
Differential pressure <sup>1)</sup>	0...900 bar Further information can be found in chapter "7.4. Ordering chart" on page 8.
Orifice	Closed without power (CF A): DN 0.5 and DN 0.77
Circuit function	A Further information can be found in chapter "2. Circuit functions" on page 4.
Thermal insulation class of solenoid coil	Class H
Performance data	
Duty cycle	100 % continuous operation
Electrical data	
Operating voltage	24 V DC, 24 V 50 Hz, 24 V 60 Hz, 120 V 60 Hz, 230 V 50 Hz (other voltages on request)
Voltage tolerance	$\pm 10$ %
Medium data	
Operating medium <sup>2)</sup>	Hydrogen
Medium temperature	- 40 °C...+ 80 °C
Viscosity	Max. 22 mm <sup>2</sup> /s (22 cSt)
Product connections	
Electrical connection	Male cable plug according to DIN 43650 Terminal box M16×1.5 (ATEX)
Port connection	G ¼
Approvals and conformities	
Degree of protection	IP65 according to DIN 60529
Explosion protection	Further information can be found in chapter "3.4. Explosion protection" on page 4.
Environment and installation	
Installation position	Actuator upright or horizontal
Ambient temperature	Closed without power (CF A): - 20 °C...+ 50 °C

1.) Pressure data: overpressure to atmospheric pressure, depending on orifice, tightness seal or nominal pressure

2.) Medium resistance according to material combination

## 2. Circuit functions

Symbol	Description
	<b>Circuit function A (CF A)</b> 2/2-way solenoid valve Direct-acting Normally closed

## 3. Approvals and conformities

### 3.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available variants can be supplied with the below mentioned approvals or conformities.

### 3.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives. This includes the following directives:

- Pressure equipment directive 2014/68/EU category IV
- Machinery directive 2006/42/EC

### 3.3. Standards


The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

### 3.4. Explosion protection

Approval	Description	
 	<b>Optional: Explosion protection (valid for coils with terminal box)</b>	
	<b>As a category 3 device suitable for zone 2/22.</b>	<b>As a category 2 device suitable for zone 1/21 (expected to be available from Q2 2026).</b>
	<b>ATEX:</b> II 3G Ex ec IIC T3 Gc III 3D Ex mb tb IIIB T155 °C Db  <b>IECEX:</b> Ex ec IIC T3 Gc Ex mb tb IIIB T155 °C Db	<b>ATEX:</b> II 2G Ex e mb IIC T4 Gb II 2D Ex tb mb IIIC T130 °C Db  <b>IECEX:</b> Ex e mb IIC T4 Gb Ex tb mb IIIC T130 °C Db

## 4. Materials

### 4.1. Bürkert resistApp



#### Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

[Start chemical resistance check](#)


## 5. Dimensions

### 5.1. Threaded variant

Standard variant, normally closed (CF A)

**Note:**


Dimensions in mm



**ATEX/IECEx terminal box variant**

**Note:**

Dimensions in mm



## 6. Performance specifications

### 6.1. Power consumption

**Note:**

The cable plug for alternating current (AC) valves contains an integrated rectifier.

Coil size [mm]	Cold performance [W]
49 (8)	24
49 (8) ATEX	24

## 7. Ordering information

### 7.1. Bürkert eShop



#### Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

### 7.2. Bürkert product filter




#### Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

### 7.3. Bürkert Product Enquiry Form



#### Bürkert Product Enquiry Form – Your enquiry quickly and compactly

Would you like to make a specific product enquiry based on your technical requirements? Use our Product Enquiry Form for this purpose. There you will find all the relevant information for your Bürkert contact. This will enable us to provide you with the best possible advice.

[Fill out the form now](#)

DTS 1000636664 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.12.2025

### 7.4. Ordering chart

#### Standard variant

**Note:**

Other variants are available on request.

Circuit function	Port connection	Orifice	K <sub>v</sub> value water	Pressure range (MAWP <sup>1.)</sup> )	Article no.		
		[mm]	[m <sup>3</sup> /h]	[bar]	024/DC [V/Hz]	024/AC [V/Hz]	230/AC [V/Hz]
<b>Stainless steel body, internal G thread, seal material PCTFE+PTFE, cable head with integrated rectifier for AC included in scope of delivery</b>							
<b>CF A</b> 2/2-way solenoid valve Direct-acting Normally closed 	G ¼	0.5	0.015	0...900	20092947	20093197	20093199
		0.7	0.020	0...500	20093200	20093201	20093202

o. r. = on request

1.) Maximum allowable working pressure

#### ATEX/IECEx terminal box variant

**Note:**

As a category 3 device suitable for zone 2/22.

Circuit function	Port connection	Orifice	K <sub>v</sub> value water	Pressure range (MAWP <sup>1.)</sup> )	Article no.		
		[mm]	[m <sup>3</sup> /h]	[bar]	024/DC [V/Hz]	024/AC [V/Hz]	230/AC [V/Hz]
<b>Stainless steel body, internal G thread, seal material PCTFE+PTFE</b>							
<b>CF A</b> 2/2-way solenoid valve Direct-acting Normally closed 	G ¼	0.5	0.015	0...900	20122660	o. r.	o. r.
		0.7	0.020	0...500	20126568	o. r.	o. r.

o. r. = on request

1.) Maximum allowable working pressure

DTS 1000636664 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.12.2025