Radar filling level meter for liquids and bulk solids

- Suitable for simple applications such as water treatment, storage tanks and small silos
- Continuous filling level measurement up to 20 m, 4...20 mA, 2-wire
- Available process connections: thread (G, NPT, R 1½)
- Excellent radar signal focusing and high measurement dynamics
- Adjustable via Bluetooth, available with or without display

Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

Type 8619 ▸
multiCELL – multi-channel/ multi-function transmitter/ controller

Type 8692 ▸
Digital electropneumatic positioner for integrated mounting on process control valves

Type 8647 ▸
AirLINE SP – electropneumatic automation system

Type ME44 ▸
I/O module, IP 20

Type description

The device Type 8131 is a non-contact radar level meter, ideal for continuous level measurement of liquids and bulk solids in basic applications. It is particularly suitable for storage tanks, water treatment applications (open channel measurement) as well as through plastic tanks. For solids, it can be used in small silos or open tanks.

The radar level meter, available in 1½" with G, NPT or R connection, is equipped with a plastic housing and a plastic integrated antenna.

The excellent focus of the radar signal and the high measurement dynamics allow excellent measurement results even in small, narrow and high containers, as the risk of signal interference by installations, constructions and vessel walls is significantly reduced. Signal damping, e.g. due to signal length, foaming or low dielectric constant values of liquids, becomes much less important.

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

© Christian Bürkert GmbH & Co. KG, Subject to alteration

Visit product website ▸

Table of contents

1. General technical data 3

2. Approvals and conformities 6

2.1. General notes ... 6
2.2. Conformity ... 6
2.3. Standards ... 6
2.4. Explosion protection ... 6
2.5. North America (USA/Canada) ... 7
2.6. Foods and beverages/Hygiene ... 7

3. Materials 7

3.1. Bürkert resistApp ... 7

4. Dimensions 8

5. Performance specifications 9

5.1. Measurement deviation diagram ... 9
Variant 0...10 m ... 9
Variant 0...20 m ... 9

6. Product installation 9

7. Product operation 10

7.1. Measurement principle ... 10
7.2. Product operation notes ... 10
Operating techniques ... 10

8. Product accessories 11

9. Ordering information 11

9.1. Bürkert eShop ... 11
9.2. Bürkert product filter ... 12
9.3. Ordering chart ... 12
9.4. Ordering chart accessories ... 12

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

1. General technical data

Product properties	
Material	
Make sure the device materials are compatible with the fluid you are using. Further information can be found in chapter s"3.1. Bürkert resistApp" on page 7.	
Non-wetted parts	
Cover	PBT (polyester)
Housing	PBT (polyester)
Seal	Between housing and cover: silicone O-ring Cable gland seal: EPDM
Cable gland	PA
Blind plug	PA
Wetted parts	
Process connection	PVDF
Antenna	PVDF
Seal	Flat seal between sensor and container: • FKM for the variant with G thread and without food/pharmaceutical certificate • EPDM for the variant with G thread and food/pharmaceutical certificate • No seal for variants with R and NPT threads
Display	LCD with graphical support
Dimensions	Further information can be found in chapter "4. Dimensions" on page 8.
Weight	Approx. 0.7 kg
Measured quantity	Distance between the end of the sensor antenna and the product surface. The edge of the antenna is also the measurement reference level.
Beam angle [1.]	8°
Measuring range	• 0...10 m depending on application and medium (recommended measuring range 0...5 m with bulk solids) • 0...20 m depending on application and medium (recommended measuring range 0...10 m with bulk solids)
Damping (63 % of the input variable)	0...999 s, adjustable
Operating mode	The configurable operating mode depends on the country in which the device is used. • Mode 1: EU, Albania, Andorra, Azerbaijan, Australia, Belarus, Bosnia and Herzegovina, Canada, Iceland, Liechtenstein, Moldavia, Monaco, Montenegro, Morocco, New Zealand, Northern Macedonia, Norway, San Marino, Saudi Arabia, Serbia, South-Africa, Switzerland, Turkey, Ukraine, United Kingdom, USA • Mode 2: Brazil, Japan, South Korea, Taiwan, Thailand • Mode 3: India, Malaysia • Mode 4: Kazakhstan, Russia
Performance data	
Blocking distance	Depending on the operating conditions • Operating mode 1, 2 and 4: 0 mm • Operating mode 3: ≥ 250 mm
Measuring range resolution	1 mm
Measurement deviation	According to EN 60770-1 • Variant 0...10 m: ≤ 5 mm for liquids (measurement distance > 0.25 m) • Variant 0...20 m: ≤ 2 mm for liquids (measurement distance > 0.25 m) Further information can be found in chapter "5.1. Measurement deviation diagram" on page 9.
Non-repeatability [2.]	• Variant 0...10 m: ≤ 5 mm • Variant 0...20 m: ≤ 2 mm
Measuring frequency	W-Band (80 GHz technology)
Measuring cycle time [3.]	≤ 250 ms
Step response time [3.] [4.]	≤ 3 s
Temperature drift	< 0.03 %/10K or max. 0.3 % related to the 16.7 mA span

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

Electrical data	
Operating voltage (U_n)	12...35 V DC Connection to main supply: permanent
Power source (not supplied)	Limited energy circuit (power max. 100 W) according to IEC 61010-1, e.g.: • Class 2 power supply unit (according to UL1310) • SELV power supply unit (safety extra-low voltage) with suitable internal or external limitation of the output current • PELV power supply unit (protective low voltage) with suitable internal or external limitation of the output current
DC reverse polarity protection	Yes
Residual ripple (at DC)	• For 12 V< U_n < 18 V: ≤ 0.7 V_{eff} (16...400 Hz) • For 18 V< U_n < 35 V: ≤ 1.0 V_{eff} (16...400 Hz)
Overvoltage category according to IEC 61010-1	Category III
Protection class according to IEC 61010-1	Class III
Starting current	≤ 3.6 mA; ≤ 10 mA for 5 ms after switching on
Load resistor	$(U_n - U_{min})/0.022$ A
Output	• Variant 0...10 m: 4...20 mA • Variant 0...20 m: 4...20 mA/HART
Output signal range	• Variant 0...10 m: 3.8...20.5 mA (default setting) • Variant 0...20 m: 3.8...20.5 mA/HART (default setting)
Signal resolution	0.3 µA
Output current	Max. 22 mA
Fault signal	Current output: mA value unchanged, ≥ 21 mA or ≤ 3.6 mA (adjustable)
Voltage supply cable	• Cable diameter: 4.5...9 mm • Wire cross-section: – Massive wire, stranded wire: 0.2 mm² (AWG 24)...2.5 mm² (AWG 14) – Stranded wire with end sleeve: 0.2 mm² (AWG 24)...1.5 mm² (AWG 16)
Medium data	
Process temperature [5.]	• Variant 0...10 m: - 40...+ 60 °C (- 40...+ 140 °F) • Variant 0...20 m: - 40...+ 80 °C (- 40...+ 176 °F)
Process pressure [5.]	Vessel pressure: - 1...3 bar (- 100...300 kPa/- 14.5...43.5 psig)
Product connections	
Process connection	G, NPT or R 1½ thread
Electrical connection	Cable gland M20 × 1.5
Wireless communication: Bluetooth	
Communication interface	Bluetooth radio V5.0, downward compatible with V4.0
System requirements	• For smartphone/tablet: – Operating system: iOS 13 or newer – Operating system: Android 5.1 or newer – Bluetooth: 4.0 LE or newer • For PC/notebook – Operating system: Windows 10 or newer – DTM Collection: 10/2020 or newer – Bluetooth: 4.0 LE or newer
Frequency	2.402...2.480 GHz
Emitted power	Max. + 2.2 dBm
Number of participants	Max. 1
Typical effective range	25 m (82 ft) [6.]
Approvals and conformities	
Directives	
CE directive	Further information on the CE Directive can be found in chapter "2.3. Standards" on page 6.

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

NAMUR recommendation	• NE21 - Electromagnetic compatibility of equipment • NE43 - Signal level for fault information from measuring transducers • NE53 - Compatibility of field devices and display/adjustment components • NE107 - Self-monitoring and diagnosis of field devices
Explosion protection	ATEX/IECEx [7.] (only variant 0...20 m): EN IEC 60079-0:2018, IEC 60079-26:2015, EN 60079-11:2012 Further information can be found in chapter "2.4. Explosion protection" on page 6.
North America (USA/Canada)	On request • CSA ordinary location • FM (Factory Mutual) ordinary location Further information can be found in chapter "2.5. North America (USA/Canada)" on page 7.
Foods and beverages/Hygiene	On request • FDA declaration of conformity [7.] • 1935/2004/EC declaration [7.] Further information can be found in chapter "2.6. Foods and beverages/Hygiene" on page 7.
Others	Radio licenses [7.]: Europe (in EC declaration), New Zealand, USA, South Korea, Australia, Canada, Brazil, Malaysia, Serbia, Japan, Thailand, India, Taiwan, Morocco, Ukraine, South Africa
Environment and installation	
Ambient temperature	• Operation: – Variant 0...10 m: - 40...+ 60 °C (- 40...+ 140 °F) – Variant 0...20 m: - 40...+ 70 °C (- 40...+ 176 °F) • Storage and transport: - 40...+ 80 °C (- 40...+ 176 °F)
Relative air humidity	Max. 95 %
Height above sea level	Max. 5000 m
Degree of protection according to IEC/EN 60529	IP66/IP67 with M20 × 1.5 cable plug mounted and tightened
Pollution degree	Degree 4 (when used with fulfilled housing protection)

1.) Outside the specified beam angle, the energy level of the radar signal is 50 % (- 3 dB) less.
2.) Already included in the measurement deviation
3.) With operating voltage U_n ≥ 24 V DC
4.) Time span after a sudden measurement distance change from 1...5 m, until the output signal has taken for the first time 90 % of the final value (IEC 61298-2).
5.) Observe the specifications on the type label. It indicates the respective lowest value to be applied.
6.) Depending on the local conditions
7.) Approval of VEGAPULS 11, VEGAPULS 21 or VEGAPULS 31 product range from VEGA

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

2. Approvals and conformities

2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available variants can be supplied with the below mentioned approvals or conformities.

2.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

2.4. Explosion protection

Approval	Description
	Optional: Explosion protection [1.)] Ex marking of the components according to: **ATEX:** KIWA 19ATEX0028X • II 1G, 1/2G Ex ia IIC T4 Ga, Ga/Gb **IECEx:** IECEx KIWA 19.0015X • Ex ia IIC T4...T1 Ga or Ga/Gb **UKEx:** UL21UKEX2284X Rev. 1 • II 1G, 1/2G Ex ia IIC T4 Ga or Ga/Gb **c-FM-us:** FM20CA0003X • Cl I, Div 1, Gp ABCD T4; Cl I, Zn 0, 0/1 Ex ia IIC T4 Ga or Ga/Gb **c-CSA-us:** Certificate: 80000123 • Class I, Division 1, Groups A, B, C, D; Class II, Division 1, Groups E, F, G; Class III T4 Ex ia IIC T4 Ga, GaGb Class I, Zone 0, 0/1 AEx ia IIC T4 Ga, Ga/Gb Any unauthorized modifications made to the device will invalidate the Ex-certification.

1.) Approval of VEGAPULS 21 or VEGAPULS 31 product range from VEGA

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

2.5. North America (USA/Canada)

Approval	Description
C US	**Optional: CSA ordinary location [1.] for Canada and the USA** The products are CSA approved for Canada and the USA according to: • CAN/CSA-C22.2 No. 61010-1-12 • UL 61010-1 (ELECTRICAL EQUIPMENT FOR MEASUREMENT, CONTROL, AND LABORATORY USE – Part 1: General Requirements) Certificate: 80001942
FM C US APPROVED	**Optional: FM (Factory Mutual) ordinary location [1.]** The products are FM approved for the USA and Canada according to: • FM Class 3810, ANSI/UL 61010-1, ANSI/UL 50E and ANSI/IEC 60529:R Certificate: FM19NUS0009 • CAN/CSA-C22.2 No. 61010-1, CSA-C22.2 No. 94.2 and CAN/CSA-C22.2 No. 60529 Certificate: FM19NCA0004 The products are suitable for use in ordinary (non-hazardous) locations, indoor and outdoor, with degree of protection IP66/67 or IP66/68 (IPX8@ 3 bar, 24 hr) as well as Type 4X and Type 6P.

1.) Approval of VEGAPULS 11 or VEGAPULS 21 product range from VEGA

2.6. Foods and beverages/Hygiene

Conformity	Description
FDA	**FDA [1.] – Code of Federal Regulations** The devices comply in their composition with the Code of Federal Regulations published by the FDA (Food and Drug Administration, USA).
	EC Regulation 1935/2004 [1.] of the European Parliament and of the Council All wetted materials are compliant with EC Regulation 1935/2004 according to the manufacturer's declaration.

1.) Approval of VEGAPULS 11 or VEGAPULS 21 product range from VEGA

3. Materials

3.1. Bürkert resistApp



Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

Start chemical resistance check

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

4. Dimensions

Note:
Dimensions in mm, unless otherwise stated



DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

5. Performance specifications

5.1. Measurement deviation diagram

The following drawings show the measurement deviation of Type 8131 according to the variant under the following process reference conditions according to EN 61298-1:

- Temperature: + 18...+ 30 °C (+ 64...+ 86 °F)
- Relative humidity: 45...75 %
- Air pressure: 860...1060 mbar
- Installation reference conditions:
  - Distance to installations: > 200 mm
  - Reflector: flat plate reflector
  - False reflections: biggest interfering signal, 20 dB smaller than the useful signal

In case of deviations from reference conditions, the installation-related offset can be up to ± 4 mm. This offset can be compensated by the adjustment.

Variant 0...10 m



Variant 0...20 m



6. Product installation

The Type 8131 level meter can be screwed directly onto a tank. However, threaded flanges, weld-on threaded connections or hygienic threaded adapters for simple adaptation to the process connection of the device with threaded connection are available as accessories. Adjustable brackets or swivel-head brackets are also available, allowing the instrument to be easily mounted on a wall or ceiling. Particularly in the case of open channels, this is a simple and effective way of aligning the sensor with the liquid surface.

Further information on accessories can be found in chapter "8. Product accessories" on page 11.

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

7. Product operation

7.1. Measurement principle

The radar measuring device for the measurement of liquid or bulk solids levels consists of a housing with electronics and a process connection with antenna. The lens-shaped antenna of the radar sensor emits a continuous, frequency-modulated radar signal. This is reflected by the liquid or bulk solids surface and received by the antenna as an echo. Radar waves propagate at the speed of light. The frequency difference between the transmitted and received signal is determined by special algorithms in the sensor electronics. The filling level is calculated, converted into a corresponding output signal and transmitted as a measured value.

The measuring range of the radar level measuring device Type 8131 begins physically at the end of the antenna.



7.2. Product operation notes

Operating techniques

Devices with integrated Bluetooth module can be adjusted wirelessly via standard adjustment tools:

- Smartphone/tablet (iOS or Android operating system)
- PC/notebook with Bluetooth USB adapter (Windows operating system)

Wireless connection to standard operating devices	Description	
	**1**	Radar filling level meter
	2	Smartphone/tablet
	3	PC/notebook with Bluetooth USB adapter
	Operation is via the free App “Wireless Device configurator” from the “Apple App Store”, the “Google Play Store” or the “Baidu Store”. Alternatively, adjustment can also be carried out via PACTware/DTM and a Windows PC.	

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

8. Product accessories

Note:
The following accessories are available on request. Part numbers for some of these accessories are listed in Chapter "9.4. Ordering chart accessories" on page 12. For accessories not listed, contact your Bürkert sales office.

Accessory	Description
Length [mm] to sensor center: 80 200 400 200  Sensor holder ø 1 ½", adjustable Sensor holder ø 1 ½", fixed	**Mounting bracket for wall mounting:** • length 80 or 200 mm, with Ø 1½" adjustable sensor holder • length 200 mm, with Ø 1½" fixed sensor holder
Length [mm] to sensor center: 400 400 500...800  Horizontally swivelling Vertically foldable Extendable Sensor holder ø 1 ½"	**Mounting bracket for wall mounting with Ø 1½" sensor holder:** • horizontally swivelling, length 400 mm • vertically foldable, length 400 mm • extendable, length 500...800 mm
	Adapter flange • DN 50 PN 10 • DN 80 PN 6 • DN 100 PN 6
	Hygienic adapter (G 1½) • Clamp 2", 2½", 3", 4" DIN 32676, ISO 2852 • Aseptic DN 50, DN 65, DN 80 PN 2 DIN 11851

9. Ordering information

9.1. Bürkert eShop

Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

Order online now

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026

9.2. Bürkert product filter

Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements?
Use the Bürkert product filter and find suitable articles for your application quickly and easily.

Try out our product filter

9.3. Ordering chart

Measuring range	Operating voltage	Process connection	Output	Approvals and conformities			Electrical connection	Article no.	
[m]	[V DC]			Ex protection	FDA	ECR1935/2004		Without display	With display
0...10	12...35 V DC	G 1½	4...20 mA (2 wires)	No	No	No	Cable gland M20 × 1.5	575830	–
		NPT 1½						575831	–
		R 1½						575832	–
0...20	12...35 V DC	G 1½	4...20 mA (2 wires)	No	No	No		575833	576670
		NPT 1½						575834	576671
		R 1½						575835	576672
		G 1½		Yes	No	No		575836	576673
		NPT 1½						575837	576674
		R 1½						575838	576675
		G 1½		No	Yes	Yes		575839	576676
		NPT 1½						575840	576677
		R 1½						575841	576678

Further variants on request

Approval

- CCOE/NEPSI/KTL/TIIS
- INMETRO/IA
- NSF/ANSI/CAN61/WRAS for variant with measuring range of 0...20 m

9.4. Ordering chart accessories

Description		Article no.
Mounting accessory		
Mounting bracket for wall mounting with Ø 1½" adjustable sensor holder	80 mm	576439
	200 mm	576653
	400 mm	576481
Adapter flange	DN 50 PN10	576285
	DN 80 PN6	576654
Hygienic adapter (G 1½)	Clamp 2"	575926

DTS 1000646695 EN Version: - Status: RL (released | freigegeben | valide) printed: 28.10.2026