bürkert
FLUID CONTROL SYSTEMS

Oval gear volume flow sensor for low volume flow rates

- For highly viscous fluids
- Value indication, monitoring, transmitting, On/Off control and batch control in combination with different transmitters

Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

Type 8025
Insertion flowmeter or batch controller with paddle wheel and flow transmitter or remote batch controller

Type 8692
Digital electropneumatic positioner for integrated mounting on process control valves

Type 8619
multiCELL – multi-channel/ multi-function transmitter/ controller

Type description

This sensor is specially designed for measurement or batch control of highly viscous fluids like glue, honey or oil. It allows an easy connection to transmitters like Type 8025 or Type 8619 for more functionality.

The sensor for low volume flow operates according to the oval-gear measuring principle. Thi well-proven oval gear principle enables reliable and highly accurate measurem ith high repeatability over a wide flow and viscosity range.
Low pr and high pressure resistance allow the device to be used in a vari even at low pressure conditions

llector NPN frequency output and frequency output on re cable.

Phase out

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

© Christian Bürkert GmbH & Co. KG, Subject to alteration

Visit product website

Table of contents

1. General technical data 3

2. Approvals and conformities 4

2.1. Conformity 4
2.2. Standards 4
2.3. Pressure Equipment Directive (PED) 4
Device used on a pipe 4

3. Materials 4

3.1. Bürkert resistApp 4
3.2. Material specifications 5

4. Dimensions 5

5. Product installation 6

5.1. Installation notes 6
Flow measurement 6

6. Product operation 6

6.1. Measuring principle 6

7. Ordering information 7

7.1. Bürkert eShop 7
7.2. Bürkert product filter 7
7.3. Ordering chart 7
7.4. Ordering chart accessories 7

Phase out

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

1. General technical data

Product properties	
Material	
Make sure the device materials are compatible with the fluid you are using. Further information can be found in chapter "3.1. Bürkert resistApp" on page 4.	
Further information on the materials can be found in chapter "3.2. Material specifications" on page 5.	
Non-wetted parts	
Screw	Stainless steel 316
Tag plate	Aluminium
Wetted parts	
Axis	Alloy C
Oval gear	PPS
Sensor body	PPS
Cover	PPS
Seal	FFKM
Compatibility	With Type 8025 Universal transmitter/batch controller, Type 8611 eCONTROL Universal controller or Type 8619 multiCELL transmitter/Controller Further information can be found in the respective technical data sheets, see **data sheets Type 8025** ▶, **Type 8611** ▶, **Type 8619** ▶ for more information.
Dimensions	Further information can be found in chapter "4. Dimensions" on page 5.
Measuring principle	Oval gear
Type of sensor	Hall effect (Transistor output) or Reed contact (reed switch outpu)
Measuring range	0.5...500 l/h (0.13...132 gph) (depends on the variant)
Standard K factor	• For flow range 0.5...120 l/h: 1000 pulses/l • For flow range 15...500 l/h: 400 pulses/l
Performance data	
Measurement deviation	± 1 % of measured value
Repeatability	≤ 0.03 % of measured val
Electrical data	
Operating voltage	4.5...24 V DC
Current consumption	≤ 9 mA (Hall ef
Output	• Hall effe – Fr 25 mA p at 24 V DC V DC,
Medium data	
Fluid temperat	...+ 176 °F)
Fluid press	
Dynami (higher on request)	
Max	revent damage from dirt or foreign matter, we strongly recommend the installation of a 75 µm 00 mesh) strainer as close as possible to the inlet side of the meter.
	Thread ¼" (G or NPT)
Ele	• 5-wire cable • 1 m length
Approval ormities	
Directives	
CE directive	Further information on the CE Directive can be found in chapter "2.2. Standards" on page 4.
Pressure equipment directive	Complying with article 4, paragraph 1 of 2014/68/EU directive Further information on the pressure equipment directive can be found in chapter "2.3. Pressure Equipment Directive (PED)" on page 4.

Phase out

Environment and installation	
Ambient temperature	Operation and storage: -15...+80 °C (+5...+176 °F)
Relative air humidity	≤ 85 %, without condensation
Height above sea level	Max. 2000 m
Operating condition	Continuous
Device mobility	Fixed
Application range	Indoor and outdoor Protect the device against electromagnetic interference, ultraviolet rays and, when installed outdoors, against the effects of climatic conditions.
Degree of protection	IP54 (NEMA 13)
Installation category	Category I according to UL/EN 61010-1
Pollution degree	Degree 2 according to UL/EN 61010-1

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

2. Approvals and conformities

2.1. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

2.2. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

2.3. Pressure Equipment Directive (PED)

The device conforms to article 4, paragraph 1 of the Pressu ipment Directive (PED) 2014/68/EU under the following conditions:

Device used on a pipe

Note:

- The data in the table is independent of th al and the fluid.
- PS = maximum admissible pressure (i pe

Type of fluid	onditions
Fluid group 1, Article 4, Paragr	DN ≤ 25
Fluid group 2, Article 4, Pa	DN ≤ 32 or PS*DN ≤ 1000
Fluid group 1, Article 4, 1	DN ≤ 25 or PS*DN ≤ 2000
Fluid group 2, Articl	DN ≤ 200 or PS ≤ 10 or PS*DN ≤ 5000

Phase out

3.

3.



Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

Start chemical resistance check

3.2. Material specifications



No.	Element	Material
1	Screws	Stainless steel 316
2	Tag plate	Aluminium
3	Cap	PPS
4	Seal	FFKM
5	Oval gear	PPS
6	Shaft	Alloy C
7	Body	PPS

4. Dimensions

Note:
Dimensions in mm, unless otherwise stated



Phase out

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

5. Product installation

5.1. Installation notes

Flow measurement

Note:
The device is not suitable for use in gaseous media and steam.

The flowmeter can be installed in any orientation as long as **the rotor shafts are always in a horizontal plane**.



The following installation conditions must also be observed:

- The pipe always has to be filled with fluid at all times near the device.
- The pipe design must be such that no air bubbles or cavitation can form within the medium near the device at any time.
- We recommend the installation of a 75 µm strainer as close as possible to the inlet side of the meter, to prevent damage from particles,
- Air purges can damage the appliance and should therefore be avoided.

6. Product operation

6.1. Measuring principle

When liquid flows through the pipe, the rotors turn. This r… …duces a measuring signal in the associated Hall sensor. The rotation frequency of this signal is proportional to the flow velo… …The volume of the fluid being transferred in this way is exactly determined through the sensor geometry.



A conversion co… …nables the conversion of this frequency into a flow rate. The standard K-factor depending o… …meter's operating instructions, see **Type 8071** ▶. To improve the measurement deviation, a device-s… …abel.

Phase out

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026

7. Ordering information

7.1. Bürkert eShop

Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

Order online now

7.2. Bürkert product filter

Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements?
Use the Bürkert product filter and find suitable articles for your application quickly and easily.

Try out our product filter

7.3. Ordering chart

Measuring range for fluid with viscosity		Pipe connection	Max. ure	Material				Article no.
> 5 mPa.s	< 5 mPa.s			Body	Rotor	Shaft	Seal	
0.5...100 l/h (0.13...26.4 gph)	2 [1)]...100 l/h (0.53...26.4 gph)	G ¼"		PPS	PPS	Alloy C	FFKM	432288
15...500 l/h (4.00...132 gph)	40...500 l/h (10.56...132 gph)							430856
0.5...100 l/h (0.13...26.4 gph)	2 [1)]...100 l/h (0.53...26.4 gph)							448654
15...500 l/h (4.00...132 gph)	40...500 l/h (10.56...13							448655

1.) For non-lubricating fluids = 6 l/h

7.4. Orderi

Descriptio		Article no.
Set wit	.5...100 l/h	550921
Set	ge 15...500 l/h	550922
	d reed contact	553654
		550959

Phase out

DTS 1000024863 EN Version: - Status: PO (Phase out | Phase out | Phase out) printed: 02.11.2026