



Fitting connectors

- M5 ... G 2 1/2"
- Nickel-plated brass, stainless steel, plastic, aluminium

Product variants described in the data sheet may differ from the product presentation and description.

Type description

Includes:

Standard fittings

- double nipple
- detachable double nipple
- reducers
- reducer sleeves
- extension nipple
- extensions
- sleeves
- angled fittings
- dummy plug
- hose connectors
- lock nut
- T-connector
- crosspiece

Screwed fittings

- bulkhead fittings
- pressure gauge fittings
- elbows
- T-shaped tube hose fitting
- T-shaped fittings
- union nut
- tube hose fittings
- ring connectors
- seal rings
- distribution manifold
- four-way distributor blocks
- flow manifold

Table of contents

1. General technical data	4
2. Approvals and conformities	4
2.1. General notes	4
2.2. Conformity	4
2.3. Standards	4
3. Materials	4
3.1. Bürkert resistApp	4
4. Dimensions	5
5. Ordering information	5
5.1. Bürkert eShop	5
5.2. Bürkert product filter	5
5.3. Ordering chart standard fittings	5
Overview standard fittings	5
Double nipples, cylindrical, without O-ring, according to UNI-ISO 228/1, nickel-plated brass	6
Double nipples, cylindrical, without O-ring, according to UNI-ISO 228/1, stainless steel 1.4571	6
Double nipples, conical, according to UNI-ISO 7/1	6
Double nipples, detachable, male, according to UNI-ISO 7/1, brass	7
Double nipples, detachable, male, according to UNI-ISO 7/1, stainless steel 1.4571	7
Reducers, cylindrical, according to UNI-ISO 228/1, nickel-plated brass	7
Reducers, cylindrical, according to UNI-ISO 228/1, stainless steel 1.4571	7
Reducers, conical, according to UNI-ISO 228/1 and UNI-ISO 7/1	8
Reducer sleeves, according to UNI-ISO 228/1	8
Extension nipples, conical, according to UNI-ISO 228/1 and UNI-ISO 7/1	8
Extension nipples, cylindrical, without O-ring, according to UNI-ISO 228/1	8
Extensions, according to UNI-ISO 228/1	9
Sleeves, according to UNI-ISO 7/1	9
Sleeves, according to UNI-ISO 228/1	9
Elbows, with internal thread, according to UNI-ISO 228/1	9
Elbows, with internal G thread according to UNI-ISO228/1 and conical external R thread according to DIN EN 10226-1	10
Dummy plugs without O-ring, according to UNI-ISO 228/1, stainless steel 1.4571	10
Dummy plugs, with O-ring, according to UNI-ISO 228/1	10
Hose connectors, with O-ring, according to UNI-ISO 228/1	10
Lock nuts, according to UNI-ISO 228/1	11
T-pieces, female and male, with internal thread, according to UNI-ISO 228/1	11
T-pieces, with internal G thread according to UNI-ISO228/1 and conical external R thread according to DIN EN 10226-1	11
Crosspieces, with internal thread, according to UNI-ISO 228/1	12
5.4. Ordering chart screw fittings	12
Overview screw fittings	12
Straight screwed fittings	12
Straight screwed fittings, with O-ring	13
Bulkhead fittings, nickel-plated brass	13
Bulkhead fittings, plastic	13
Pressure gauge fittings	13
Elbows, male, conical, according to UNI-ISO 7/1, plastic	14
Elbow, male, conical, according to UNI-ISO 7/1, nickel-plated brass	14
Elbow, female	14
T-piece, with hose fitting	14
T-screwing, central male, conical, according to UNI-ISO 7/1	15
Union nut	15
Hose connections, with nut	15

Banjo bolt, single with 2 seals	15
Banjo bolt, double with 3 seals	15
Single banjo body	16
Double banjo body	16
Seal rings.....	16
Distribution manifold, 3-fold	16
Distribution manifold, 8-fold	17
Four-way distributor block.....	17
Flow manifold	17

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

1. General technical data

Product properties

Dimensions Further information can be found in chapter "5. Ordering information" on page 5.

Performance data

Maximum nominal pressure ¹⁾

Nickel-plated brass

Standard fittings	60 bar (except double nipple 3-pc and plug)
Detachable double nipple and dummy plug	16 bar
Screw fittings	18 bar

Stainless steel

Standard fittings	40 bar (except double nipple 3-pc)
Double nipple 3-pc	16 bar

Plastic

Screw fittings	10 bar (except elbow, seal rings and distributor blocks)
Elbow, seal rings	18 bar
Distributor block	13 bar

Aluminium

Seal rings	18 bar
Distribution and flow manifold	16 bar

1.) Pressure data: overpressure to atmospheric pressure

2. Approvals and conformities

2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available variants can be supplied with the below mentioned approvals or conformities.

2.2. Conformity


In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

3. Materials

3.1. Bürkert resistApp



Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

[Start chemical resistance check](#)

4. Dimensions

Further information can be found in chapter “5. Ordering information” on page 5.

5. Ordering information

5.1. Bürkert eShop



Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

5.2. Bürkert product filter



Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.















[Try out our product filter](#)

5.3. Ordering chart standard fittings












Overview standard fittings

- Double nipple
- Detachable double nipple
- Reducers
- Reducer sleeves
- Extension nipple
- Extensions
- Sleeves
- Elbow
- Dummy plug
- Hose connectors
- Lock nut
- T-piece
- Crosspiece













Double nipple, cylindrical, without O-ring, according to UNI-ISO 228/1, nickel-plated brass

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Nickel-plated brass	60	M5	M5	11.5	10	782000 
			M5	G 1/8	14.5	10	782001 
			G 1/8	G 1/8	17	10	780123 
			G 1/8	G 1/4	19	10	780124 
			G 1/8	G 3/8	20	10	780125 
			G 1/4	G 1/4	21	10	780126 
			G 1/4	G 3/8	22	10	780127 
			G 1/4	G 1/2	24	10	780128 
			G 3/8	G 3/8	24	10	780129 
			G 3/8	G 1/2	24	10	780130 
			G 1/2	G 1/2	26.5	10	780131 
			G 1/2	G 3/4	27	10	782002 
G 3/4	G 3/4	28	10	782003 			

Double nipple, cylindrical, without O-ring, according to UNI-ISO 228/1, stainless steel 1.4571

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Stainless steel 1.4571	40	M5	M5	15	1	787843 
			G 1/8	G 1/8	18	1	787844 
			G 1/4	G 1/4	23	1	787845 
			G 3/8	G 3/8	23	1	787846 
			G 1/2	G 1/2	30	1	787847 
			G 3/4	G 3/4	33	1	787848 
			G 1	G 1	50	1	787849 
			G 1 1/4	G 1 1/4	58	1	787850 
			G 1 1/2	G 1 1/2	61	1	787851 
G 2	G 2	61	1	787852 			

Double nipple, conical, according to UNI-ISO 7/1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Nickel-plated brass	60	R 1/8	R 1/8	21	10	782006 
			R 1/8	R 1/4	24	10	782007 
			R 1/8	R 3/8	25	10	782008 
			R 1/4	R 1/4	27	10	782009 
			R 1/4	R 3/8	28	10	782010 
			R 1/4	R 1/2	32	10	782011 
			R 3/8	R 3/8	29	10	782012 
			R 3/8	R 1/2	32.5	10	782013 
			R 1/2	R 1/2	35	10	782014 
			R 1/2	R 3/4	37.5	10	782015 
R 3/4	R 3/4	40.5	10	782016 			

Double nipple, detachable, external thread, according to UNI-ISO 7/1, brass

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Brass	16	R 1/8	R 1/8	27	10	782090
			R 1/4	R 1/4	34	10	782091
			R 3/8	R 3/8	36	10	782092
			R 1/2	R 1/2	44	1	782093
			R 3/4	R 3/4	52	1	782094
			R 1	R 1	65	1	782095
			R 1/8	R 1/4	30	10	782096
			R 1/4	R 3/8	35	10	782097

Double nipple, detachable, external thread, according to UNI-ISO 7/1, stainless steel 1.4571

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Stainless steel 1.4571	16	R 1/8	R 1/8	27	1	787853
			R 1/4	R 1/4	35	1	787854
			R 3/8	R 3/8	36	1	787855
			R 1/2	R 1/2	44	1	787856
			R 3/4	R 3/4	75	1	787857
			R 1	R 1	90	1	787858
			R 1 1/2	R 1 1/2	110	1	787859
			R 2	R 2	120	1	787860

Reducer, cylindrical, according to UNI-ISO 228/1, nickel-plated brass

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Nickel-plated brass	60	G 1/8	M5	10.5	10	781843
			G 1/4	G 1/8	13	10	780136
			G 3/8	G 1/8	14	10	780137
			G 3/8	G 1/4	14	10	780138
			G 1/2	G 1/4	15.5	10	780139
			G 1/2	G 3/8	15.5	10	780140

Reducer, cylindrical, according to UNI-ISO 228/1, stainless steel 1.4571

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]		
	Stainless steel 1.4571	40	G 1/4	G 1/8	11	1	787861
			G 3/8	G 1/4	14	1	787862
			G 1/2	G 3/8	18	1	787863
			G 3/4	G 1/2	24	1	787865
			G 1	G 3/4	21	1	787866

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Reducer, conical, according to UNI-ISO 228/1 and UNI-ISO 7/1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]	[pieces]	
	Nickel-plated brass	60	R 1/4	G 1/8	16	10	782017
			R 3/8	G 1/8	17	10	782018
			R 3/8	G 1/4	17	10	782019
			R 1/2	G 1/4	20	10	782020
			R 1/2	G 3/8	20	10	782021
			R 3/4	G 1/2	23	10	782022

Reducer sleeve, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]	[pieces]	
	Nickel-plated brass	60	G 1/8	G 1/4	21.5	10	782038
			G 1/4	G 3/8	25.5	10	782040
			G 1/4	G 1/2	28.5	10	782041
			G 3/8	G 1/2	29.5	10	782042

Extension nipple, conical, according to UNI-ISO 228/1 and UNI-ISO 7/1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]	[pieces]	
	Nickel-plated brass	60	R 1/8	G 1/8	20	10	782023
			R 1/8	G 1/4	22.5	10	782024
			R 1/4	G 1/4	25	10	782025
			R 1/4	G 3/8	28.5	10	782026
			R 3/8	G 3/8	28.5	10	782027
			R 3/8	G 1/2	32	10	782028
			R 1/2	G 1/2	34	10	782029

Extension nipple, cylindrical, without O-ring, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	Packaging unit	Article no.
					[mm]	[pieces]	
	Nickel-plated brass	60	M5	G 1/8	17	10	782030
			G 1/8	G 1/8	18.5	10	782031
			G 1/8	G 1/4	21.5	10	782032
			G 1/4	G 1/4	22.5	10	782033
			G 1/4	G 3/8	26	10	782034
			G 3/8	G 3/8	26.5	10	782035
			G 3/8	G 1/2	29.5	10	782036
			G 1/2	G 1/2	29.5	1	782037

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Extension, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure	F	L	Packaging unit	Article no.
		[bar]				
	Nickel-plated brass	60	G 1/8	22	10	782085
			G 1/8	42	10	782086
			G 1/8	51	10	782087
			G 1/4	35	10	782088
			G 1/4	51	10	782089

Sleeve, according to UNI-ISO 7/1

Dimensions	Material	Max. nominal pressure	F	L	Packaging unit	Article no.
		[bar]				
	Stainless steel 1.4408	40	Rp 1/8	18	1	787868
			Rp 1/4	26	1	787869
			Rp 3/8	26	1	787870
			Rp 1/2	30	1	787871
			Rp 3/4	35	1	787872
			Rp 1	40	1	787873
			Rp 1 1/4	48	1	787874
			Rp 1 1/2	48	1	787875
			Rp 2	56	1	787876

Sleeve, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure	F	L	Packaging unit	Article no.
		[bar]				
	Nickel-plated brass	60	M5	11	10	782004
			G 1/8	15	10	780132
			G 1/4	22	10	780133
			G 3/8	24	10	780134
			G 1/2	30	10	780135

Elbow, with internal thread, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure	F Internal thread	L	Packaging unit	Article no.
		[bar]				
	Nickel-plated brass	60	G 1/8	20.5	10	782047
			G 1/4	26	10	782048
			G 3/8	30	10	782049
			G 1/2	36	1	782050

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Elbow, with internal G thread according to UNI-ISO228/1 and conical external R thread according to DIN EN 10226-1

Dimensions	Material	Max. nominal pressure [bar]	F	F1	L	L1	Packaging unit [pieces]	Article no.
					[mm]	[mm]		
	Nickel-plated brass	60	M5	M 5	11.0	11.5	10	788365
			G 1/8	R 1/8	16.5	20.5	10	782051
			G 1/4	R 1/4	24.5	26	10	782052
			G 3/8	R 3/8	26	30	10	782053
			G 1/2	R 1/2	30	36	1	782054

Dummy plug without O-ring, according to UNI-ISO 228/1, stainless steel 1.4571

Dimensions	Material	Max. nominal pressure [bar]	F	L	Packaging unit [pieces]	Article no.
				[mm]		
	Stainless steel 1.4571	40	G 1/2	15	1	787816
			G 3/4	11	1	787817
			G 1/8	11	1	774721
			G 1/4	13	1	774729
			G 3/8	14	1	774732
			G 1	22	1	787880

Dummy plug, with O-ring, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure [bar]	F	L	Packaging unit [pieces]	Article no.
				[mm]		
	Nickel-plated brass	16	M5	6.5	10	782005
			M7	8.5	10	787054
			G 1/8	8.5	10	780141
			G 1/4	11	10	780142
			G 3/8	12.5	10	780143
			G 1/2	14.5	10	780144

Hose connector, with O-ring, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure [bar]	F	Diameter	L	Packaging unit [pieces]	Article no.
				[mm]	[mm]		
	Nickel-plated brass	60	G 1/8	7	31	10	782070
			G 1/4	7	33	10	782071
			G 1/8	8	31	10	782072
			G 1/8	9	31	10	782073
			G 1/4	9	33	10	782074
			G 3/8	9	34	10	782075
			G 1/4	12	33	10	782076
			G 3/8	12	34	10	782077
			G 1/2	12	36	10	782078
			G 3/8	17	34	10	782079
			G 1/2	17	36	10	782080

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Lock nut, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure	F	L	Packaging unit	Article no.
		[bar]				
	Nickel-plated brass	60	G 1/8	13	10	782043
			G 1/4	15	10	782044
			G 3/8	17.5	10	782045
			G 1/2	20	10	782046

T-piece, with internal and external thread, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure	F	L	Packaging unit	Article no.
		[bar]				
	Nickel-plated brass	60	R 1/8	20.5	10	782055
			R 1/4	26	10	782056
			R 3/8	30	1	782057
			R 1/2	36	1	782058

T-piece, with internal G thread according to UNI-ISO228/1 and conical external R thread according to DIN EN 10226-1

Dimensions	Material	Max. nominal pressure	F	L	L1	Packaging unit	Article no.
		[bar]					
	Nickel-plated brass	60	G 1/8	16.5	20.5	10	782059
			G 1/4	24.5	26	10	782060
			G 3/8	26	30	1	782061
			G 1/2	30	36	1	782062

Dimensions	Material	Max. nominal pressure	F	F1	L	L1	Packaging unit	Article no.
		[bar]						
	Nickel-plated brass	60	G 1/8	R 1/8	37	20.5	10	782063
			G 1/4	R 1/4	50.5	26	10	782064
			G 3/8	R 3/8	56	30	1	782065
			G 1/2	R 1/2	66	36	1	782066

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Crosspiece, with internal thread, according to UNI-ISO 228/1

Dimensions	Material	Max. nominal pressure [bar]	F	L	Packaging unit [pieces]	Article no.
				[mm]		
	Nickel-plated brass	60	G 1/8	20.5	10	782067
			G 1/4	26	1	782068
			G 3/8	28	1	782069

5.4. Ordering chart screw fittings

Overview screw fittings

- Screwed fittings
- Bulkhead fittings
- Pressure gauge fittings
- Elbow
- T-connector
- T-screwing
- Union nut
- Hose connection
- Banjo bolt
- Banjo body
- Seal rings
- Distribution manifold
- Four-way distributor blocks
- Flow manifold

Straight screwed fittings

Material	Max. nominal pressure	F	Packaging unit	Article no.
	[bar]		[pieces]	
PPS	10	G 1/4...28 1/8	1	787060
PEEK		G 1/4...28 1/8	1	787061
PP		G 1/4...28 1/8	1	787062
PPS		G 1/4...28 1/16	1	787063
PEEK		G 1/4...28 1/16	1	787064
PP		G 1/4...28 1/16	1	787065

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Straight screwed fitting, with O-ring

Dimensions	Material	Max. nominal pressure [bar]	F	Diameter	L [mm]	Packaging unit [pieces]	Article no.
				[mm]			
	Nickel-plated brass	18	M5	4/2	23	10	780145
			M5	6/4	23	10	780146
			G 1/8	6/4	25	10	780147
			G 1/4	6/4	27	10	780148
			G 1/8	8/6	25	10	780149
			G 1/4	8/6	27	10	780150
			G 3/8	8/6	29	10	780151
			G 1/4	10/8	29	10	780152
			G 3/8	10/8	31	10	780153
			G 1/2	10/8	33	10	780154
			G 3/8	12/10	33	10	780155
G 1/2	12/10	35	1	780156			

Bulkhead fitting, nickel-plated brass

Dimensions	Material	Max. nominal pressure [bar]	Diameter	L [mm]	Packaging unit [pieces]	Article no.
			[mm]			
	Nickel-plated brass	18	6/4	47	10	780165
			8/6	48	10	780166
			10/8	49	10	780167
			12/10	53	10	780168

Bulkhead fitting, plastic

Dimensions	Material	Max. nominal pressure [bar]	Diameter	L [mm]	Packaging unit [pieces]	Article no.
			[mm]			
	Plastic	10	6/4	50	10	782197
			8/6	51	10	782198

Pressure gauge fitting

Dimensions	Material	Max. nominal pressure [bar]	Diameter	F	L [mm]	Packaging unit [pieces]	Article no.
			[mm]				
	Nickel-plated brass	18	6/4	G 1/8	26.5	10	780157
			6/4	G 1/4	29.5	10	780158
			8/6	G 1/8	26.5	10	780159
			8/6	G 1/4	29	10	780160
			8/6	G 3/8	33	10	780161
			10/8	G 1/4	31	10	780162
			10/8	G 3/8	35	10	780163
			10/8	G 1/2	38	10	780164

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Elbow, external thread, conical, according to UNI-ISO 7/1, plastic

Dimensions	Material	Max. nominal pressure	Diameter	F	L	L1	Packaging unit	Article no.
		[bar]	[mm]				[pieces]	
	Plastic	18	6/4	R 1/8	16	23	10	782209
			6/4	R 1/4	19	24	10	782211
			8/6	R 1/4	20	25	10	782212

Elbow, external thread, conical, according to UNI-ISO 7/1, nickel-plated brass

Dimensions	Material	Max. nominal pressure	Diameter	F	L	L1	Packaging unit	Article no.
		[bar]	[mm]				[pieces]	
	Nickel-plated brass	18	5/3	R 1/8	17	21.5	10	782163
			6/4	R 1/8	17	22	10	782164
			8/6	R 1/8	17	22	10	782165
			6/4	R 1/4	20	22	10	782166
			8/6	R 1/4	20	22	10	782167
			10/8	R 1/4	21	25	10	782168
			8/6	R 3/8	22	23	10	782169
			10/8	R 3/8	22	25	10	782170
			12/10	R 3/8	24	31	10	782171
			10/8	R 1/2	26	28.5	10	782172
			12/10	R 1/2	14	26	1	782173

Elbow, internal thread

Dimensions	Material	Max. nominal pressure	Diameter	F	L	L1	Packaging unit	Article no.
		[bar]	[mm]				[pieces]	
	Nickel-plated brass	18	6/4	G 1/8	21	22	10	782174
			8/6	G 1/4	24	23	10	782175

T-piece, with hose fitting

Dimensions	Material	Max. nominal pressure	Diameter	L	Packaging unit	Article no.
		[bar]	[mm]		[pieces]	
	Nickel-plated brass	18	6/4	22	10	780169
			8/6	22	10	780170
			10/8	25	10	780171
			12/10	31	1	780172

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

T-screwing, external, conical, according to UNI-ISO 7/1

Dimensions	Material	Max. nominal pressure	Diameter	F	L	L1	Packaging unit	Article no.
		[bar]					[mm]	
	Nickel-plated brass	18	5/3	R 1/8	17	21.5	10	782176
			6/4	R 1/8	17	22	10	782177
			6/4	R 1/4	20	22	10	782179
			8/6	R 1/8	17	22	10	782178
			8/6	R 1/4	20	22	10	782180
			8/6	R 3/8	22	23	10	782182
			10/8	R 1/4	21	25	10	782181
			10/8	R 3/8	22	25	10	782183
			10/8	R 1/2	26	28.5	1	782185
			12/10	R 1/2	24	31	1	782186
			12/10	R 3/8	26	31	1	782184

Union nut

Dimensions	Material	Max. nominal pressure	Diameter	F	L	Packaging unit	Article no.
		[bar]				[mm]	
	Nickel-plated brass	18	4/2	M7 × 0.5	9	10	780173
			6/4-M5	M8 × 0.5	9	10	780174
			6/4	M10 × 1	11	10	780175
			8/6	M12 × 1	11	10	780176
			10/8	M14 × 1	12	10	780177
			12/10	M16 × 1	12	10	780178

Hose connection, with nut

Dimensions	Material	Max. nominal pressure	Diameter	Packaging unit	Article no.
		[bar]			
	POM	10	6/4	10	782221
			8/6	10	782222

Banjo bolt, single with 2 seals

Dimensions	Material	Medium	F	L	Packaging unit	Article no.
				[mm]		
	Nickel-plated brass	Air	M5	18	10	780053
			G 1/8	28	10	780054
			G 1/4	33	10	780055
			G 3/8	37	10	780056
			G 1/2	42	1	780057

Banjo bolt, double with 3 seals

Dimensions	Material	Medium	F	L	Packaging unit	Article no.
				[mm]		
	Nickel-plated brass	Air	G 1/8	44.5	10	780058
			G 1/4	51.5	10	780059
			G 3/8	58.5	10	780060
			G 1/2	67.5	1	780061

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Single banjo body

Dimensions	Material	Max. nominal pressure	Diameter	F	L	Packaging unit	Article no.
		[bar]	[mm]		[mm]	[pieces]	
	Nickel-plated brass	18	4/2	M5	20.5	10	780179
			6/4	M5	20.5	10	780180
			6/4	G 1/8	24.5	10	780181
			6/4	G 1/4	26.5	10	780182
			8/6	G 1/8	24	10	780183
			8/6	G 1/4	26	10	780184
			8/6	G 3/8	28.5	10	780185
			10/8	G 1/4	28	10	780186
			10/8	G 3/8	29	10	780187
			10/8	G 1/2	30.5	10	780188
			12/10	G 1/2	33.5	1	780189

Double banjo body

Dimensions	Material	Max. nominal pressure	Diameter	F	L	Packaging unit	Article no.
		[bar]	[mm]		[mm]	[pieces]	
	Nickel-plated brass	18	6/4	G 1/8	24.5	10	780190
			6/4	G 1/4	26.5	10	780191
			8/6	G 1/8	25	10	780192
			8/6	G 1/4	26	10	780193
			8/6	G 3/8	28.5	10	780194
			10/8	G 1/4	27.5	10	780195
			10/8	G 3/8	29	10	780196
			10/8	G 1/2	30.5	10	780197
			12/10	G 1/2	33.5	10	780198

Seal ring

Dimensions	Material	Max. nominal pressure	Diameter	D	Packaging unit	Article no.
		[bar]	[mm]	[mm]	[pieces]	
	Aluminium	18	1/8	13.8	10	780200
			1/4	17.8	10	780201
			3/8	21	10	780202
			1/2	26	10	780203
	Plastic	18	M5	9	10	780199

Distribution manifold, 3-fold

Dimensions	Material	Max. nominal pressure	G	L	Packaging unit	Article no.
		[bar]		[mm]	[pieces]	
	Aluminium	16	M5	40	1	787881
			G 1/8	56	1	787882
			G 1/4	89	1	787883
			G 3/8	85	1	787884
			G 1/2	105	1	787885

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026

Distribution manifold, 8-fold

Dimensions	Material	Max. nominal pressure [bar]	G	G1	L	Packaging unit [pieces]	Article no.
					[mm]		
	Aluminium	16	G 1/4	M5	65	1	787886
			G 3/8	1/8	114	1	787887
			G 1/2	1/4	144	1	787888
			G 3/4	1/2	170	1	787889

Four-way distributor block

Dimensions	Material	Max. nominal pressure [bar]	F	Diameter	L	Packaging unit [pieces]	Article no.	
				[mm]				
	Plastic body, brass-threaded inserts	13		G 1/8	4.5	31	1	782081
				G 1/4	5.5	40	1	782082
				G 3/8	5.5	50	1	782083
				G 1/2	5.5	50	1	782084

Flow manifold

Dimensions	Material	Max. nominal pressure [bar]	G	G1	L	Packaging unit [pieces]	Article no.
					[mm]		
	Aluminium	16	G 1/4	2 x G 1/8	54	1	787890
				3 x G 1/8	72	1	787891
				4 x G 1/8	90	1	787892
				5 x G 1/8	108	1	787893
				2 x G 1/4	68	1	787894
				3 x G 1/4	92	1	787895
				4 x G 1/4	116	1	787896
				5 x G 1/4	140	1	787897
	Aluminium	16	G 1/4	4 x G 1/8	54	1	787717
				6 x G 1/8	72	1	787718
				8 x G 1/8	90	1	787719
				10 x G 1/8	108	1	787720
				4 x G 1/4	68	1	787721
				6 x G 1/4	92	1	787722
				8 x G 1/4	116	1	787723
				10 x G 1/4	140	1	787724
				6 x G 1/2	116	1	787725
				8 x G 1/2	152	1	787726
10 x G 1/2	188	1	787727				

DTS 1000112007 EN Version: J Status: RL (released | freigegeben | valide) printed: 13.05.2026