



Manually operated 2-way globe control valve

- Excellent control accuracy
- Exchangeable valve seats enable perfect coordination under the most demanding operating conditions
- Robust actuator with optional stroke limitation and locking
- Stainless steel valve body with flange, socket, clamp or welded connection

Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

	Type 2301 Pneumatically operated 2-way Globe Control Valve	▶
	Type 3361 Electromotive 2-way globe control valve	▶
	Type 2921 Manually operated 2/2-way globe valve	▶
	Type 2960 Manually operated 2-way angle seat control valve	▶
	Type 8802 ELEMENT continuous control valve systems – overview	▶
	Type 8840 Modular process valve cluster – distributor and collector	▶

Type description

The Type 2961 control valve consists of a manual actuator and a globe valve body with exchangeable seats made of high-quality stainless steel. Each globe valve body can be equipped with up to 8 valve seat sizes and reaches the desired flow characteristic curve in interaction with parabolic cones. The precise spindle guide enables control, even under demanding operating conditions. A soft PTFE or PEEK seal guarantees reliable sealing. The actuator is made of high-quality plastic and is suitable for use in demanding environments. It possesses a visual position indicator and can be optionally equipped with stroke limitation and locking. The spindle seal uses tried-and-tested V-seals and possesses spring compensation, which means that it does not need to be pulled back manually.

Table of contents

1. General technical data	3
<hr/>	
2. Approvals and conformities	4
2.1. General notes.....	4
2.2. Conformity	4
2.3. Standards.....	4
2.4. Explosion protection	4
2.5. Drinking water	4
2.6. Foods and beverages/Hygiene	5
<hr/>	
3. Materials	6
3.1. Bürkert resistApp	6
3.2. Material specifications	6
<hr/>	
4. Dimensions	7
4.1. Actuator	7
4.2. Body with flange connection	8
4.3. Body with threaded connection.....	9
4.4. Body with welded connection.....	10
4.5. Body with clamp connection	11
<hr/>	
5. Performance specifications	12
5.1. Fluidic data	12
Flow characteristics	12
Overview of fluidic data for flow below seat (for liquids, steam and gases).....	12
5.2. Operating limits.....	14
Operating limits for medium temperature and operating pressure	14
Operating limits for seat seal	15
Operating limits for optional versions	15
<hr/>	
6. Product design and assembly	16
6.1. Product features.....	16
<hr/>	
7. Ordering information	17
7.1. Bürkert eShop.....	17
7.2. Bürkert product filter.....	17
7.3. Bürkert Product Enquiry Form	17

1. General technical data

Product properties	
Dimensions	Further information can be found in chapter "4. Dimensions" on page 7.
Material	Further information can be found in chapter "3. Materials" on page 6.
Design	Globe control valve
Nominal diameter (port connection)	DN 10...DN 100, NPS ½...NPS 4
Flow direction	Flow to open (below seat)
Performance data	
Operating pressure	0 bar(g) ... 25 bar(g) (see "5.1. Fluidic data" on page 12)
Nominal pressure	PN 25 (DIN EN 1333), Class 150 (DIN EN 1759)
Seat leakage according to DIN EN 60534 - 4:2006	Leakage class II Leakage class VI for PTFE and PEEK (see "5.1. Fluidic data" on page 12)
K _v value	0.1 m ³ /h...140 m ³ /h (see "5.1. Fluidic data" on page 12)
Operating characteristic	Equal percentage
Medium data	
Medium	Steam, water, neutral gases, alcohol, oils, fuels, hydraulic fluids, salt solution, alkali solutions, organic solvents
Medium temperature	-40 °C...+230 °C (see "5.2. Operating limits" on page 14)
Viscosity	Max. 600 mm ² /s
Process/Port connection & communication	
Port connection ¹⁾	
Flange connection	DIN EN 1092 - 1 ANSI B 16.5 JIS 10K
Threaded connection	G (DIN ISO 228 - 1) NPT (ASME B1.20.1) RC (ISO 7 - 1)
Welded connection	DIN EN ISO 1127 / ISO 4200 / DIN 11866 series B DIN 11850 - 2 / DIN 11866 series A ASME BPE / DIN 11866 series C SMS 3008
Clamp connection	DIN 32676 series B (pipe: ISO 4200) DIN 32676 series A (pipe: DIN 11850 - 2) ASME BPE
Approvals and conformities	
Further information can be found in chapter "2. Approvals and conformities" on page 4.	
Environment and installation	
Ambient temperature	-10 °C...+60 °C
Installation position	As required, preferably with actuator upright

1.) Further versions are available on request.

2. Approvals and conformities

2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available versions can be supplied with the below mentioned approvals or conformities.

2.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives. This includes the following directives:

- Pressure Equipment Directive 2014/68/EU

2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

2.4. Explosion protection

Approval	Description																								
 	<p>Optional: Explosion protection Suitable as category 2 device for zone 1/21 and zone 2/22 (optional).</p> <p>ATEX: EPS 18 ATEX 2 008 X II 2G Ex h IIC T4...T2 Gb II 2D Ex h IIIC T135 °C...T300 °C Db</p> <p>IECEx: IECEx EPS 18.0007 X Ex h IIC T4...T2 Gb Ex h IIIC T135 °C...T300 °C Db</p> <table border="1"> <thead> <tr> <th>Temperature class</th> <th>T2</th> <th>T3</th> <th>T4</th> </tr> </thead> <tbody> <tr> <td>Permissible surface temperature</td> <td>+300 °C</td> <td>+200 °C</td> <td>+135 °C</td> </tr> <tr> <td>Ambient temperature</td> <td>-10...+60 °C</td> <td>-10...+60 °C</td> <td>-10...+60 °C</td> </tr> <tr> <td>Restrictions from the device</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Maximum medium temperature</td> <td>+230 °C</td> <td>+185 °C</td> <td>+125 °C</td> </tr> <tr> <td>Restrictions from the device</td> <td></td> <td></td> <td></td> </tr> </tbody> </table>	Temperature class	T2	T3	T4	Permissible surface temperature	+300 °C	+200 °C	+135 °C	Ambient temperature	-10...+60 °C	-10...+60 °C	-10...+60 °C	Restrictions from the device				Maximum medium temperature	+230 °C	+185 °C	+125 °C	Restrictions from the device			
Temperature class	T2	T3	T4																						
Permissible surface temperature	+300 °C	+200 °C	+135 °C																						
Ambient temperature	-10...+60 °C	-10...+60 °C	-10...+60 °C																						
Restrictions from the device																									
Maximum medium temperature	+230 °C	+185 °C	+125 °C																						
Restrictions from the device																									

2.5. Drinking water

Conformity	Description
	<p>Suitable for use in drinking water applications The materials comply with the assessment principles (UBA) for materials in contact with drinking water (TrinkwasserV).</p> <p>Stainless steel body PF39: Suitable for products with medium temperature up to 85 °C (hot water)</p>


DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024

2.6. Foods and beverages/Hygiene

Conformity	Description
FDA	FDA – Code of Federal Regulations (valid for the variable code PL02) All wetted materials are compliant with the Code of Federal Regulations published by the FDA (Food and Drug Administration, USA) according to the manufacturer's declaration.
	EC Regulation 1935/2004 of the European Parliament and of the Council (valid for the variable code PL01, PL02) All wetted materials are compliant with EC Regulation 1935/2004/EC according to the manufacturer's declaration.

3. Materials

3.1. Bürkert resistApp




Bürkert resistApp – Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

[Start chemical resistance check](#)

3.2. Material specifications




Nr.	Element	Werkstoff
1	Cover	Polyamide (PA)
2	Screw	Stainless steel 1.4301
3	Locking device	Stainless steel 1.4305
4	Handwheel	Polyphenylene sulphide (PPS)
5	Visual position indicator with scale	Polyamide (PA)
6	Spindle seal	PTFE V-rings (filled), with spring compensation
7	Stem	Stainless steel 1.4401 or 1.4404
8	Spindle guide	Stainless steel 1.4404 (316L), PTFE filled
9	Housing seal	Graphite
10	Control cone	1.4571 (optionally hardened)
11	Seat seal (optional)	PTFE or PEEK
12	Valve seat with O-ring	Stainless steel 1.4571, EPDM
13	Valve body	Stainless steel 316L/CF3M

4. Dimensions

4.1. Actuator

Note:

Dimensions in mm




Nominal connection size (pipe)		Handwheel diameter Ø	H1	H2 (locking)
[DN]	[NPS]	[mm]		
15	½	45 (S)	217	224
20	¾	45 (S)	224	230
25	1	45 (S)	228	234
32	1 ¼	110 (M)	296	303
40	1 ½	110 (M)	301	307
50	2	110 (M)	307	313
65	2 ½	160 (L)	361	368
80	3	160 (L)	369	375
100	4	160 (L)	379	385

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | validé) printed: 18.03.2024

4.2. Body with flange connection

Note:

Dimensions in mm



Nominal diameter (port connection)	DIN EN 1092-1 PN 25 FTF 1 according to DIN EN 558-1							JIS 10K FTF 10 according to DIN EN 558-2							
	DN	Ø DF	LF	Ø BF	AF	Ø D	A x α	Ø MF	Ø DF	LF	Ø BF	AF	Ø D	A x α	Ø MF
10	90	130	60	16	14	4 x 90°	13.6	-	-	-	-	-	-	-	-
15	95	130	65	16	14	4 x 90°	18.1	95	108	70	12	15	4 x 90°	18.1	
20	105	150	75	18	14	4 x 90°	23.7	100	117	75	14	15	4 x 90°	23.7	
25	115	160	85	18	14	4 x 90°	29.7	125	127	90	14	19	4 x 90°	29.7	
32	140	180	100	18	18	4 x 90°	38.4	135	140	100	16	19	4 x 90°	38.4	
40	150	200	110	18	18	4 x 90°	44.3	140	165	105	16	19	4 x 90°	44.3	
50	165	230	125	20	18	4 x 90°	56.3	155	203	120	16	19	4 x 90°	56.3	
65	185	290	145	22	18	8 x 45°	66.0	175	216	140	18	19	4 x 90°	71.5	
80	200	310	160	24	18	8 x 45°	81.0	185	241	150	18	19	8 x 45°	84.3	
100	235	350	190	24	22	8 x 45°	100.0	292	292	175	18	19	8 x 45°	109.1	


Nominal diameter (port connection)	ANSI B 16.5 Class 150 FTF 37 according to DIN EN 558-2						
NPS	Ø DF	LF	Ø BF	AF	Ø D	A x α	Ø MF
½	89	184	60.5	11.2	15.7	4 x 90°	15.7
¾	99	184	69.9	12.7	15.7	4 x 90°	20.8
1	108	184	79.2	14.2	15.7	4 x 90°	26.7
1½	127	222	98.6	17.5	15.7	4 x 90°	40.9
2	152	254	120.7	19.1	19.1	4 x 90°	52.6
2½	178	276	139.7	22.3	19.1	4 x 90°	62.7
3	190	298	152.5	23.9	19.1	4 x 90°	78.0
4	229	352	190.5	23.9	19.1	8 x 45°	102.4

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024

4.3. Body with threaded connection

Note:

Dimensions in mm




Nominal diameter (port connection)	G (DIN ISO 228 - 1) NPT (ASME B1.20.1) RC (ISO 7 - 1)					LM	SW
	D	E					
DN	NPS	[G]	[NPT]	[Rc]			
10	3/8	12	10.3	10.1	65	27	
15	1/2	14	13.7	13.2	65	27	
20	3/4	16	14	14.5	75	34	
25	1	18	16.8	16.8	90	41	
32	1 1/4	20	17.3	19.1	110	50	
40	1 1/2	22	17.3	19.1	120	55	
50	2	24	17.6	23.4	150	70	
65	2 1/2	26	23.7	26.7	185	85	
80	3	28	30.5	29.8	205	100	
100	4	32	33	35.8	240	125	

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024

4.4. Body with welded connection

Note:
Dimensions in mm




Nominal diameter (port connection) DN	ES	LS	DIN EN ISO 1127 / ISO 4200 / DIN 11866 series B		DIN 11850-2 / DIN 11866 series A / DIN EN 10357 series A	
			Ø DS	WS	Ø DS	WS
10	20	90	17.2	1.6	13	1.5
15	20	90	21.3	1.6	19	1.5
20	20	100	26.9	1.6	23	1.5
25	26	130	33.7	2.0	29	1.5
32	26	140	42.4	2.0	35	1.5
40	26	150	48.3	2.0	41	1.5
50	26	175	60.3	2.0	53	1.5
65	26	210	76.1	2.3	70	2.0
80	26	230	88.9	2.3	85	2.0
100	26	260	114.3	2.6	104	2.0

Nominal diameter (port connection) NPS	ES	LS	ASME BPE / DIN 11866 series C	
			Ø DS	WS
½	20	90	12.7	1.65
¾	20	90	19.05	1.65
1	20	100	25.4	1.65
1½	26	140	38.1	1.65
2	26	150	50.8	1.65
2½	26	175	63.5	1.65
3	26	210	76.2	1.65
4	26	260	101.6	2.11

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024

4.5. Body with clamp connection

Note:
Dimensions in mm



Nominal diameter (port connection)	DIN 32676 A (Rohr: DIN 11850 - 2)				DIN 32676 B (Rohr: ISO 4200)			
	LC	Ø D2 C	Ø D1 C	SC	LC	Ø D2 C	Ø D1 C	SC
15	126	19	34	1.5	146	21.3	50.5	1.6
20	136	23	34	1.5	136	26.9	50.5	1.6
25	173	29	50.5	1.5	164	33.7	50.5	2.0
40	193	41	50.5	1.5	193	48.3	64.0	2.0
50	218	53	64	1.5	218	60.3	77.5	2.0

Nominal diameter (port connection)	ASME BPE			
NPS	LC	Ø D2 C	Ø D1 C	SC
½	122	12.7	25.0	1.65
¾	126	19.05	25.0	1.65
1	126	25.4	50.5	1.65
1½	172	38.1	50.5	1.65
2	182	50.8	64.0	1.65
2½	231	63.5	77.5	1.65
3	265	76.2	91.0	1.65
4	315	101.6	119.0	2.11


DTS 1000597490 EN Version: A Status: RL (released | freigegeben | validé) printed: 18.03.2024

5. Performance specifications

5.1. Fluidic data

Flow characteristics

- Flow characteristic according to DIN EN 60534-2-4
- K_{VR} value at 5 % of stroke for $DN > 10$ mm
 K_{VR} value at 10 % of stroke for $DN \leq 10$ mm
- K_{VR} value = smallest K_V value, at which the tilt tolerance according to DIN EN 60534-2-4 is still maintained.



Equal percentage flow curve - detailed values please see below

Overview of fluidic data for flow below seat (for liquids, steam and gases)

Note:

- K_V value [m^3/h]: measurement with water according to DIN EN 60534-2-4
- Seat leakage according to DIN EN 60534-4
- Bürkert product filter (see "7.2. Bürkert product filter" on page 17)
- Info: Rules for decimal places implemented according to works standard

Nominal diameter (pipe)		Seat size	Hand-wheel diameter Ø	Operating pressure max. CF A (Seat leakage class)			Theoretical rangeability	K_V value at stroke [m^3/h]											K_{VS} value	
				Seat seal				5%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%		
DN	NPS	[mm]	[bar(g)]	Stainless steel	PTFE	PEEK														
10	¾ ¹⁾	3	45 (S)	25 (II)	-	-	10:1	-	0.005	0.009	0.013	0.019	0.026	0.034	0.044	0.060	0.077	0.098	0.1	
		3	45 (S)	25 (II)			20:1	-	0.009	0.015	0.023	0.033	0.046	0.063	0.085	0.11	0.16	0.22	0.2	
		4	45 (S)	25 (II)			30:1	-	0.023	0.033	0.049	0.070	0.097	0.14	0.18	0.26	0.35	0.49	0.5	
		6	45 (S)	25 (II)	25 (VI)	25 (VI)	50:1	0.005	0.007	0.011	0.045	0.085	0.16	0.26	0.41	0.65	1.1	1.25	1.25	
		8	45 (S)	25 (II)	25 (VI)	25 (VI)		0.060	0.070	0.090	0.12	0.18	0.26	0.42	0.61	0.92	1.5	2.0	2.0	
		10	45 (S)	25 (II)	25 (VI)	25 (VI)		0.090	0.11	0.13	0.19	0.30	0.48	0.73	1.0	1.6	2.3	2.7	2.7	
15	½ ²⁾	3	45 (S)	25 (II)	-	-	10:1	-	0.005	0.009	0.013	0.019	0.026	0.034	0.044	0.060	0.077	0.098	0.1	
		3	45 (S)	25 (II)			20:1	-	0.009	0.015	0.023	0.033	0.046	0.063	0.085	0.11	0.16	0.22	0.2	
		4	45 (S)	25 (II)			30:1	-	0.023	0.033	0.049	0.070	0.097	0.14	0.18	0.26	0.35	0.49	0.5	
		6	45 (S)	25 (II)	25 (VI)	25 (VI)	50:1	0.005	0.007	0.011	0.045	0.085	0.16	0.26	0.41	0.65	1.1	1.25	1.25	
		8	45 (S)	25 (II)	25 (VI)	25 (VI)		0.070	0.080	0.11	0.13	0.19	0.27	0.43	0.63	0.95	1.6	2.1	2.1	
		10	45 (S)	25 (II)	25 (VI)	25 (VI)		0.090	0.11	0.15	0.19	0.31	0.49	0.75	1.1	1.7	2.5	3.1	3.1	
		15	45 (S)	25 (II)	25 (VI)	25 (VI)		0.14	0.17	0.22	0.35	0.52	0.80	1.2	1.8	2.7	3.7	4.3	4.3	
20	¾ ²⁾	10	45 (S)	25 (II)	25 (VI)	25 (VI)	50:1	0.10	0.12	0.15	0.19	0.30	0.46	0.67	1.0	1.5	2.1	2.8	2.8	
		15	45 (S)	25 (II)	25 (VI)	25 (VI)		0.13	0.17	0.21	0.32	0.48	0.71	1.0	1.5	2.3	3.4	4.4	4.4	
		20	45 (S)	25 (II)	25 (VI)	25 (VI)		0.19	0.24	0.29	0.42	0.64	0.97	1.4	2.0	2.9	4.2	5.9	5.9	

1.) Deviation for port connections according to ASME BPE: the next largest Nominal diameter (port connection) is used, e.g. NPS 1 instead of NPS ¾.

2.) According to the Pressure Equipment Directive 97/23/EC for compressible fluids of Group 1 (hazardous gases and vapours according to Article 3 No. 1.3 letter a first dash)

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024


Nominal diameter (pipe)		Seat size	Hand-wheel diameter Ø	Operating pressure max. CF A (Seat leakage class)			Theoretical range-ability	K _v value at stroke [m³/h]											K _{vs} value
				Seat seal				5%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	
DN	NPS	[mm]	[bar(g)]	Stain-less steel	PTFE	PEEK													
25	1	3	45 (S)	25 (II)	-	-	10:1	-	0.005	0.009	0.013	0.019	0.026	0.034	0.044	0.060	0.077	0.098	0.1
		3	45 (S)	25 (II)	-	-	20:1	-	0.009	0.015	0.023	0.033	0.046	0.063	0.085	0.11	0.16	0.22	0.2
		4	45 (S)	25 (II)	-	-	30:1	-	0.023	0.033	0.049	0.070	0.097	0.14	0.18	0.26	0.35	0.49	0.5
		6	45 (S)	25 (II)	25 (VI)	25 (VI)	50:1	0.005	0.007	0.011	0.045	0.085	0.16	0.26	0.41	0.65	1.1	1.25	1.25
		8	45 (S)	25 (II)	25 (VI)	25 (VI)	0.070	0.080	0.11	0.13	0.19	0.27	0.43	0.63	0.95	1.6	1.8	1.8	
		10	45 (S)	25 (II)	25 (VI)	25 (VI)	0.10	0.12	0.15	0.19	0.30	0.46	0.67	1.0	1.5	2.1	2.8	2.8	
		15	45 (S)	25 (II)	25 (VI)	25 (VI)	0.13	0.17	0.21	0.33	0.48	0.72	1.1	1.5	2.4	3.5	4.6	4.6	
		20	45 (S)	25 (II)	25 (VI)	25 (VI)	0.19	0.24	0.30	0.44	0.64	0.98	1.4	2.1	3.2	4.5	6.1	6.1	
32	1 ¼ ²⁾	20	110 (M)	25 (II)	25 (VI)	25 (VI)	0.33	0.38	0.62	0.94	1.4	2.0	3.0	4.4	6.1	8.1	10.4	10.4	
		25	110 (M)	25 (II)	25 (VI)	25 (VI)	0.22	0.25	0.35	0.50	0.70	1.1	1.6	2.5	3.8	5.8	8.0	8.0	
		32	110 (M)	25 (II)	25 (VI)	25 (VI)	0.40	0.47	0.73	1.1	1.6	2.5	3.7	5.4	7.5	10.3	13.0	13.0	
40	1 ½ ²⁾	25	110 (M)	25 (II)	25 (VI)	25 (VI)	0.48	0.60	0.85	1.3	2.1	3.1	4.5	6.8	10.2	14.0	17.8	17.8	
		32	110 (M)	25 (II)	25 (VI)	25 (VI)	0.40	0.50	0.75	1.1	1.7	2.6	3.8	5.6	8.0	10.7	13.6	13.6	
		40	110 (M)	25 (II)	25 (VI)	25 (VI)	0.48	0.60	0.85	1.3	2.1	3.2	4.6	6.9	11.0	15.0	20.0	20.0	
50	2 ²⁾	20	110 (M)	25 (II) ¹⁾	-	-	-	0.60	0.70	1.1	1.7	2.7	4.0	6.0	9.2	13.8	18.2	23.8	23.8
		32	110 (M)	25 (II) ¹⁾	-	-	0.24	0.31	0.51	0.76	1.1	1.7	2.5	3.6	5.3	7.9	11.8	12.0	
		32	110 (M)	25 (II) ¹⁾	25 (VI) ¹⁾	25 (VI) ¹⁾	0.48	0.60	0.90	1.3	2.1	3.2	4.6	6.9	11.6	16.0	21.0	21.0	
		40	110 (M)	25 (II) ¹⁾	25 (VI) ¹⁾	25 (VI) ¹⁾	0.60	0.70	1.0	1.7	2.6	4.0	5.9	9.2	14.0	18.9	24.5	24.5	
		50	110 (M)	25 (II) ¹⁾	25 (VI) ¹⁾	20 (VI) ¹⁾	0.90	1.1	1.9	2.9	4.5	6.8	10.5	15.5	22.0	29.5	37.0	37.0	
65	2 ½ ²⁾	40	160 (L)	25 (II) ¹⁾	25 (VI) ¹⁾	25 (IV) ¹⁾	0.65	0.75	1.1	1.8	2.8	4.3	6.5	10.4	16.0	22.0	29.0	29.0	
		50	160 (L)	25 (II) ¹⁾	25 (VI) ¹⁾	20 (VI) ¹⁾	1.0	1.2	2.0	3.1	4.8	6.7	9.7	16.0	24.0	35.0	45.0	45.0	
		65	160 (L)	24 (II) ¹⁾	24 (VI) ¹⁾	14 (VI)	1.6	2.0	3.0	5.0	8.0	13.5	22.0	33.0	45.0	56	65	65	
80	3 ²⁾	50	160 (L)	25 (II) ¹⁾	25 (VI) ¹⁾	20 (VI) ¹⁾	1.0	1.2	2.0	3.4	5.3	8.3	13.0	19.0	26.0	35.0	45.0	45.0	
		65	160 (L)	24 (II) ¹⁾	24 (VI) ¹⁾	14 (12.5*) (VI)	1.6	2.0	2.9	5.0	8.2	13.0	22.0	35.0	48.0	61	73	73	
		80	160 (L)	16 (II) ¹⁾	16 (VI) ¹⁾	10 (VI)	2.5	3.4	6.3	10.7	16.0	27.0	42.5	58	73	87	100	100	
100	4	65	160 (L)	24 (II) ¹⁾	24 (VI) ¹⁾	14 (VI) ¹⁾	1.4	1.8	2.8	5.0	8.8	15.0	25.0	37.0	50	64	77	77	
		80	160 (L)	16 (II) ¹⁾	16 (VI) ¹⁾	10 (VI)	2.2	3.1	5.9	10.3	17.5	30.0	48.0	66	82	97	110	110	
		100	160 (L)	10 (II)	10 (VI)	6 (VI)	3.8	5.2	9.5	15.0	26.0	46.5	68	90	111	128	140	140	

1.) According to the Pressure Equipment Directive 97/23/EC for compressible fluids of Group 1 (hazardous gases and vapours according to Article 3 No. 1.3 letter a first dash)
 2.) Deviation for port connections according to ASME BPE: the next largest Nominal diameter (port connection) is used, e.g. NPS 1 instead of NPS ¾.

5.2. Operating limits

Operating limits for medium temperature and operating pressure

The operating range of Bürkert process valves is in addition to the maximum operating pressures limited by the nominal pressure according to the relevant standard.



- Operating limits for PN25 according to DIN EN 12516-1
- Operating limits for flange 10K according to JIS B 2220
- Operating limits for Class 150 according to ASME B16.34
- Saturated steam curve for water

Operating limits for seat seal

Tight sealing required	Leakage class (DIN EN 60534 - 4)	Medium temperature	Seat seal
No An additional shut-off valve is recommended	III/IV (metal seals) Metal-sealed valves have larger leakages (0.1 % or 0.01 % of the nominal flow rate are permissible). Metallic seals are impervious even under demanding process conditions.	-40...+230 °C	Stainless steel
Yes An additional shut-off valve is often unnecessary.	VI (soft seals) By using plastics as sealing material, the control valves can close tightly. Their use is not recommended in cases of increased erosion due to demanding process conditions.	-40...+130 °C (recommended for ≤ +130 °C)	PTFE
		-10...+230 °C (recommended for > +130 °C)	PEEK

Operating limits for optional versions

High-temperature version

Thanks to an adaption of the spindle seal, this version is suitable for applications with steam, neutral gases and other heat transfer mediums up to +230 °C.

Water version

For applications with water up to +200 °C, a special configuration of the spindle seal increases service life significantly. It is recommended for water temperatures starting at +85 °C.

Drinking water version

Wetted materials are tested in contact with the medium are tested for suitability with drinking water up to +85 °C.

Low-temperature version

Suitable for minimum medium temperatures down to -40 °C

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | validé) printed: 18.03.2024

6. Product design and assembly

6.1. Product features

Note

More detailed information can be found in the **operating instructions Type 2961** ▶.

<p>Position indicator</p> <p>When turning the handwheel counterclockwise, the reproducible stroke scale becomes visible between the attachment and the handwheel visible.</p> <p>The scale on the handwheel, together with the stroke scale, enables reproducible adjustment of the flow rate.</p>	<p>Handwheel with scale</p> <p>Reproducible stroke scale</p>
<p>Interlock (optional)</p> <p>The valve can be secured against unintentional or unauthorized operation.</p> <p>For this purpose, a securing pin can be pressed down and turned.</p> <p>The locking pin has a hole (Ø 3.8) and can be secured with a padlock.</p>	<p>Lock pin</p> <p>Closed position</p> <p>Open position</p>
<p>Stroke limitation (optional)</p> <p>Both the minimum and the maximum position of the valve can be adjusted via an adjustment sleeve. The handwheel can be removed for this purpose.</p>	<p>Screw on handwheel</p> <p>Square</p> <p>Adjusting sleeve</p>

DTS 1000597490 EN Version: A Status: RL (released | freigegeben | valide) printed: 18.03.2024

7. Ordering information

7.1. Bürkert eShop




Bürkert eShop – Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

7.2. Bürkert product filter



Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

7.3. Bürkert Product Enquiry Form

Note:

Please see our Product Enquiry Form for a full explanation of our specification key.



Bürkert Product Enquiry Form – Your enquiry quickly and compactly

Would you like to make a specific product enquiry based on your technical requirements? Use our Product Enquiry Form for this purpose. There you will find all the relevant information for your Bürkert contact. This will enable us to provide you with the best possible advice.

[Fill out the form now](#)