







- No obstacles inside the measuring tube, compact, lightweight and low energy consumption
- Conforms to hygienic requirements, CIP/SIP compatible
- Ideal for liquids with low or no conductivity
- Digital communication, parameterisation via Communicator, display
- Optional: ATEX/IECEx certification, II 3G/D



Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

overview



Type 8802 **ELEMENT** continuous control valve systems -



Type 8619 multiCELL - Multi-channel and multi-function transmitter/controller



Type 8647 AirLINE SP - electropneumatic automation system



Type ME43 Fieldbus gateway

Type description

The Type 8098 flowmeter is part of the FLOWave product range. It is based on SAW (Surface Acoustic Waves) technology and is mainly designed for applications with the highest hygienic demands. This is achieved by using suitable stainless steel materials, a measuring tube completely free of any internal parts and an ideal outer hygienic design.

FLOWave offers a range of integrated functions including the advantages of flexibility, ease of cleaning, compact dimensions, lightweight, easy installation and handling, and is compliant with numerous standards.

Optimal measurement results can be achieved with homogeneous liquids, free of air and solid particles. For liquids with high viscosity, an integrated viscosity compensation can be activated. Gas and steam cannot be measured; however, their flow does not have any negative effect on the device or its operation and other liquids flowing through afterwards are measured correctly as before.

Beside volume flow, a density measurement optional feature is available. With this option, the mass flow is calculated based on volume flow and density measurements.

Special functions derived from further process values (differentiation factor (DF), acoustic transmission factor) offer additional information about the particular liquid in use (for details, see chapter "7.2. Special functions" on page 29).



Table of contents

1.	Gene	eral technical data	4
	1.1.	About the device	4
	1.2.	All variants	
	1.3.	FLOWave L flowmeter	
	1.0.	With or without industrial communication	
		With industrial communication (Ethernet variant)	
	1.4.	FLOWave S flowmeter	
	1.4.	1 LOWave o Howhieler	12
2.	Appr	rovals and conformities	13
	2.1.	General notes	13
	2.2.	Conformity	13
	2.3.	Standards	13
	2.4.	Pressure Equipment Directive (PED)	14
		Device used on a pipe	
	2.5.	Explosion protection	
	2.6.	North America (USA/Canada)	
	2.7.	Foods and beverages/Hygiene	
	2.8.	Others	
	2.0.	Network protocol	
3.	Mate	erials	15
	0.1	Düdinik analist Anna	45
	3.1.	Bürkert resistApp	
	3.2.	Material specifications	
		FLOWave L flowmeter without industrial communication	
		FLOWave L flowmeter with industrial communication	
		FLOWave S flowmeter	18
4.	Dime	ensions	19
	4.1.	Transmitter of the FLOWave L flowmeter without industrial communication	19
	4.2.	Transmitter of the FLOWave L flowmeter with industrial communication (Ethernet variant)	19
	4.3.	Transmitter of the FLOWave S flowmeter	19
	4.4.	Flowmeter with clamp connections	
	4.5.	Flowmeter with aseptic collar flange connections (BF)	
	4.6.	Flowmeter with aseptic collar clamp connections (BKS)	
	4.7.	Flowmeter with thread connections	
5.	Perf	ormance specifications	24
0.		·	
	5.1.	Medium temperature diagram	
	5.2. 5.3.	Measurement deviation table	
6.	Prod	luct installation	26
	6.1.	Installation notes	26
	6.2.	Selection of the nominal diameter	26
	6.3.	Mounting options	27
		FLOWave L flowmeter	27
		FLOWave S flowmeter	27
7.	Prod	luct operation	28
	7.1.	Measuring principle	28
	7.2.	Special functions	
8.	Prod	luct design and assembly	29



	8.1.	Product assembly	29
9.	Prod	uct accessories	30
10.	Orde	ering information	30
	10.1.	Bürkert eShop	30
	10.2.	Recommendation regarding product selection	31
	10.3.	Bürkert product filter	
	10.4.	Bürkert Product Enquiry Form	32
	10.5.	Bürkert 3D Model	32
	10.6.	Ordering chart FLOWave L flowmeter with or without industrial communication	32
		Clamp connection acc. to DIN 32676 series A for pipe acc. to DIN 11866 series A (DIN 11850)	32
		Clamp connection acc. to DIN 32676 series B for pipe acc. to DIN 11866 series B (ISO 1127)	33
		Clamp connection acc. to DIN 32676 series C for pipe acc. to DIN 11866 series C (ASME BPE)	34
		Thread connection acc. to DIN 11851 series A for pipe acc. to DIN 11866 series A (DIN 11850)	35
	10.7.	Ordering chart FLOWave S flowmeter	36
		Clamp connection acc. to DIN 32676 series A for pipe acc. to DIN 11866 series A (DIN 11850)	36
		Clamp connection acc. to DIN 32676 series B for pipe acc. to DIN 11866 series B (ISO 1127)	
		Clamp connection acc. to DIN 32676 series C for pipe acc. to DIN 11866 series C (ASME BPE)	
		Thread connection acc. to DIN 11851 series A for pipe acc. to DIN 11866 series A (DIN 11850)	
	10.8	Ordering chart accessories	



1. General technical data

1.1. About the device

The flowmeter Type 8098 consists of:

• either a flow sensor Type S097 and a FLOWave L transmitter (variant FLOWave L flowmeter), which is available with or without industrial communication (the FLOWave L variant with industrial communication, recognisable by the two M12 female connectors and the M12 male connector, is called the Ethernet variant.)



or a flow sensor Type S097 and a FLOWave S transmitter (variant FLOWave S flowmeter)



1.2. All variants

Note:

- The following data applies to all variants mentioned above.
- In the following table, the term "full scale" refers to full scale of volume flow rate, i.e. the flow rate corresponding to 10 m/s flow velocity.

Product properties

Material

Make sure the device materials are compatible with the fluid you are using. Further information can be found in chapter "3.1. Bürkert resistApp" on page 15.

Further information on the materials can be found in chapter "3.2. Material specifications" on page 16.

Non wetted parts

For sensor with process connection size ≤ DN 50/2": stainless steel 304/1.4301
 For sensor with process connection size > DN 50/2": stainless steel 316L/1.4435

Wetted parts

Measurement tube and process Stainless steel 316L/1.4435 with low delta ferrite content connection

Surface quality

Measurement tube (inner surface)• Ra < 0.8 μm (30 μin.) or</th>• Ra < 0.4 μm (15 μin.) (electro-polished) according to ISO 4288</td>DimensionsFurther information can be found in chapter "4. Dimensions" on page 19.Measuring elementInterdigital transducersMeasuring principleBased on SAW (Surface Acoustic Waves)

Measuring range

Volume flow rate measurement 0...1.7 m³/h up to 0...200 m³/h

Further information can be found in chapter "10.6. Ordering chart FLOWave L flowmeter with or without industrial communication" on page 32 or "10.7. Ordering chart FLOWave S flowmeter" on page 36.

Density measurement 1.) 0.8...1.3 g/cm³ (inactive by default, selectable upon request)

Mass flow rate measurement 1.) 0...1 360 kg/h up to 0...260 000 kg/h (inactive by default, selectable upon request)

Temperature measurement -20...+140 °C (-4...+284 °F)

Visit product website ▶ 4 | 40



scale)

Special function	Active by default, deselectable upon request.
	ATF: acoustic transmission factor
	DF: differentiation factor
	Further information can be found in chapter "7.2. Special functions" on page 29.

Performance data

Volume flow rate measurement

Under reference conditions i.e. measuring fluid = water free from gas bubbles and solids, ambient and water temperature = 23 °C ±1 °C (73.4 °F ± 1.8 F), and short refresh time, while maintaining turbulent or laminar flow profile, with the minimum inlet (40 x DN) and outlet (1 x DN) distances and the appropriate internal diameter of the pipes. Deviation from reference conditions can be adjusted through the use of a built-in correction K factor adjustment or Teach-in Procedure.

Density measurement	As an option 1.)
Refresh time	Selectable between very short, short and long Further information can be found in chapter "5.3. Refresh time table" on page 25.
	 From 1 % of full scale up to 10 % of full scale: ±0.04 % of full scale
Repeatability	Further information can be found in chapter "5.2. Measurement deviation table" on page 25. • From 10 % of full scale up to full scale: ±0.2 % of the measured value
	 From 1 % of full scale up to 10 % of full scale: ±0.08 % of full scale
Measurement deviation	 From 10 % of full scale up to full scale: ±0.4 % of the measured value

Density measurement

Under reference conditions i.e. measuring fluid = water free from gas bubbles and solids, ambient and water temperature = 23 °C ±1 °C (73.4 °F ± 1.8 F). Deviations from reference conditions, especially exposure of the device to temperatures above 90 °C can be adjusted through the use of a built in adjustment procedure (see user manual Type 8098.

through the use of a built in adj	justment procedure (see user manual Type 8098).
Measurement deviation	 Standard product adjustment: ±2% of the measured value
	 After Teach-In: ±1% of the measured value (at teach-in density value)
Repeatability	±1% of the measured value
Refresh time	Selectable between very short, short and long
	Further information can be found in chapter "5.3. Refresh time table" on page 25.

Mass flow rate measurement As an option 1.)

Refresh time

Under reference conditions i.e. measuring fluid = water free from gas bubbles and solids, ambient and water temperature = 23 °C ±1 °C (73.4 °F ±1.8 F), and short refresh time, while maintaining turbulent or laminar flow profile, with the minimum inlet (40 x DN) and outlet (1 x DN) distances and the appropriate internal diameter of the pipes. Deviation from reference conditions, can be adjusted through the

use of a built-in correction K f	actor adjustment or Teach-in Procedure.
Measurement deviation	Standard K-factor:
	 From 10 % of full scale up to full scale: ±2.4 % of the measured value
	- From 1 % of full scale up to 10 % of full scale: \pm (2 % of the measured value + 0.08 % of full scale)
	After Teach-In:
	 From 10 % of full scale up to full scale: ±1.4 % of the measured value at teach-in density and mass flow rate values
	 From 1% of full scale up to 10% of full scale: ±(1% of the measured value +0.08% of full scale) at teach-in density and mass flow rate values
	Further information can be found in chapter "5.2. Measurement deviation table" on page 25.
Repeatability	 From 10 % of full scale up to full scale: ±1.2 % of the measured value

Repeatability	•	From 10 % of full scale up to full scale: \pm 1.2 % of the measured value
	•	From 1 % of full scale up to 10 % of full scale: \pm (1 % of the measured value \pm 0.04 % of full scale

Selectable between very short, short and long Further information can be found in chapter "5.3. Refresh time table" on page 25.

Temperature measurement	
Measurement deviation	• For T° ≤ 100 °C (+212 °F): ±1 °C (+1.8 °F)
	• For 100 °C (+212 °F) < T° <140 °C (+284 °F): ±1.5 %
Refresh time	Approx. 0.1 s
Electrical data	
Operating voltage	1235 V DC filtered and regulated
	• Tolerance: ±10 %
	 Connection to main supply: permanent (through external SELV (Safety Extra Low Voltage) and LPS (Limited Power Source) power supply)
Power source (not supplied)	Limited power source according to UL/EN 62368-1 standards or limited energy circuit according to UL/EN 61010-1 §9.4
DC reverse polarity protection	Yes

5 | 40 Visit product website



Voltage supply cable							
For cable gland	• 0.21.5 mm ² d	ross-section					
-	In nickel plated	brass:					
	 Cable with r 	naximum operating temp	erature greater than +80 °C	C (+176 °F)			
		iameter, shielded cable	9. January 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1.	(
	In stainless ste						
			overture eventor than 1 00 %	2 (. 176 °F)			
			erature greater than +80 °C	5 (+ 176 °F)			
For F. nin M10 male connector		iameter, shielded cable	ture avector than 100 °C (176 °F\			
For 5-pin M12 male connector (A-coded)			ture greater than +80 °C (+	- 176 ⁻ F)			
(1.0000)		meter, shielded cable,					
5 4 : MOC 1			-pin M12 female connector				
For 4-pin M12 female connector (D-coded)			ture greater than +80 °C (+				
<u> </u>	• 5e / CAT-5 min	category, 100 m max. le	ength, shielded conductor v	vith minimum STP			
Medium data	Non dongorous li	vida aamaliina viith arti	ala 4 81 af 2014/69/EU dir	active. Fruther information can be			
Fluid			nt Directive (PED)" on pag	ective. Further information can be le 14.			
			or a fluid with a sound veloc				
	• between 1000	m/s and 2000 m/s for pro	ocess connection DN 08, 36	" and ½"			
	between 800 m	s and 2300 m/s for proc	cess connection DN ≥15 or	≥ ³ / ₄ "			
Fluid temperature		` '	num fluid temperature can	be restricted by the ambient			
	operating temp	erature.					
	• Max. conditions for sterilisation process: up to +140 °C (+284 °F) (+130 °C (+266 °F) for ATEX/						
	 IECEx variant) for max. 60 min Maximum temperature gradient: 10 °C/s (18 °F/s) (measured by the integrated sensor on the device) 						
Fluid pressure (max.)	· Waximan temp	oratare gradient. To O/o	(10 170) (incusared by the	integrated seriour on the device,			
DN / Pipe standard	DIN 11850	ISO 1127	ASME BPE	SMS 3008			
DN 08, %", ½"	PN 25	PN 25	PN 25	_			
DN 15, 3/4", DN 25, 1", 11/2"	PN 25	PN 25	PN 25	PN 25			
DN 40	PN 25	PN 16	-	PN 25			
DN 50, 2"	PN 16	PN 16	PN 16	PN 16			
DN 65, 2½", DN 80, 3"	PN 10	PN 10	PN 10	-			
Process/Pipe connection & con							
Process connection size / pipe	size 3.) according to)					
DIN 32676 series A / DIN 11850		l 15, DN 25, DN 40, DN 5					
DIN 32676 series B / ISO 1127		l 15, DN 25, DN 40, DN 5					
DIN 32676 series C / ASME BPE		", 1", 1½", 2", 2½" and 3		DN 00			
DIN 11864-2 form A series A / DIN 11850	Aseptic collar flan	ge (BF)**/: DIN 15, DIN 25,	DN 40, DN 50, DN 65 and	DN 80			
DIN 11864-2 form A series B / ISO 1127	Aseptic collar flan	ge (BF) ^{4.)} : DN 08, DN 15,	DN 25, DN 40, DN 50, DN	65 and DN 80			
DIN 11864-2 form A series C / ASME BPE	Aseptic collar flan	ge (BF) ^{4.)} : ½", ¾", 1", 1½	" and 2"				
DIN 11864-3 form A series A / DIN 11850	Aseptic collar clar	np ferrule (BKS) ^{4.)} : DN 15	i, DN 25, DN 40 and DN 50				
DIN 11864-3 form A series B / ISO 1127	Aseptic collar clar	np ferrule (BKS) ^{4.)} : DN 08	s, DN 15, DN 25, DN 40 and	I DN 50			
DIN 11864-3 form A series C / ASME BPE	/ Aseptic collar clamp ferrule (BKS) ^{4.} : ½", ¾", 1", 1½" and 2"						
ASIVIL DEL							
SMS 3017 / SMS 3008	Clamp: DN 25, DN	l 40 and DN 50					
	Thread: DN 65 an						

Visit product website ▶ 6 | 40



Approvals and conformities	
• •	
Directives CE directive	Further information on the CE Directive can be found in chapter "2.3. Standards" on page 13.
Pressure equipment directive	 Complying with article 4, paragraph 1 of 2014/68/EU directive Further information on the pressure equipment directive can be found in chapter "2.4. Pressure Equipment Directive (PED)" on page 14.
	- CRN 0C21751 declaration ^{5,)}
Explosion protection	On request: ATEX/IECEx
North America (USA/Canada)	On request: UL Listed for the USA and Canada
Foods and beverages/Hygiene	• 3-A (28-06) Sanitary Standards Inc.
	EHEDG (Type EL CLASS I) ^{6.)}
	FDA declaration of conformity
	On request:
	- USP class VI declaration
	- ECR1935/2004 declaration
Materials	Inspection certificate 3.1
	Certification of compliance ASME BPE
	On request:
	 Certification of conformity for the surface quality DIN 4762, EN ISO 4287, EN ISO 4288
	Certification of conformity for passivation and electro-polishing processes
Others	Fluidic test report (test regarding volumetric flow rate or volume and mass flow rates, if density and mass flow rate option chosen)
	On request:
	 Calibration certificate (volumetric flow rate, volume and mass flow rates and density)
	- Test report 2.2
	MTBF (Mean Time Between Failures) manufacturer declaration
Environment and installation	WITE (Weat Time Detween Fallaces) manuacturer decidration
Ambient temperature	 Operation: depends on the fluid temperature. Further information can be found in chapter "5.1. Medium temperature diagram" on page 24.
	• Storage: -20+70 °C (-4+158 °F)
Relative air humidity	≤85 %, without condensation
Height above sea level	Max. 2000 m
Operating condition	Continuous
Equipment mobility	Fixed device
Application range	Indoor and outdoor Protect the device against electromagnetic interference, ultraviolet rays and, when installed outdoors, against the effects of climatic conditions.
Degree of protection 7.)	IP65, IP67 (according to IEC/EN 60529), NEMA 4X (according to NEMA250), if the product is wired and if the cable glands are tightened and the covers are screwed tight. Unused cable glands must be sealed with the stopper gaskets provided (mounted upon delivery of the product). An unused M12 fixed connector must be protected by the screwed plug.
Installation category	Category I according to UL/EN 61010-1

- 1.) Only for a flowmeter with a process connection size of DN 08...DN 80 or $10^{12}\,\mathrm{m}...3^{11}$
- 2.) Customer specific setting on request. Contact your Bürkert sales office.
- 3.) See dimension tables of the sensor in chapters "4.4. Flowmeter with clamp connections" on page 20, "4.5. Flowmeter with aseptic collar flange connections (BF)" on page 22, "4.6. Flowmeter with aseptic collar clamp connections (BKS)" on page 23, and "4.7. Flowmeter with thread connections" on page 24.
- 4.) In German: BF = Bundflansch, BKS= Bundklemmstutzen
- 5.) Only for a flowmeter with a process connection size of $\%"\dots2",$ pending for the other sizes.
- 6.) The EHEDG compliance for :

Pollution degree

• clamp connection according to DIN 32676 is only valid if used in combination with EHEDG-compliant gaskets from Combifit International B.V.

Degree 2 according to UL/EN 61010-1

- threaded connection according to DIN 11851 is only valid if used in combination with EHEDG-compliant gaskets from
 - 1. Kieselmann GmbH, Germany (ASEPTO-STAR k-flex upgrade gaskets) or
- 2. Siersema Komponenten Service (S.K.S.) B.V. (Netherlands SKS gasket set DIN 11851 EHEDG with EPDM or FKM inner gasket).
- 7.) Not evaluated by UL, only IP64 is evaluated by the ATEX notified body and by the IECEx certified body.

7 | 40



1.3. FLOWave L flowmeter

The FLOWave L flowmeter is available in four variants of the transmitter:

- Stainless steel transmitter with nickel plated brass cable glands and M12 male connector
- · Stainless steel transmitter with stainless steel cable glands and M12 male connector (full stainless steel variant)
- Stainless steel transmitter with stainless steel M12 female and male connectors and industrial communication (Ethernet variant)
- Stainless steel transmitter with stainless steel cable glands and M12 male connector (ATEX/IECEx variant).



With or without industrial communication

The following data applies to all variants (unless otherwise stated).

Product properties

Material

Further information on the materials can be found in chapter "3.2. Material specifications" on page 16.

Non wetted parts

Blind cover Stainless steel 304/1.4301 Transmitter housing Stainless steel 304/1.4301

Functional earth element Cylinder screw, washer, washer spring in stainless steel A4 and blind rivet nut in stainless steel 1.4578/

Diaphragm in ePTFE (expanded polytetrafluoroethylene), O-ring in silicone 60 Shore A, body in Pressure compensating element

stainless steel

Display module Float glass, stainless steel 304/1.4301 and EPDM (ethylene propylene diene monomer) seal

Seal

VMQ silicone (Methyl Vinyl Silicone) M12 fixed connector and • 4-pin M12 female connector:

screwed plug

Body in stainless steel 304L/1.4307, contact support in PBT GF30 (Polybutyleneterephthalate

30 % glass fibre reinforced) and seal in EPDM

• 5-pin M12 male connector:

- Body in nickel plated brass and seal in NBR (nitrile butadiene rubber) or

- Body in stainless steel 316L/1.4404 and seal in NBR or VMQ silicone

Cable gland · Body in nickel plated brass and seal in TPE (thermoplastic elastomer) or

· Languages: German, English, French

• Body in stainless steel 304L/1.4307 and seal in TPE (FDA-compliant) or

Body in stainless steel 316L/1.4404 and seal in EPDM

Blind plug Black POM (polyoxymethylene), PA6 or PA

Display • 2.4", monochrome graphic (240 × 160 pixels)

Weight (approx. in kg)	DN 08, 3%", ½"	DN 15, 3/4"	DN 25, 1"	DN 40, 1½"	DN 50, 2"	DN 65, 2½"	DN 80, 3"	
Clamp	2.1	2	2.2	3	3.2	5.4	5.5	
Flange	2.3	2.4	2.7	3.6	3.8	6	6.2	
Thread (dairy thread)	_	_	_	_	_	5.7	6.1	

moda (aan ja moda)		0	0
Performance data			
Frequency resolution	0.05 Hz over 02 000 Hz range		
420 mA output uncertainty	±0.04 mA		
420 mA output resolution	0.8 μΑ		

8 | 40 Visit product website



Electrical data								
Power consumption	Without any consumption of output							
	 For device with 2xM20x1.5 cable glands and 1x5-pin M12 male connector: max. 5 W 							
	 For device with 2×4-pin M12 female connectors and 1×5-pin M12 male connector, Ethernet variant: max. 8 W 							
	 For device with 2×4-pin M12 female connectors and 1×5-pin M12 male connector, Ethernet variant, with display module: max. 9 W 							
Output	Valid for non-Ethernet variants only							
Number of outputs	3 (1 digital, 1 analogue and 1 configurable: digital or analogue)							
Digital output	Overload information (through software diagnostics function) Transistor:							
	 Type: NPN or PNP (wiring dependent), open collector, galvanically isolated 							
	 Operating modes: pulse (by default), On/Off, threshold, frequency (user configurable) 							
	 10 kHz, 535 V DC, max. 700 mA, max. pulse duration: 2 s, selectable limits: 							
	 0.000110 000 pulses/litre or 0.00019 999.99 litres/pulse 							
	- 0.000110 000 pulses/kg or 0.00019 999.99 kg/pulse ^{1.)}							
	Protected against polarity reversals of DC and overloads							
Analogue output	Open loop detection (through software diagnostics function) Current:							
	• 420 mA							
	• 3.6 mA or 22 mA to indicate an error (only if 420 mA scale selected); galvanically isolated							
	• Max. loop impedance: 1 300 Ω at 35 V DC, 1 000 Ω at 30 V DC, 700 Ω at 24 V DC, 450 Ω at 18 V DC							
Process/Pipe connection 8	& communication							
Electrical connection	2xM20x1.5 cable glands and 1x5-pin M12 male connector (A-coded) for non-Ethernet variants only							
Data transfer	External communication through büS (Bürkert system bus, CANopen protocol)							
Environment and installation	on							
Ambient temperature	Operation:							
	 For device with 2x M20 x 1.5 cable glands and 1 x 5-pin M12 male connector: 							
	 10+70 °C (+14+158 °F) or -10+40 °C (+14+104 °F) for ATEX/IECEx variant, if -20 °C (4 °F) ≤ fluid temperature ≤80 °C (176 °F), 							
	 At a fluid temperature >80 °C (176 °F), the maximum ambient temperature decreases linearly from 70 °C (158 °F) up to 40 °C (104 °F) or from 40 °C (104 °F) up to 30 °C (86 °F) for ATEX/ IECEx variant. 							
	This means that at a fluid temperature of 80 °C (176 °F) the ambient temperature may be a maximum of 70 °C and at a fluid temperature of 140 °C (130 °C for the ATEX/IECEx variant) the ambient temperature may only be a maximum of 40 °C (30 °C for the ATEX/IECEx variant).							
	 For device with 2×4-pin M12 female connectors and 1×5-pin M12 male connector, Ethernet variant: -10+55 °C (+14+131 °F) 							

^{1.)} Only if option density and mass flow is activated.

Visit product website ▶ 9 | 40

Further information can be found in chapter "5.1. Medium temperature diagram" on page 24.



With industrial communication (Ethernet variant)

Process/Pipe connection & cor	nmunication						
Electrical connection	2×4-pin M12 female connectors (D-coded) and 1×5-pin M12 male connector (A-coded)						
Industrial Communication							
Supported network protocol	Modbus TCP						
	PROFINET						
	EtherNet/IP						
	• EtherCAT						
Light-emitting diode	2 Link/Act LEDs (green)						
Light childing diode	2 Link LEDs (green) 2 Link LEDs (yellow)						
Madhua TOD anata aal	2 Link LLDs (yellow)						
Modbus TCP protocol Protocol	Internet protocol, varion 4 (IDv4)						
Network topology	Internet protocol, version 4 (IPv4) • Tree						
Network topology							
	• Star						
ID and the contract	Line (open daisy chain) Olatic ID address						
IP configuration	Static IP address						
Turner in the control of	Not supported: BOOTP (Bootstrap Protocol), DHCP (Dynamic Host Configuration)						
Transmission speed	10 or 100 MBit/s						
PROFINET protocol							
PROFINET IO specification	V2.3						
Network topology	• Tree						
	• Star						
	Ring (closed daisy chain)						
	Line (open daisy chain)						
Network management	LLDP (Link Layer Discovery Protocol)						
	SNMP V1 (Simple Network Management Protocol)						
	MIB (Management Information Base)						
P configuration	DCP (Discovery and Configuration Protocol)						
	Manual (Device naming and IP setting)						
Transmission speed	100 MBit/s full duplex						
Maximum supported conform- ance class	CC-B						
Media Redundancy (for ring topology)	MRP client is supported						
GSDml file	See Device Description Files Type 8098 ▶ on the website under "Software".						
EtherNet/IP protocol							
Protocol	Internet protocol, version 4 (IPv4)						
Network topology	• Tree						
	• Star						
	Ring (closed daisy chain)						
	Line (open daisy chain)						
	Linear (open Daisy Chain)						
P configuration	Static IP address						
3	BOOTP (Bootstrap Protocol)						
	DHCP (Dynamic Host Configuration Protocol)						
Transmission speed	10 or 100 MBit/s						
Duplex mode	Half duplex, full duplex, auto-negotiation						
MDI mode (Medium Dependant Interface)	Auto-MDIX						
Predefined standard objects	Identity, Message Router, Assembly, Connection Manager, DLR, QoS, TCP/IP Interface, EtherNet Link object						
EDS file	See Device Description Files Type 8098 on the website under "Software".						

Visit product website

10 | 40



EtherCAT protocol 1.)

Industrial Ethernet interface X1,

X1: EtherCAT IN, X2: EtherCAT OUT

Maximum number of cyclic

input/output data

512 bytes in total

Maximum number of cyclic input 1024 bytes

Maximum number of cyclic

output data

1024 bytes

Acyclic communication (CoE) • SDO

• SDO master-slave

• SDO slave-slave (depends on master capacity)

Complex slave Type

Fieldbus Memory Management

Unit (FMMU)

8

Sync Manager

4

Transmission speed

100 Mbit/s

Approvals and Certificates

Certification

 PROFINET • EtherNet/IP

^{1.)} EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH.



1.4. FLOWave S flowmeter

The FLOWave S flowmeter is available in four variants of the transmitter:

- · Stainless steel transmitter without output and with stainless steel 5-pin M12 male connector
- Stainless steel transmitter with 2 configurable outputs (DO/AO) and stainless steel 8-pin M12 male connector
- Stainless steel transmitter without output and with stainless steel 5-pin M12 male connector (ATEX/IECEx variant)
- Stainless steel transmitter with 2 configurable outputs (DO/AO) and stainless steel 8-pin M12 male connector (ATEX/IECEx variant)



Product properties

Material

Further information on the materials can be found in chapter "3.2. Material specifications" on page 16.

Non wetted parts

Cover Stainless steel 304/1.4301

Light guide PC (Polycarbonate) and O-ring in EPDM (Ethylene Propylene Diene Monomer)

Transmitter housing Stainless steel 304/1.4301

Functional earth element Cylinder screw, washer, washer spring in stainless steel A4 and jumper of the ground terminal in

stainless steel 304L

Seal Between sensor and transmitter: VMQ silicone (Methyl Vinyl Silicone)

M12 fixed connector and 5- or 8-pin M12 male connector: stainless steel 316L/1.4404 or 303/1.4305 and with seal in EPDM

screwed plug

9/4	1"	11/2"	2"	2 ½"	3"	
1.6	1.8	2.6	2.8	5.0	5.1	
2.0	2.3	3.2	3.4	5.6	5.8	
_	_	_	_	5.3	5.7	
	1.6 2.0	2.0 2.3	1.6 1.8 2.6 2.0 2.3 3.2	1.6 1.8 2.6 2.8 2.0 2.3 3.2 3.4	1.6 1.8 2.6 2.8 5.0 2.0 2.3 3.2 3.4 5.6	1.6 1.8 2.6 2.8 5.0 5.1 2.0 2.3 3.2 3.4 5.6 5.8

Electrical data

Power consumption For device without output: max. 2.5 W

• For device with 2 outputs (DO/AO): max. 5 W

Output

Number of outputs

Digital output

Only for device with 8-pin M12 male connector

2, each configurable as digital or analogue output

Overload information (through software diagnostics function)

- Type: NPN or PNP (wiring dependent), open collector, galvanically isolated
- Operating modes: pulse (by default), On/Off, threshold, frequency (user configurable)
- 10 kHz, 5...35 V DC, max. 700 mA, max. pulse duration: 2 s, selectable limits:
 - 0.0001...10 000 pulses/litre or 0.0001...9 999.99 litres/pulse
 - 0.0001...10 000 pulses/kg or 0.0001...9 999.99 kg/pulse 1.)

· Protected against polarity reversals of DC and overloads

Open loop detection (through software diagnostics function)

Current: • 4...20 mA

- 3.6 mA or 22 mA to indicate an error (only if 4...20 mA scale selected); galvanically isolated
- Max. loop impedance: 1300 Ω at 35 V DC, 1000 Ω at 30 V DC, 700 Ω at 24 V DC, 450 Ω at 18 V DC

Process/Pipe connection & communication

Electrical connection

Analogue output

- 1 × 5-pin M12 male connector (A-coded) for device without output
- 1 x 8-pin M12 male connector (A-coded) for device with 2 outputs

12 | 40 Visit product website



Data transfer

- Device without output: external communication through büS (Bürkert system bus, CANopen protocol)
- Device with 2 outputs: büS connection only to the Bürkert Communicator for configuration and software update of the device. Due to the missing CAN shield the conventional büS/ CANopen communication is not recommended.

Environment and installation

Ambient temperature

Operation:

- All variants except ATEX/IECEx variant:
 - -10...+70 °C (+14...+158 °F) if -20 °C (4 °F) ≤ fluid temperature ≤80 °C (176 °F)
 - at a fluid temperature > 80 °C (176 °F), the maximum ambient temperature decreases linearly from 70 °C (158 °F) up to 40 °C (104 °F).

This means that at a fluid temperature of 80 °C (176 °F) the ambient temperature may be a maximum of 70 °C (158 °F) and at a fluid temperature of 140 °C (284 °F) the ambient temperature may only be a maximum of 40 °C (104 °F).

- ATEX/IECEx variant:
- -10...+60 °C (+14...+140 °F) if -20 °C (4 °F) ≤ fluid temperature ≤100 °C (212 °F)
- at a fluid temperature > 100 °C (212 °F), the maximum ambient temperature decreases linearly from 60 °C (140 °F) up to 45 °C (136 °F).

This means that at a fluid temperature of 100 °C (212 °F) the ambient temperature may be a maximum of 60 °C (140 °F) and at a fluid temperature of 130 °C (266 °F) the ambient temperature may only be a maximum of 45 °C (136 °F)

Further information can be found in chapter "5.1. Medium temperature diagram" on page 24.

2. Approvals and conformities

2.1. General notes

- The approvals and conformities listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- · Not all available variants of the device can be supplied with the below mentioned approvals or conformities.

2.2. Conformity

In accordance with the Declaration of Conformity, the product is compliant with the EU Directives.

2.3. Standards

The applied standards which are used to demonstrate compliance with the EU Directives are listed in the EU-Type Examination Certificate and/or the EU Declaration of Conformity.

Visit product website ▶ 13 | 40

^{1.)} Only if option density measurement and mass flow rate measurement is activated



2.4. Pressure Equipment Directive (PED)

The device conforms to article 4, paragraph 1 of the Pressure Equipment Directive (PED) 2014/68/EU under the following conditions:

Device used on a pipe

Note:

- The data in the table is independent of the chemical compatibility of the material and the fluid.
- PS = maximum admissible pressure (in bar), DN = nominal diameter of the pipe

Type of fluid	Conditions
Fluid group 1, article 4, paragraph 1.c.i	DN ≤25
Fluid group 2, article 4, paragraph 1.c.i	DN ≤32 or PS*DN ≤1000
Fluid group 1, article 4, paragraph 1.c.ii	DN ≤25 or PS*DN ≤2000
Fluid group 2, article 4, paragraph 1.c.ii	DN ≤200 or PS ≤10 or PS*DN ≤5000

2.5. Explosion protection

Approval

Description



Optional: Explosion protection

As a category 3 device suitable for zone 2/22 (optional).

Ex marking of the components according to the following table:



FLOWave L flowmeter	FLOWave S flowmeter				
ATEX	ATEX				
II 3G Ex ec IIC T4 Gc	II 3G Ex ec IIC T4 Gc				
II 3D Ex tc IIIC T110 °C Dc or T130 °C Dc	II 3D Ex tc IIIC T130 °C Dc				
IECEx	IECEx				
• Ex ec IIC T4 Gc	• Ex ec IIC T4 Gc				
Ex tc IIIC T110 °C Dc or T130 °C Dc	Ex tc IIIC T130 °C Dc				

Measures to comply with ATEX/IECEx requirements: refer to the

- Supplement Type 8098 FLOWave L | ATEX/IECEx Variant ▶ or
- Supplement Type 8098 FLOWave S | ATEX/IECEx Variant ▶

under user manual.

The Ex. certification is only valid if the Bürkert device is used as described in the supplement ATEX/IECEx. If unauthorized changes are made to the device, the Ex. certification becomes invalid.

2.6. North America (USA/Canada)

C UL US

DescriptionOptional: UL Listed for the USA and Canada

The products are UL Listed for the USA and Canada according to:

- UL 61010-1 (ELECTRICAL EQUIPMENT FOR MEASUREMENT, CONTROL, AND LABORATORY USE Part 1: General Requirements)
- CAN/CSA-C22.2 No. 61010-1

Certificate number: 2017-10-27-E237737



2.7. Foods and beverages/Hygiene

Approval	Description						
3	3-A Sanitary Standards Inc. (valid for the variable code PE05) The products comply with 3-A Sanitary Standards Inc (3-A SSI) as per certificate. Certificate authorization number: 1178						
ERTIFIED C NOT THE ELL TOPE ELL	 EHEDG (European Hygienic Engineering and Design Group) (Type EL CLASS I) (valid for the variable code PI01) The EHEDG compliance is only valid if the flowmeter with clamp connection according to DIN 32676 is used in combination with gaskets from Combifit International B.V. 						
CLASSI	 if the flowmeter with threaded connection according to DIN 11851 is used in combination with gaskets from Kieselmann GmbH, Germany (ASEPTO-STAR k-flex upgrade gaskets) or 						
	 Siersema Komponenten Service (S.K.S.) B.V. (Netherlands SKS gasket set DIN 11851 EHEDG with EPDM or FKM inner gasket) 						

Conformity	Description				
FDA	FDA – Code of Federal Regulations (valid for the variable code PL02, PL03) The devices are compliant in their composition with the Code of Federal Regulations published by the FDA (Food and Drug Administration, USA) according to the manufacturer's declaration.				
USP United States Pharmacopeial Convention (USP) (valid for the variable code PL04) All wetted materials are biocompatible according to the manufacturer's declaration.					
77	EC Regulation 1935/2004 of the European Parliament and of the Council (valid for the variable code PL01, PL02) All wetted materials are compliant with EC Regulation 1935/2004 according to the manufacturer's declaration.				


2.8. Others

Network protocol

Approval	Description
PROFU°	PROFINET Certificate number: Z12446
EtherNet/IP	EtherNet/IP Document number: 11839
Ether CAT.	EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH.

3. Materials

3.1. Bürkert resistApp



Bürkert resistApp - Chemical resistance chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

Start chemical resistance check

Visit product website

15 | 40




3.2. Material specifications

FLOWave L flowmeter without industrial communication

Note:

The following picture describes a device with $2 \times M20 \times 1.5$ cable glands, 1×5 -pin M12 connector and clamp connection.



No.	Element	Material					
1	Blind cover	Stainless steel 304/1.4301					
2	Display module	Float glass, stainless steel 304/1.4301					
3	Multi-colour LED behind seal (used for e.g. to indicate the status of the product, based on the NAMUR NE 107 standard)	VMQ silicone					
4	Transmitter housing	Stainless steel 304/1.4301					
5a	Cable gland (full stainless steel variant)	Body in stainless steel 304L/1.4307 and seal in TPE (according to FDA)					
5b	Cable glands	Body in nickel plated brass and seal in TPE					
5с	Cable glands (ATEX/IECEx variant)	Body in stainless steel 316L/1.4404 and seal in EPDM					
6a	Blind plug (full stainless steel variant)	PA6					
6b	Blind plug	Black POM					
6с	Blind plug (ATEX/IECEx variant)	PA					
7	5-pin M12 male connector (wired to büS) with screwed plug	 Body in stainless steel 316L/1.4404 and seal in NBR (if equipped with 5a) or in VMQ silicone (if equipped with 5c) or Body in nickel plated brass and seal in NBR (if equipped with 5b) 					
8	Functional earth	Cylinder screw, washer, washer spring in stainless steel A4 and blind rivet nut in stainless steel 1.4578/A4					
9	Seal	VMQ silicone					
10	Blind cover	Stainless steel 304/1.4301					
11	Sensor housing	For sensor with process connection: • ≤ DN 50/2": stainless steel 304/1.4301 • > DN 50/2": stainless steel 316L/1.4435					
12	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content					
13	Process connection (either clamp connections or flange connections)	Stainless steel 316L/1.4435 with low delta ferrite content					
14	Pressure compensating element	Diaphragm in ePTFE, O-ring in silicone 60 Shore A and body in stainless steel (316L/1.4404)					

Visit product website


16 | 40



FLOWave L flowmeter with industrial communication

Note:

The following picture describes a device (Ethernet variant) with 2×4 -pin M12 female connectors, 1×5 -pin M12 male connector and flange connection.



No.	Element	Material						
1	Blind cover or	Stainless steel 304/1.4301						
2	Display module	Float glass, stainless steel 304/1.4301						
3	Multi-colour LED behind seal (used for e.g. to indicate the status of the product, based on the NAMUR NE 107 standard)	VMQ silicone						
4	Transmitter housing	Stainless steel 304/1.4301						
5	4-pin M12 female connectors with screwed plug	Body in stainless steel 304L/1.4307, contact support in PBT GF30 and seal in EPDM						
6	5-pin M12 male connector (wired to büS) with screwed plug	Body in stainless steel 316L/1.4404 and seal in NBR						
7	Functional earth	Cylinder screw, washer, washer spring: stainless steel A4 blind rivet nut: stainless steel 1.4578/A4						
8	Blind cover	VMQ silicone						
9	Seal	Stainless steel 304/1.4301						
10	Sensor housing	Stainless steel 304/1.4301 1.)						
11	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content						
12	Process connection (either clamp connections or flange connections) Stainless steel 316L/1.4435 with low delta ferrite content							
13	Pressure compensating element	Diaphragm: ePTFE; support: polyester; O-ring: silicone 60 Shore A; body: stainless steel (316L/1.4404)						

^{1.)} If clamp connections according to DIN 32676 or threaded connections according to DIN 11851 are used instead of flange connections, the material of the sensor housing for DN >50 is stainless steel 316L/1.4435

Visit product website


17 | 40



FLOWave S flowmeter

Note:

The following picture shows a device with 1×5 -pin M12 male connector and clamp connection.



No.	Element	Material					
1	Cover	Stainless steel 304/1.4301					
2	Light guide for status display behind seal (used for e.g. indicating the status of the product, based on the NAMUR NE 107 standard)	PC and O-ring in EPDM					
3	Transmitter housing	Stainless steel 304/1.4301					
4	5-pin M12 male connector (wired to büS) with screwed plug or 8-pin M12 male connector (wired to büS as service interface 1) and 2 x DO/AO) (with screwed plug)	Stainless steel 316L/1.4404 or 303/1.4305 and seal in EPDM					
5	Functional earth	Cylinder screw, washer, washer spring: stainless steel A4Jumper of the ground terminal: stainless steel 304L					
6	Seal	VMQ silicone					
7	Sensor housing	For sensor with process connection: • ≤ DN 50/2": stainless steel 304/1.4301 • > DN 50/2": stainless steel 316L/1.4435					
8	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content					
9	Process connection (either clamp connections or flange connections)	Stainless steel 316L/1.4435 with low delta ferrite content					

^{1.)} büS connection to the Bürkert communicator only for configuration and software update of the device. Due to the lack of CAN shielding, the conventional büS/CANopen communication is not recommended.

Visit product website

18 | 40




4. Dimensions

4.1. Transmitter of the FLOWave L flowmeter without industrial communication

Note:


Dimensions in mm, unless otherwise stated



4.2. Transmitter of the FLOWave L flowmeter with industrial communication (Ethernet variant)

Note:


Dimensions in mm, unless otherwise stated



4.3. Transmitter of the FLOWave S flowmeter

Note:


Dimensions in mm, unless otherwise stated





4.4. Flowmeter with clamp connections

- Dimensions in mm, unless otherwise stated
- Clamp connection according to DIN 32676 series A, B or C, or SMS 3017





Process and pip	s connection e size	HL	HS	HL1	HS1	L	L1	ØD	ØD1	ØD2	ØD3	ØG
[mm]	[inch]											
Clamp	according to	DIN 3267	76 series	A and proc	ess pipe a	according	to DIN 11	866 series	A (DIN 118	50)		
08	_	250	184	220	154	158	105	10	10	14	34	60.3
15 ^{1.)}	_	250	184	220	154	166	105	16	15.75	19.05	34	60.3
25 1.)	_	250	184	220	154	236	105	26	22.1	25.4	50.5	60.3
40 1.)	_	250	184	200	134	326	180	38	34.8	38.1	50.5	91
50 1.)	_	250	184	200	134	306	180	50	47.5	50.8	64	91
65	_	321	255	251	185	300	210	66	66	70	91	139.7
80	_	321	255	251	185	300	210	81	81	85	106	139.7
Clamp	according to	DIN 3267	76 series l	B and prod	ess pipe a	according	to DIN 11	866 series	B (ISO 112	27)		
08	_	250	184	220	154	158	105	10.3	10.3	14	25	60.3
15	_	250	184	220	154	168	105	18.1	18.1	21.3	50.5	60.3
15 ^{2.)}	_	250	184	220	154	168	105	18.1	18.1	21.3	34	60.3
25	_	250	184	220	154	175	120	29.7	29.7	33.7	50.5	60.3
40	_	250	184	200	134	273	180	44.3	44.3	48.3	64	91
50	_	250	184	200	134	273	180	56.3	56.3	60.3	77.5	91
65	_	321	255	251	185	300	210	72.1	72.1	76.1	91	139.7
80	_	321	255	251	185	300	210	84.3	84.3	88.9	106	139.7
Clamp	according to	DIN 3267	76 series (C and prod	ess pipe a	according	to DIN 11	866 series	C (ASME I	BPE)		
_	3/8	250	184	220	154	158	105	7.75	7.75	14	25	60.3
_	1/2	250	184	220	154	158	105	9.4	9.4	14	25	60.3
_	3/4	250	184	220	154	143	105	15.75	15.75	19.05	25	60.3
-	1	250	184	220	154	143	105	22.1	22.1	25.4	50.5	60.3
_	1½	250	184	200	134	273	180	34.8	34.8	38.1	50.5	91
-	2	250	184	200	134	273	180	47.5	47.5	50.8	64	91
-	2½	321	255	251	185	300	210	60.2	60.2	63.5	77.5	139.7
_	3	321	255	251	185	300	210	72.9	72.9	76.2	91	139.7
Clamp	according to	SMS 301	7 and pro	cess pipe	according	to SMS 3	8008					
25 ^{1.)}	_	250	184	220	154	143	105	22.6	22.1	25.4	50.5	60.3
40 1.)	_	250	184	200	134	273	180	35.6	34.8	38.1	50.5	91
50 ^{1.)}	_	250	184	200	134	273	180	48.6	47.5	50.8	64	91

^{1.)} DIN 32676 series A and SMS 3017 based on ASME BPE measurement tube sizes with adapted concentric clamp connection, design according to EHEDG DOC8 guidelines


^{2.)} Similar to DIN 32676 series B, but with clamp connection 34.0



4.5. Flowmeter with aseptic collar flange connections (BF)

Note:

- Dimensions in mm, unless otherwise stated
- Aseptic collar flange connection (BF) according to DIN 11864-2 form A series A, B or C



Process of and pipe	connection size	HL	HS	HL1	HS1	L	L1	L2	ØD	ØD1	ØD2	ØD3	ØG	ØΊ	K
[mm]	[inch]	-													
Flange ad	Flange according to DIN 11864-2 series A and process pipe according to DIN 11866 series A (DIN 11850)														
15 ^{1.)}	_	250	184	220	154	166	163	105	16	15.75	19.05	59	60.3	9	42
25 ^{1.)}	_	250	184	220	154	240	237	105	26	22.1	25.4	70	60.3	9	53
40 1.)	_	250	184	200	134	330	327	180	38	34.8	38.1	82	91	9	65
50 ^{1.)}	_	250	184	200	134	310	307	180	50	47.5	50.8	94	91	9	77
65	_	321	255	251	185	300	297	210	66	66	70	113	139.7	9	95
80	_	350	283	265	199	300	297	210	81	81	85	133	168.3	11	112
Flange ad	cording to	DIN 118	64-2 se	ries B ar	nd proce	ess pipe	accord	ing to DI	N 11866	series	B (ISO 1	127)			
08	_	250	184	220	154	158	155	105	10.3	10.3	14	54	60.3	9	37
15	_	250	184	220	154	173	170	105	18.1	18.1	21.3	62	60.3	9	45
25	_	250	184	220	154	190	187	120	29.7	29.7	33.7	74	60.3	9	57
40	_	250	184	200	134	278	275	180	44.3	44.3	48.3	88	91	9	71
50	_	250	184	200	134	265	262	180	56.3	56.3	60.3	103	91	9	85
65	_	350	283	265	199	300	29	210	72.1	72.1	76.1	125	168.3	11	104
80	_	350	283	265	199	300	197	210	84.3	84.3	88.9	137	168.3	11	116
Flange ad	cording to	DIN 118	64-2 se	ries C aı	nd proce	ess pipe	accord	ing to D	N 11866	series	C (ASMI	E BPE)			
_	1/2	250	184	220	154	158	155	105	9.4	9.4	14	54	60.3	9	37
_	3/4	250	184	220	154	171	168	105	15.75	15.75	19.05	59	60.3	9	42
_	1	250	184	220	154	168	165	105	22.1	22.1	25.4	66	60.3	9	49
_	11/2	250	184	200	134	278	275	180	34.8	34.8	38.1	79	91	9	62
_	2	250	184	200	134	278	275	180	47.5	47.5	50.8	92	91	9	75

^{1.)} DIN 11864-2 series A based on ASME BPE measurement tube sizes with adapted concentric flange connection, design according to EHEDG DOC8 guidelines

Visit product website


22 | 40



4.6. Flowmeter with aseptic collar clamp connections (BKS)

Note:

- Dimensions in mm, unless otherwise stated
- Aseptic collar clamp connection (BKS) according to DIN 11864-3 form A series A, B or C



Process of pipe size	connection and	HL1	HS1	L	L1	L2	ØD	ØD1	ØD2	ØD3	ØG
[mm]	[inch]										
Clamp ac	cording to DIN 1	1864-3 se	ries A and	process p	oipe accord	ding to DIN	l 11866 ser	ies A (DIN	11850)		<u> </u>
15 ^{1.)}	-	220	154	166	163	105	16	15.75	19.05	34	60.3
25 ^{1.)}	-	220	154	240	237	105	26	22.1	25.4	50.5	60.3
40 1.)	-	200	134	330	327	180	38	34.8	38.1	64	91
50 ^{1.)}	-	200	134	310	307	180	50	47.5	50.8	77.5	91
Clamp ac	cording to DIN 1	1864-3 se	ries B and	process	oipe accord	ding to DIN	l 11866 ser	ies B (ISO	1127)		
08	_	220	154	158	155	105	10.3	10.3	14	34	60.3
15	-	220	154	169	166	105	18.1	18.1	21.3	34	60.3
25	-	220	154	190	187	120	29.7	29.7	33.7	50.5	60.3
40	-	200	134	280	277	180	44.3	44.3	48.3	64	91
50	-	200	134	271	268	180	56.3	56.3	60.3	91	91
Clamp ac	cording to DIN 1	1864-3 se	ries C and	process	oipe accor	ding to DIN	N 11866 ser	ies C (ASN	IE BPE)		
_	1/2	220	154	158	155	105	9.4	9.4	14	34	60.3
_	3/4	220	154	167	164	105	15.75	15.75	19.05	34	60.3
_	1	220	154	164	161	105	22.1	22.1	25.4	50.5	60.3
_	11/2	200	134	278	275	180	34.8	34.8	38.1	64	91
_	2	200	134	279	276	180	47.5	47.5	50.8	77.5	91

^{1.)} DIN 11864-3 series A based on ASME BPE measurement tube sizes with adapted concentric clamp connection, design according to EHEDG DOC8 guidelines


23 | 40



4.7. Flowmeter with thread connections

Note:

- Dimensions in mm, unless otherwise stated
- Thread connection according to DIN 11851 series A




Process connection and pipe size [mm]	HL	HS	HL1	HS1	L	L1	L2	ØD	ØD2	Ø D3 1.)	ØG
Thread according to DIN	11851										
65	321	255	251	185	300	284	210	66	70	Rd 95 x 1/6	139.7
80	321	255	251	185	300	284	210	81	85	Rd 110x1/4	139.7

^{1.)} Thread according to DIN 405-1

5. Performance specifications

5.1. Medium temperature diagram



Visit product website

24 | 40



5.2. Measurement deviation table

Note:

- This table shows the measurement according to pipe diameter and process connection standards, per measuring range.
- In the following table, the term "full scale" refers to full scale of volume flow rate, i.e. the flow rate corresponding to 10 m/s flow velocity.

DN	Pipe standard	Flow velocity in sensor tube in [m/s] in % of full scale	0.1 1	1 10		10 100
3/8"	ASME BPE	Volume flow rate range [m³/h]	0.017 ± 0.	0.17 .08 % of full scale	± 0.4 % of measured value	1.7
1/2"	ASME BPE	Volume flow rate range [m³/h]	0.025 ± 0.	0.25 .08 % of full scale	± 0.4 % of measured value	2.5
08	ISO 1127 DIN 11850	Volume flow rate range [m³/h]	0.03 ± 0.	0.30 .08 % of full scale	± 0.4 % of measured value	3
³ / ₄ " 15	ASME BPE DIN 11850	Volume flow rate range [m³/h]	0.07 ± 0.	0.7 .08 % of full scale	± 0.4 % of measured value	7
15	ISO 1127	Volume flow rate range [m³/h]	0.10 ± 0.	1.0 .08 % of full scale	± 0.4 % of measured value	10
1" 25 25	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.14 ± 0.	1.4 .08 % of full scale	± 0.4 % of measured value	14
25	ISO 1127	Volume flow rate range [m³/h]	0.25 ± 0.	2.5 .08 % of full scale	± 0.4 % of measured value	25
1½" 40 40	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.35 ± 0.	3.5 .08 % of full scale	± 0.4 % of measured value	35
40	ISO 1127	Volume flow rate range [m³/h]	0.56 ± 0.	5.6 .08 % of full scale	± 0.4 % of measured value	56
2" 50 50	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.64 ± 0	6.4 .08 % of full scale	± 0.4 % of measured value	64
50	ISO 1127	Volume flow rate range [m³/h]	0.90 ± 0	9.0 .08 % of full scale	± 0.4 % of measured value	90
2½"	ASME BPE	Volume flow rate range [m³/h]	1.02 ± 0	10.2 .08 % of full scale	± 0.4 % of measured value	102
65	DIN 11850	Volume flow rate range [m³/h]	1.23 ± 0.	12.3 .08 % of full scale	± 0.4 % of measured value	123
65	ISO 1127	Volume flow rate range [m³/h]	1.47 ± 0	14.7 .08 % of full scale	± 0.4 % of measured value	147
3"	ASME BPE	Volume flow rate range [m³/h]	1.50 ± 0.	15.0 .08 % of full scale	± 0.4 % of measured value	150
80	DIN 11850	Volume flow rate range [m³/h]	1.85 ± 0	18.5 .08 % of full scale	± 0.4 % of measured value	185
80	ISO 1127	Volume flow rate range [m³/h]	2.00 ± 0	20.0 .08 % of full scale	± 0.4 % of measured value	200

5.3. Refresh time table

Selectable mode	Volume flow rate	Density	Mass flow rate
Very short	~25 ms	1 s	~25 ms
Short	~40 ms	1 s	~40 ms
Long	~75 ms	0.5 s	~75 ms

Visit product website

25 | 40



6. Product installation

6.1. Installation notes

Note:

The device is not suitable for use in gaseous media and steam. However, their flow does not have any negative effect on the device or its operation. Other liquids flowing through again afterwards are measured correctly as before.

The factory calibration of the FLOWave is done under reference conditions with inlet (40 x DN) and outlet (1 x DN) distances and the appropriate internal diameter of the pipes.

Deviation from reference conditions can be easily adjusted through the use of a built-in K factor adjustment or Teach in procedure. We can support you if necessary, please do not hesitate to contact us.

The device can be installed into either horizontal, oblique or vertical pipes. But an installation on a vertical pipe will be better to prevent air or gas bubbles inside the measurement area. For proper operation always ensure a totally filled measurement tube.

Conformity to 3-A and EHEDG requires an angle of at least 5° (for SMS or series A connections) or 3° (all others available connections) against horizontal to ensure complete draining however this not necessary for proper operation of the FLOWave.

The suitable pipe size can be selected using the diagram for selecting the nominal diameter of the pipe. See chapter "6.2. Selection of the nominal diameter" on page 26.

6.2. Selection of the nominal diameter

The following graph is used to determine the appropriate DN of the pipe and fitting for the application, according to the fluid velocity and the flow rate. On the chart, the intersection of flow velocity and flow rate gives the appropriate diameter.

Example 1:

Flowmeter with process connection according to DIN 32676 series B (pipe ISO 1127) or DIN 11864-2 form A series B (pipe ISO 1127)

- Nominal flow: 10 m3/h
- Optimal flow rate: 1...3 m/s


Result: Select a pipe size of DN 40 or DN 50

Example 2:

Flowmeter with process connection according to DIN 32676 series A (pipe DIN 11850) or DIN 11864-2 series A (pipe DIN 11850)

- Nominal flow: 10 m³/h
- Optimal flow rate: 1...3 m/s

Result: Select a pipe size of DN 40 or DN 50






6.3. Mounting options

FLOWave L flowmeter

The product is delivered as described in position 1 in the picture below. The position of the transmitter can be changed in 90° steps. The position of the display module and the blind cover can also be changed in steps of 90° both on the top of the unit and on the front face.



For safety reasons the display module and blind cover on the top or front are locked. The display module and blind cover can be unlocked with a magnetic key which is included in the delivery of each device.



FLOWave S flowmeter

The product is delivered as described in position 1 in the picture below. The position of the transmitter can be changed in 90° steps. For safety reasons the transmitter is locked. The transmitter can be unlocked with a magnetic key which is included in the delivery of each device.



27 | 40



7. Product operation


7.1. Measuring principle

The technology used is based on SAW (Surface Acoustic Waves). The type of wave propagation is similar to what happens when an earthquake occurs in nature.

In the case of FLOWave it is a miniaturized signal, not running on the surface of the earth but on a measurement tube. FLOWave uses so called interdigital transducers which are placed on flattened areas of the tube surface. Each one acts as emitter as well as receiver. Two of them (nos. 1 and 4) emit forward, in the direction of the liquid flow, the others (nos. 2 and 3) backwards, i.e. in the opposite direction to the direction of flow. The propagation time is measured from emitter to receiver. The difference between the forward and backward propagation time of the waves is proportional to the volume flow rate.

The high performance measurement is achieved by the following aspects:

- · Each emitter sends multiple signals that are received on two other receivers
- The results are based on the reception of the signals that pass through the liquid one or more times.
- Several measurements can be performed based on the collected information. Many properties of the liquid can be derived, including the flow velocity, the fluid density, the fraction of the transmitted signal ("acoustic transmission factor"), and the so-called "differentiation factor" (see following), as well as information about the presence of gas bubbles or solid parts.
- Mass flow is calculated from fluid density and volume flow.
- Mass flow and density measurements are an option on standard FLOWave flowmeters, which requires adjustment and calibration during
 manufacture. It is therefore necessary to specify whether or not the device is to be equipped with these features when ordering the
 device.



This figure shows, as an example, the reception signals when interdigital transducer 1 is transmitting. The emitter excitation produces the SAW with a frequency of more than 1 MHz.

As a result of the emission of these waves, the following effects occur:

- A wave propagates along the surface of the tube (see blue line).
- A wave is emitted (see teal green line) and passes through the liquid towards the opposite side of the tube at a certain angle, which depends mainly on the speed of propagation on the surface of the tube and in the liquid.
- Upon reaching the opposite side of the tube, two effects take place.
 - A wave is triggered in the tube and propagates (see green line) to receiver 3
 - A wave is triggered in the liquid (see yellow line) and passes through it again to the opposite wall of the tube. The analysis of the transmitted and received waves allows deriving the process values (velocity, density, flow rates).

These effects are repeated and thus generate the many signals received, which are differentiated in the image with different colours.



7.2. Special functions

Note:

DF, ATF, density and mass flow features must be selected upon initial order of device.

For the detection of gas bubbles and solid particles the device (from firmware version 01.05.00) includes a so called "acoustic transmission factor (ATF)" with a measurement range of 5...120%, whose value is constantly recorded and directly influenced by the presence of gas bubbles and solid particles.

A "differentiation factor (DF)", with a measuring range of 0.8...1.3, is available for the detection and differentiation of liquids. This continuously measured value, which uses water as a reference fluid, is temperature-compensated and so its value is representative in a tight value range for each liquid. The changes in value of this process measurement enable differentiation between different liquids.

Before SW version 05.00.00, the differentiation factor was named density factor. As the density option has been added, the name has been changed to avoid confusion.

8. Product design and assembly


8.1. Product assembly

The 8098 flowmeter consists of a S097 flow sensor and a FLOWave L transmitter (variant FLOWave L flowmeter) or FLOWave S transmitter (variant FLOWave S flowmeter).


The flow sensor includes the measurement tube equipped with interdigital transducers, the sensor housing and the process connections in accordance to the standards ISO, ASME BPE, DIN, SMS. At present the sensor size ranges from DN 08 to DN 80 or from %" to 3".

The FLOWave L flowmeter is available with or without display. The high resolution display includes a capacitive working keypad for all interactive user actions, guided by a user friendly menu system. The output signals include one analogue output and one digital output; while a third output signal can be switched between analogue and digital through parametrisation. Electrical connection is done on push-in connectors via two cable glands and/or one M12 connector.

The FLOWave S flowmeter is only available without display. The electrical connection is made via an M12 male connector.



FLOWave S flowmeter



Visit product website ▶ 29 | 40




9. Product accessories

Note:

To configure a device without a display, use the USB-büS interface Type 8923 and the Bürkert Communicator software Type 8920. For the FLOWave S with 2 outputs, the büS adaptor cable, article no. 773286, is also required.

See **Software manual Type 8920** ▶ for more information.



10. Ordering information

10.1. Bürkert eShop



Bürkert eShop - Easy ordering and quick delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

Order online now

Visit product website ▶ 30 | 40



10.2. Recommendation regarding product selection

Note:

- The installation of the flowmeter in a pipe requires the use of counter-connection, seals, fixing elements, etc. depending on the used norm.
- The drawings show the installation with a FLOWave L variant of the flowmeter. The installation is also valid for the FLOWave S variant.

For instance with middle-sized devices:

Connection	Description
	With clamp connection according to DIN 32676 series A To insert a FLOWave DN 40 with clamp connections according to DIN 32676 series A (with Ra <0.8 µm) to a pipe according to DIN 11866 series A (DIN 11850), the correct adapters to be selected and separately ordered are for instance • 2x BBS-25 clamp ferrules, article no. 747237, see data sheet Type BBS-25 ▶ for more information
	2x the appropriate seals (not provided)
	2x the corresponding clamps, article no. 731164
	With aseptic collar flange (BF) according to DIN 11864-2 form A To insert a FLOWave DN 40 with collar flanges according to DIN 11864-2 series B (with Ra <0.8 μm) to a pipe according to DIN 11866 series B (ISO 1127), the correct adapters to be selected and separately ordered are for instance
+ - - - - - - - 	• 2x BBS-06 aseptic groove flange, article no. 731860, see data sheet Type BBS-06 ▶ for more information
	2x the appropriate seals (not provided)
	8x the corresponding screws, flat washers and nuts (please refer to the DIN 11864-2 standard)
	With aseptic collar clamp (BKS) according to DIN 11864-3 form A To insert a FLOWave 1" with hygienic collar clamps according to DIN 11864-3 series C (with Ra <0.8 μ m) to a pipe according to DIN 11866 series C (ASME BPE), the correct adapters to be selected and separately ordered are for instance
	• 2x BBS-05 aseptic groove clamp, article no. 730272, see data sheet Type BBS-05 ▶ for more information
	2x the appropriate seals (not provided)
	• 2x the corresponding clamps, article no. 731164
	With thread according to DIN 11851 To insert a FLOWave with thread according to DIN 11851 series A to a pipe according to DIN 11850, suitable adapters (not available from Bürkert) are required, for instance
	2x the conical ferrule
 	2x the appropriate DIN 11851 seal
	2x the corresponding round slotted nut

10.3. Bürkert product filter



Bürkert product filter - Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

Try out our product filter

Visit product website

31 | 40



10.4. Bürkert Product Enquiry Form



Bürkert Product Enquiry Form - Your enquiry quickly and compactly

Would you like to make a specific product enquiry based on your technical requirements? Use our Product Enquiry Form for this purpose. There you will find all the relevant information for your Bürkert contact. This will enable us to provide you with the best possible advice.

Fill out the form now

10.5. Bürkert 3D Model

Applications & Tools



Bürkert 3D Model - Interactive Animation

3D Model and Interactive Animation are available on the website of the flowmeter Type 8098.

See website of the Type 8098 ▶ under "Applications and Tools".

10.6. Ordering chart FLOWave L flowmeter with or without industrial communication

Clamp connection acc. to DIN 32676 series A for pipe acc. to DIN 11866 series A (DIN 11850)

Note:

- To configure a device without a display, use the USB-büS interface Type 8923 (must be ordered separately, see chapter "9. Product
 accessories" on page 30 and "10.8. Ordering chart accessories" on page 40).
- The following variants are equipped with a display and the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diameter 1.)	Maximal	Dimensions ^{2.)}	Surface quality		Approval ar	nd	Article no.	
	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube	conformity			
[mm]	[m ³ /h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)		
	Variant without industrial communication (2 cable glands 4) M20 x1.5 and 1 x 5-pin M12 male connector), operating volta 1235 V DC							
15	7	19.05 x 1.65; 34.0	Ra<1.6	Ra<0.8	Yes	Yes	569159 ≒	
				Ra<0.4			569161 ≒	
25	14	25.4 x 1.65; 50.5		Ra<0.8			569163 🖼	
				Ra<0.4			569165 ≒	
40	35	38.1 x1.65; 50.5		Ra<0.8			569167 📜	
				Ra<0.4			569169 📜	
50	64	50.8 x 1.65; 64.0		Ra<0.8			569171 ≒	
				Ra<0.4			569173 ≒	
65	123	70.0x2.0; 91.0		Ra<0.8			573445 🛱	
				Ra<0.4			573373 🛱	
80	185	85.0 x 2.0; 106.0		Ra<0.8			573446 🖼	
				Ra<0.4			573374 ≒	

^{1.) =} process connection size and pipe size

32 | 40

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.

^{4.)} Cable glands in nickel plated brass



Clamp connection acc. to DIN 32676 series B for pipe acc. to DIN 11866 series B (ISO 1127)

- To configure a device without a display, use the USB-büS interface Type 8923 (must be ordered separately, see chapter "9. Product accessories" on page 30 and "10.8. Ordering chart accessories" on page 40).
- The following variants are equipped with a display and the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diameter 1.)	Maximal	Dimensions ^{2.)}	Surface quality		Approval a	nd	Article no.		
	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube	conformity				
[mm]	[m³/h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)			
Variant without industrial communication (2 cable glands 4) M20x1.5 and 1x5-pin M12 male connector), operating voltage 1235 V DC									
08	3	14×1.85; 25.0	Ra<1.6	Ra<0.8	Yes	Yes	573126 ≒		
				Ra<0.4			573128 ≒		
15	10	21.3×1.6; 50.5		Ra<0.8		Yes	566187 ≒		
		21.3×1.6; 34.0				No	566235 ≒		
		21.3×1.6; 50.5		Ra<0.4		Yes	566195 ≒		
		21.3×1.6; 34.0	-			No	566237 ≒		
25	25	33.7×2.0; 50.5	_	Ra<0.8		Yes	566188 ≒		
				Ra<0.4			566196 ≒		
40	56	48.3×2.0; 64.0		Ra<0.8			566189 ≒		
				Ra<0.4			566197 ≒		
50	90	60.3×2.0; 77.5	_	Ra<0.8			566190 ≒		
				Ra<0.4			566198 ≒		
65	147	76.1 x 2.0; 91.0	_	Ra<0.8			573442 📜		
				Ra<0.4			573370 ≒		
80	200	88.9 x 2.3; 106.0		Ra<0.8			573443 🖼		
				Ra<0.4			573371 🛱		

^{1.) =} process connection size and pipe size

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.

^{4.)} Cable glands in nickel plated brass



Clamp connection acc. to DIN 32676 series C for pipe acc. to DIN 11866 series C (ASME BPE)

- To configure a device without a display, use the USB-büS interface Type 8923 (must be ordered separately, see chapter "9. Product accessories" on page 30 and "10.8. Ordering chart accessories" on page 40).
- The following variants are equipped with a display and the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diame-	Maximal		Surface quality		Approval ar	nd conform	ity	Article no.
ter ^{1.)}	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube		3-A (28-06) EHEDG ^{3,)} UL		
[inch]	[m ³ /h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)	UL	
Variant v		ustrial communicati	on (2 cable glands ^{4.)} M20	x1.5 and 1 × 5-pin M1	2 male conn	ector), ope	rating	voltage of
3/8	1.7	14.00 x 3.125; 25.0	Ra<1.6	Ra<0.8	Yes	Yes	No	573112 ≒
				Ra<0.4				573114 ≒
							Yes	573116 🛒
1/2	2.5	14.00 x 2.3; 25.0		Ra<0.8			No	573119 ≒
				Ra<0.4				573121 ≒
							Yes	573123 ≒
3/4	7	19.05×1.65; 25.0		Ra<0.8			No	566203 ≒
				Ra<0.4				566211 ≒
							Yes	569675 ≒
1	14	25.4×1.65; 50.5		Ra<0.8			No	566204 ≒
				Ra<0.4				566212 ≒
							Yes	569676 ≒
1½	35	38.1 × 1.65; 50.5		Ra<0.8			No	566205 ≒
				Ra<0.4				566213 ≒
							Yes	569677 ≒
2	64	50.8×1.65; 64.0		Ra<0.8			No	566206 ≒
				Ra<0.4				566214 📜
							Yes	569678 ≒
21/2	100	63.5 x 1.65; 77.5		Ra<0.8			No	573448 📜
				Ra<0.4				573376 ≒
					_		Yes	574710 🛱
3	150	76.2 x 1.65; 91.0		Ra<0.8	-		No	573449 📜
				Ra<0.4			\\\	573377 🛱
							Yes	574711 🛱



Diame-	Maximal	Dimensions ^{2.)}	Surface quality		Approval ar	nd conform	ity	Article no.		
ter ^{1.)}	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube						
[inch]	[m³/h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG ^{3.)}	UL			
	Variant with industrial communication (Ethernet variant, 2×4-pin M12 female connectors and 1×5-pin M12 male connector), operating voltage of 1235 V DC									
3/8	1.7	14.00 x 3.125; 25.0	Ra<1.6	Ra<0.4	Yes	Yes	No	573117 ≒		
							Yes	573118 ≒		
1/2	2.5	14.00 x 2.3; 25.0					No	573124 ≒		
							Yes	573125 ≒		
3/4	7	19.05 × 1.65; 25.0					No	570444 ≒		
							Yes	569679 ≒		
1	14	25.4×1.65; 50.5					No	570445 ≒		
							Yes	569680 ≒		
11/2	35	38.1 × 1.65; 50.5					No	570446 ∖≕		
							Yes	569681 ≒		
2	64	50.8×1.65; 64.0					No	570447 ≒		
							Yes	569682 ≒		
21/2	100	63.5 x 1.65; 77.5					No	574716 🛱		
							Yes	574720 ≒		
3	150	76.2 x 1.65; 91.0					No	574717 ≒		
							Yes	574721 ≒		

^{1.) =} process connection size and pipe size

Thread connection acc. to DIN 11851 series A for pipe acc. to DIN 11866 series A (DIN 11850)

- To configure a device without a display, use the USB-büS interface Type 8923 (must be ordered separately, see chapter "9. Product accessories" on page 30 and "10.8. Ordering chart accessories" on page 40).
- The following variants are equipped with a display and the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diameter 1.)	Maximal	Dimensions 2.)	Surface quality	Surface quality			Article no.
	flow rate	D2 x s; D3	Housing, outer surface of measurement tube Inner surface of measurement tube		conformity		
[mm]	[m³/h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 2.)	
Variant with 1235 V DO		rial communication (2	cable glands ^{4.)} M20x1.5	and 1×5-pin M12 male	e connector)	, operating v	voltage of
65	123	70.0 x 2.0; Rd 95 x ½	Ra<1.6	Ra<0.8	Yes	Yes	573463 🛱
80	185	85.0x2.0; Rd 110x1/4		Ra<0.8			573464 ≒

^{1.) =} process connection size and pipe size

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.

^{4.)} Cable glands in nickel plated brass

^{2.)} D2 for holder; s = thickness; D3: thread connection

^{3.)} The EHEDG compliance is s only valid if used in combination with EHEDG-compliant gaskets from

[•] Kieselmann GmbH, Germany (ASEPTO-STAR k-flex upgrade gaskets) or

[•] Siersema Komponenten Service (S.K.S.) B.V. (Netherlands SKS gasket set DIN 11851 EHEDG with EPDM or FKM inner gasket).

^{4.)} Cable glands in nickel plated brass



	Further variant on request		
4 0	Process connection For pipe DIN 11850: Clamp DIN 11864-3 Flange DIN 11864-2 For pipe ISO 1127: Clamp DIN 11864-3 Flange DIN 11864-2	>	Additional With/without display Without differentiation factor (DF) Without acoustic transmission factor (ATF) With density and mass flow Ethernet module (EtherNet/IP, PROFINET, Modbus TCP/IP, ETHERCAT) ATEX/IECEx
	 For pipe ASME BPE: Clamp DIN 11864-3 Flange DIN 11864-2 For pipe SMS 3008: SMS 3017 	辞	Material • With inner surface of measurement tube - Ra < 0.8 μm (30 μin.) - Ra < 0.4 μm (15 μin.) (electro-polished) according to ISO 4288
	Orifice ■ 0880 mm ■ %3 inch		Electrical connection Cable gland in stainless steel

For any other variants, use the product enquiry form, see chapter "10.4. Bürkert Product Enquiry Form" on page 32 or check the readily available article no. listed in the Bürkert eShop.

10.7. Ordering chart FLOWave S flowmeter

Clamp connection acc. to DIN 32676 series A for pipe acc. to DIN 11866 series A (DIN 11850)

Note:

The following variants are equipped with the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diameter 1.)		Dimensions ^{2.)}	Surface quality	Approval and		Article no.			
	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube	conformity				
[mm]	[m³/h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)			
Electrical c	Electrical connection: 1 × 8-pin M12 male connector, operating voltage of 1235 V DC								
65	123	70.0x2.0; 91.0	Ra<1.6	Ra<0.8	Yes	Yes	574689 🖼		
				Ra<0.4			573421 ≒		
80	185	85.0 x 2.0; 106.0		Ra<0.8			574690 🖼		
				Ra<0.4			573422 📜		

^{1.) =} process connection size and pipe size

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.



Clamp connection acc. to DIN 32676 series B for pipe acc. to DIN 11866 series B (ISO 1127)

Note:

The following variants are equipped with the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diameter 1.)	Maximal flow rate [m³/h]	Dimensions ^{2.)} D2 x s; D3 [mm]	Surface quality	Approval and conformity		Article no.	
			Housing, outer surface of of measurement tube Inner surface of measurement tub				
[mm]			[µm]	[µm]	3-A (28-06)	EHEDG 3.)	
Electrical c	onnection:	1×5-pin M12 male o	connector, operating voltag	ge of 1235 V DC			
08	3	14×1.85; 25.0		Ra<0.8	Yes	Yes	573716 🛱
				Ra<0.4			573717 📜
15	10	21.3×1.6; 50.5		Ra<0.8		Yes	573093 🛱
		21.3×1.6; 34.0				No	573094 📜
		21.3×1.6; 50.5		Ra<0.4		Yes	573098 🛱
		21.3×1.6; 34.0				No	573099 🛱
25	25	33.7×2.0; 50.5		Ra<0.8		Yes	573095 🖼
				Ra<0.4			573100 ≒
40	56	48.3×2.0; 64.0		Ra<0.8			573096 ≒
				Ra<0.4			573101 🛱
50	90	60.3×2.0; 77.5		Ra<0.8			573097 📜
				Ra<0.4			573102 ≒
Electrical c	onnection:	1×8-pin M12 male o	connector, operating voltage	ge of 1235 V DC			
08	3	14×1.85; 25.0		Ra<0.8	Yes	Yes	571780 🖼
				Ra<0.4			571781 🛱
15	10	21.3×1.6; 50.5		Ra<0.8		Yes	571782 📜
		21.3×1.6; 34.0				No	571783 🛒
		21.3×1.6; 50.5				Yes	571784 📜
		21.3×1.6; 34.0				No	571785 🛱
25	25	33.7×2.0; 50.5		Ra<0.8		Yes	571786 ≒
				Ra<0.4			571787 📜
40	56	48.3×2.0; 64.0		Ra<0.8			571788 🖼
				Ra<0.4			571789 📜
50	90	60.3×2.0; 77.5		Ra<0.8			571790 🖼
				Ra<0.4			571791 ≒
65	147	76.1 x 2.0; 91.0		Ra<0.8			574686 ≒
				Ra<0.4			573418 📜
80	200	88.9 x 2.3; 106.0		Ra<0.8			574687 📜
				Ra<0.4			573419 📜

^{1.) =} process connection size and pipe size

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.



Clamp connection acc. to DIN 32676 series C for pipe acc. to DIN 11866 series C (ASME BPE)

Note:

The following variants are equipped with the special functions ATF (acoustic transmission factor) and DF (differentiation factor).

Diame-		Dimensions 2.)	Surface quality	Approval ar	Article no.			
ter ^{1.)}	flow rate	e D2 x s; D3	Housing, outer surface Inner surface of measurement tube					
[inch]	[m ³ /h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)	UL	
			le connector, operating v					
8	1.7	14.00 x 3.125; 25.0	Ra<1.6	Ra<0.8	Yes	Yes	No	573710 ∖≅
				Ra<0.4	-			573711 🛱
							Yes	573712 🖫
/2	2.5	14.00 x 2.3; 25.0	_	Ra<0.8	_		No	573713 🖫
		, , , , ,		Ra<0.4	_			573714 🖼
							Yes	573715 🖼
4	7	19.05×1.65; 25.0	_	Ra<0.8			No	573085
•		10100 11100, 2010		Ra<0.4	_			573089
							Yes	573190 🛱
<u> </u>	14	25.4×1.65; 50.5		Ra<0.8			No	573086 🛱
	17	20.4 × 1.00, 00.0		Ra<0.4	_		140	
				114 1017			Yes	573090 😾 573191 🖼
1/2	35	38.1×1.65; 50.5	_	Ra<0.8	_		No	
/2	00	00.1 × 1.00, 00.0		Ra<0.4			140	573087 😾
				11a < 0.4			Yes	573091 😾
)	64	50.8×1.65; 64.0		Ra<0.8				573192 😾
	04	50.6 × 1.65; 64.0					No	573088 🖼
				Ra<0.4			Vaa	573092 🖼
	.1		1	-U(40, 05 V D	•		Yes	573193 ≒
siectrica %	1.7	14.00 x 3.125; 25.0	Ra<1.6	Ra<0.8	Yes	Yes	No	F71700 >==
8	1.7	14.00 x 3.12 3, 23.0	na<1.0	Ra<0.4	162	165	INO	571792 😾
				na<0.4			Yes	571793 🛱
/.	2.5	14.00 × 0.05.0		Do +0.9	_			571794 🛱
2	2.5	14.00 x 2.3; 25.0		Ra<0.8			No	571795 🖼
				Ra<0.4			V	571796 🖼
	-	10.05 1.05 05.0	_	D- 00	_		Yes	571797 ≒
4	7	19.05×1.65; 25.0		Ra<0.8	-		No	571798 ≒
				Ra<0.4			.,	571799 ≒
							Yes	571800 😾
	14	25.4×1.65; 50.5		Ra<0.8	-		No	571801 🛒
				Ra<0.4				571802 ≒
			_		_		Yes	571803 ≒
1/2	35	38.1 × 1.65; 50.5		Ra<0.8			No	571804 🖫
				Ra<0.4				571805 🛒
							Yes	571806 🖼
!	64	50.8×1.65; 64.0		Ra<0.8			No	571807 📜
				Ra<0.4				571808 🛱
							Yes	571809 ≒
21/2	100	63.5 x 1.65; 77.5	1	Ra<0.8			No	574692 🖼
				Ra<0.4				573424 📜
			_				Yes	574718 🖼
3	150	76.2 x 1.65; 91.0		Ra<0.8	-		No	574693 🛱
				Ra<0.4			V-	573425 🖼
						Yes	574719 🖼	

^{1.) =} process connection size and pipe size

^{2.)} Dimensions of clamp connection: D2 = external diameter (side welded to measuring tube), s = wall thickness, D3 = external diameter (clamp connection side), see chapter "4.4. Flowmeter with clamp connections" on page 20.

^{3.)} The EHEDG compliance is only if used in combination with gaskets from Combifit International B.V.



Thread connection acc. to DIN 11851 series A for pipe acc. to DIN 11866 series A (DIN 11850)

Note:

The following variants are equipped with the special functions ATF (acoustic transmission factor) and DF (density factor).

Diameter 1.)	Maximal	Dimensions ^{2.)}	Surface quality		Approval ar	nd	Article no.
	flow rate	D2 x s; D3	Housing, outer surface of measurement tube	Inner surface of measurement tube	conformity		
[mm]	[m ³ /h]	[mm]	[µm]	[µm]	3-A (28-06)	EHEDG 3.)	
Electrical c	onnection:	1×8-pin M12 male co	nnector, operating voltag	e of 1235 V DC			
65	123	70.0 x 2.0; Rd 95 x ½	Ra<1.6	Ra<0.8	Yes	Yes	574707 📜
80	185	85.0x2.0; Rd 110x1/4		Ra<0.8			574708 🛱

- 1.) = process connection size and pipe size
- 2.) D2 for holder; s = thickness; D3: thread connection
- 3.) The EHEDG compliance is s only valid if used in combination with EHEDG-compliant gaskets from
 - Kieselmann GmbH, Germany (ASEPTO-STAR k-flex upgrade gaskets) or
 - Siersema Komponenten Service (S.K.S.) B.V. (Netherlands SKS gasket set DIN 11851 EHEDG with EPDM or FKM inner gasket).

Further variants on request		
Process connection For pipe DIN 11850: Clamp DIN 32676 Clamp DIN 11864-3 Flange DIN 11864-2 For pipe ISO 1127: Clamp DIN 11864-3 Flange DIN 11864-2 For pipe ASME BPE: Clamp DIN 11864-3 Flange DIN 11864-3 Flange DIN 11864-2 For pipe SMS 3008: SMS 3017	夢	Orifice • 0880 mm • 363 inch Additional • Without differentiation factor (DF) • Without acoustic transmission factor (ATF) • With density and mass flow • ATEX/IECEX Material • With inner surface of measurement tube - Ra < 0.8 μm (30 μin.) - Ra < 0.4 μm (15 μin.) (electro-polished) according to ISO 4288 Electrical connection • 1 × 5-pin M12 male connector • 1 × 8-pin M12 male connector

For any other variants, use the product enquiry form, see chapter "10.4. Bürkert Product Enquiry Form" on page 32 or check the readily available article no. listed in the Bürkert eShop.

Visit product website

39 | 40



10.8. Ordering chart accessories

Description			Article no.	
Type ME31	display module		265468 🛱	
Blind cover	in stainless steel 304/1.4301		265467 ≒	
biiidasak 🔵	Magnetic key for unlocking		690309 ≒	
System Co	nnect			
-	Gateway/Interface			
	hernet gateway (PROFINET IO, EtherNet/IP, Modbus TCP, EtherCAT®)		307390 ≒	
	gateway (PROFIBUS DPV1)		307393 ≒	
ype ME61				
	et ME61 3.5" display (8.9 cm)		368544 ≒	
DIP Acces	ssories			
üS Stick S	et			
	USB-büS interface set 1 (Type 8923) Further information can be found in chapter "9. Product accessories" on page 30.		772426 📜	
	terface set 2 (Type 8923) mation can be found in chapter "9. Product accessories" on page 30.		772551 ≒	
connectors				
	male connector, 5-pin, straight, A-coded		772416 🔄	
	ale connector, 5-pin, straight, A-coded			
	male connector, 5-pin, straight, A-coded		772417 🖼	
	ale connector, 5-pin, angled, A-coded		772418 😾	
	butor (M12 female connector, 5-pin to M12 male and female connectors, 5-pin)		772419 😾	
	butor with power interrupt (M12 female connector, 5-pin to M12 male and female connec	etors 5-nin)	772421 🖼	
buS adaptor (M12 male connector, 5-pin, A-coded to M12 male connector, 5-pin, A-coded)				
buS terminating resistor 120 ohms, M12 male connector, 5-pin				
	ting resistor 120 ohms, M12 female connector, 5-pin		772424 😾	
	s with cable		112-120 **	
	ole with M12 female connector, 8-pin to M12 male connector, 5-pin	0.5 m	773286 🖼	
	connector, 5-pin, angled, moulded on büS cable, with open leads	0.7 m	772626 🖫	
	connector, 5-pin, straight, moulded on büS cable, with open leads	1 m	772409 🖫	
	,,,	3 m	772410 🖫	
		5 m	772411 🖫	
		10 m	772412 🛒	
112 male c	onnector, 5-pin straight and micro USB connector, moulded on büS cable	0.3 m	773254 🖫	
	connector, 8-pin, straight, moulded on büS cable, with open leads	2 m	919061 🖫	
xtensions				
/_	M12 female and male connectors, 5-pin, straight, moulded on büS cable, shielded	0.1 m	772492 📜	
10		0.2 m	772402 📜	
		0.5 m	772403 🖼	
		1 m	772404 🖼	
		3 m	772405 🖼	
		5 m	772406 🖫	
		10 m	772407 📜	
		20 m	772408 📜	
ower sup	oly unit for standard rail Type 1573			
00240 V	AC / 24 V DC, 1 A (Class 2 according to NEC)		772361 🖼	
	AC / 24 V DC, 2 A (Class 2 according to NEC)		772362 🛒	
	AC / 24 V DC, 3.8 A (Class 2 according to NEC)		772898 📜	
00240 V	AC / 24 V DC, 10 A		772698 📜	

Visit product website ▶ 40 | 40